





PART NO.  
20021211

- NOTES:
- 1.MATERIAL:  
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94-V0 BLACK.  
TERMINAL: COPPER ALLOY
  - 2.THE HOUSING WILL WITHSTAND EXPOSURE TO 260-C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER OR VAPOR PHASE REFLOW OVEN.
  - 3.THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
  - 4.PRODUCT SPEC: GS-12-629
  - 5.PACKAGE SPEC: GS-14-1420
  - 6.20021211-00010CXLF FOR CUSTOMER SPECIFIED WITH PICK-UP CAP

RECOMMENDED PCB LAYOUT  
SCALE 5.000

SECTION B-B

| mat'l. code |             |     |          | surface                               |           |          | tolerance | projection | product family           |  |  |
|-------------|-------------|-----|----------|---------------------------------------|-----------|----------|-----------|------------|--------------------------|--|--|
|             |             |     |          | ISO 1302                              |           |          | ISO 406   | ISO 1101   | MINITEK127®              |  |  |
| ltr         | ecn no      | dr  | date     | tolerances unless otherwise specified |           |          |           |            | title                    |  |  |
| G           | ELX-N-23548 | TIM | 03/21/16 | angles                                |           |          | .0±.30    | mm         | SHROUDED HDR VT TH       |  |  |
|             |             |     |          | linear                                |           |          | .00±.20   |            |                          |  |  |
|             |             |     |          | 0°±2°                                 |           |          | .000±.10  | scale 1:1  |                          |  |  |
|             |             |     |          | dr                                    | ZK HU     | 08/07/12 |           |            | dwg no                   |  |  |
|             |             |     |          | engr                                  | ZK HU     | 08/07/12 |           |            | sheet 1 of 2             |  |  |
|             |             |     |          | chr                                   | BIAN RICK | 08/07/12 |           |            | 20021211                 |  |  |
|             |             |     |          | appd                                  | BIAN RICK | 08/07/12 |           |            | A3                       |  |  |
| sheet       | revision    | G   | G        |                                       |           |          |           |            | type                     |  |  |
| index       | sheet       | 1   | 2        |                                       |           |          |           |            | Product Customer Drawing |  |  |

| PART NO.           | PDS.   | DIM"x" | DIM"y" | DIM"z" |
|--------------------|--------|--------|--------|--------|
| 20021211-XXX06XXLF | 2 X 3  | 6.99   | 4.45   | 2.54   |
| 20021211-XXX08XXLF | 2 X 4  | 8.26   | 5.72   | 3.81   |
| 20021211-XXX10XXLF | 2 X 5  | 9.53   | 6.99   | 5.08   |
| 20021211-XXX12XXLF | 2 X 6  | 10.80  | 8.26   | 6.35   |
| 20021211-XXX14XXLF | 2 X 7  | 12.07  | 9.53   | 7.62   |
| 20021211-XXX16XXLF | 2 X 8  | 13.34  | 10.80  | 8.89   |
| 20021211-XXX18XXLF | 2 X 9  | 14.61  | 12.07  | 10.16  |
| 20021211-XXX20XXLF | 2 X 10 | 15.88  | 13.34  | 11.43  |
| 20021211-XXX22XXLF | 2 X 11 | 17.15  | 14.61  | 12.70  |
| 20021211-XXX24XXLF | 2 X 12 | 18.42  | 15.88  | 13.97  |
| 20021211-XXX26XXLF | 2 X 13 | 19.69  | 17.15  | 15.24  |
| 20021211-XXX28XXLF | 2 X 14 | 20.96  | 18.42  | 16.51  |
| 20021211-XXX30XXLF | 2 X 15 | 22.23  | 19.69  | 17.78  |
| 20021211-XXX32XXLF | 2 X 16 | 23.50  | 20.96  | 19.05  |
| 20021211-XXX34XXLF | 2 X 17 | 24.77  | 22.23  | 20.32  |
| 20021211-XXX36XXLF | 2 X 18 | 26.04  | 23.50  | 21.59  |
| 20021211-XXX38XXLF | 2 X 19 | 27.31  | 24.77  | 22.86  |
| 20021211-XXX40XXLF | 2 X 20 | 28.58  | 26.04  | 24.13  |
| 20021211-XXX42XXLF | 2 X 21 | 29.85  | 27.31  | 25.40  |
| 20021211-XXX44XXLF | 2 X 22 | 31.12  | 28.58  | 26.67  |
| 20021211-XXX46XXLF | 2 X 23 | 32.39  | 29.85  | 27.94  |
| 20021211-XXX48XXLF | 2 X 24 | 33.66  | 31.12  | 29.21  |
| 20021211-XXX50XXLF | 2 X 25 | 34.93  | 32.39  | 30.48  |
| 20021211-XXX52XXLF | 2 X 26 | 36.20  | 33.66  | 31.75  |
| 20021211-XXX54XXLF | 2 X 27 | 37.47  | 34.93  | 33.02  |
| 20021211-XXX56XXLF | 2 X 28 | 38.74  | 36.20  | 34.29  |
| 20021211-XXX58XXLF | 2 X 29 | 40.01  | 37.47  | 35.56  |
| 20021211-XXX60XXLF | 2 X 30 | 41.28  | 38.74  | 36.83  |
| 20021211-XXX62XXLF | 2 X 31 | 42.55  | 40.01  | 38.10  |
| 20021211-XXX64XXLF | 2 X 32 | 43.82  | 41.28  | 39.37  |
| 20021211-XXX66XXLF | 2 X 33 | 45.09  | 42.55  | 40.64  |
| 20021211-XXX68XXLF | 2 X 34 | 46.36  | 43.82  | 41.91  |
| 20021211-XXX70XXLF | 2 X 35 | 47.63  | 45.09  | 43.18  |
| 20021211-XXX72XXLF | 2 X 36 | 48.90  | 46.36  | 44.45  |
| 20021211-XXX74XXLF | 2 X 37 | 50.17  | 47.63  | 45.72  |
| 20021211-XXX76XXLF | 2 X 38 | 51.44  | 48.90  | 46.99  |
| 20021211-XXX78XXLF | 2 X 39 | 52.71  | 50.17  | 48.26  |
| 20021211-XXX80XXLF | 2 X 40 | 53.98  | 51.44  | 49.53  |
| 20021211-XXX82XXLF | 2 X 41 | 55.25  | 52.71  | 50.80  |
| 20021211-XXX84XXLF | 2 X 42 | 56.52  | 53.98  | 52.07  |
| 20021211-XXX86XXLF | 2 X 43 | 57.79  | 55.25  | 53.34  |
| 20021211-XXX88XXLF | 2 X 44 | 59.06  | 56.52  | 54.61  |
| 20021211-XXX90XXLF | 2 X 45 | 60.33  | 57.79  | 55.88  |

| PART NO.           | PDS.   | DIM"x" | DIM"y" | DIM"z" |
|--------------------|--------|--------|--------|--------|
| 20021211-XXX92XXLF | 2 X 46 | 61.60  | 59.06  | 57.15  |
| 20021211-XXX94XXLF | 2 X 47 | 62.87  | 60.33  | 58.42  |
| 20021211-XXX96XXLF | 2 X 48 | 64.14  | 61.60  | 59.69  |
| 20021211-XXX98XXLF | 2 X 49 | 65.41  | 62.87  | 60.96  |
| 20021211-XXXA0XXLF | 2 X 50 | 66.68  | 64.14  | 62.23  |

20021211 - X X X X X X LF

LEAD FREE

PLATING OPTIONAL

1: GOLD FLASH AT CONTACT, 1.27um MIN. MATTE TIN AT TAIL

2: GOLD FLASH AT CONTACT, GOLD FLASH AT TAIL

4: 0.25um Au MIN. AT CONTACT, 1.27um MIN.MATTE TIN AT TAIL

5: 0.25um Au MIN. AT CONTACT, GOLD FLASH AT TAIL

6: 0.38um GXT MIN. AT CONTACT, 1.27um MIN.MATTE TIN AT TAIL

7: 0.38um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

8: 0.76um GXT MIN. AT CONTACT, 1.27um MIN.MATTE TIN AT TAIL

9: 0.76um GXT MIN. AT CONTACT, GOLD FLASH AT TAIL

PACKING STYLE

T: TUBE

PIN NO. SEE TABLE

MATING LENGTH(DIM"A")

0: 3.05MM

TAIL LENGTH(DIM"B")

0: 2.30MM (FOR 1.6MM PCB)

1: 1.60MM (FOR 1.0MM PCB)

2: 2.70MM (FOR 2.0MM PCB)

RESERVE CODE

0: STANDARD

|             |          |    |      |            |                                       |            |                               |  |             |
|-------------|----------|----|------|------------|---------------------------------------|------------|-------------------------------|--|-------------|
| mat'l. code |          |    |      | surface    | tolerance                             | projection | product family                |  |             |
|             |          |    |      | ISO 1302 ✓ | ISO 406 ISO 1101                      |            | MINITEK127®                   |  |             |
| ltr         | ecn no   | dr | date |            | tolerances unless otherwise specified |            | title                         |  |             |
| G           |          |    |      | angles     | .0±.30                                | mm         | SHROUDED HDR VT TH            |  |             |
|             |          |    |      | linear     | .00±.20                               |            |                               |  |             |
|             |          |    |      | 0°±2°      | .000±.10                              | scale 1:1  |                               |  |             |
|             |          |    |      | dr         | ZK HU                                 | 08/07/12   | dwg no                        |  | sheet2 of 2 |
|             |          |    |      | engr       | ZK HU                                 | 08/07/12   | 20021211                      |  | A3          |
|             |          |    |      | chr        | BIAN RICK                             | 08/07/12   |                               |  |             |
|             |          |    |      | appd       | BIAN RICK                             | 08/07/12   |                               |  |             |
| sheet       | revision |    |      |            |                                       |            | type Product Customer Drawing |  |             |
| index       | sheet    |    |      |            |                                       |            |                               |  |             |