






LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			K3	REVISED PER ECO-15-011941	21AUG2015	NK	MM




SECTION X-X



RECOMMENDED HOLE LAYOUT

- ① THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- ② POINT OF MEASUREMENT FOR PLATING THICKNESS
- ③ MATERIAL: HOUSING— FLAME RETARDANT THERMOPLASTIC, COLOR—BLACK
POSTS— COPPER ALLOY
- ④ FINISH: POSTS— .000030 GOLD ON CONTACT AREA,
.000100—.000200 MATTE TIN—LEAD ON SOLDER TAIL,
ALL OVER .000050 NICKEL
- ⑤ FINISH: POSTS— .000030 GOLD ON CONTACT AREA,
.000100—.000200 MATTE TIN ON SOLDER TAIL,
ALL OVER .000050 NICKEL
- ⑥ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6	OBSOLETE	5	2.806	.106	3.032	2.900	29	60	7-102699-8	
		5	2.306	.106	2.532	2.400	24	50	7-102699-3	
		5	1.806	.106	2.032	1.900	19	40	6-102699-9	
		5	1.506	.106	1.732	1.600	16	34	6-102699-6	
		5	1.306	.106	1.532	1.400	14	30	6-102699-4	
		5	1.106	.106	1.332	1.200	12	26	6-102699-2	
		5	.806	.106	1.032	.900	9	20	5-102699-9	
		5	—	.406	.932	.800	8	18	5-102699-8	
		5	—	.306	.832	.700	7	16	5-102699-7	
		5	—	.306	.732	.600	6	14	5-102699-6	
		5	—	.206	.632	.500	5	12	5-102699-5	
		5	—	.206	.532	.400	4	10	5-102699-4	
		5	—	.106	.432	.300	3	8	5-102699-3	
		5	—	.106	.332	.200	2	6	5-102699-2	
6	OBSOLETE	4	2.806	.106	3.032	2.900	29	60	2-102699-8	
	OBSOLETE	4	2.706	.106	2.932	2.800	28	58	2-102699-7	
	OBSOLETE	4	2.606	.106	2.832	2.700	27	56	2-102699-6	
	OBSOLETE	4	2.506	.106	2.732	2.600	26	54	2-102699-5	
	OBSOLETE	4	2.406	.106	2.632	2.500	25	52	2-102699-4	
		4	2.306	.106	2.532	2.400	24	50	2-102699-3	
	OBSOLETE	4	2.206	.106	2.432	2.300	23	48	2-102699-2	
	OBSOLETE	4	2.106	.106	2.332	2.200	22	46	2-102699-1	
	OBSOLETE	4	1.906	.106	2.132	2.000	20	42	2-102699-0	
		4	1.806	.106	2.032	1.900	19	40	1-102699-9	
	OBSOLETE	4	1.706	.106	1.932	1.800	18	38	1-102699-8	
	OBSOLETE	4	1.606	.106	1.832	1.700	17	36	1-102699-7	
		4	1.506	.106	1.732	1.600	16	34	1-102699-6	
	OBSOLETE	4	1.406	.106	1.632	1.500	15	32	1-102699-5	
6	SUP BY 6-102699-6		4	1.306	.106	1.532	1.400	14	30	1-102699-4
		OBSOLETE	4	1.206	.106	1.432	1.300	13	28	1-102699-3
			4	1.106	.106	1.332	1.200	12	26	1-102699-2
		OBSOLETE	4	1.006	.106	1.232	1.100	11	24	1-102699-1
		OBSOLETE	4	.906	.106	1.132	1.000	10	22	1-102699-0
			4	.806	.106	1.032	.900	9	20	102699-9
			4	—	.406	.932	.800	8	18	102699-8
			4	—	.306	.832	.700	7	16	102699-7
			4	—	.306	.732	.600	6	14	102699-6
			4	—	.206	.632	.500	5	12	102699-5
			4	—	.206	.532	.400	4	10	102699-4
			4	—	.106	.432	.300	3	8	102699-3
			4	—	.106	.332	.200	2	6	102699-2
		OBSOLETE	4	2.006	.106	2.232	2.100	21	44	102699-1
	FINISH	E	D	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN 14APR05		 TE Connectivity	
		CHK J GESFORD 14APR05			
DIMENSIONS: INCHES		APVD J GESFORD 14APR05		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 		PRODUCT SPEC —		HDR ASSY, MOD II, COMPLIANT PIN, DBL ROW, .100 X .100 CL, 4 SIDED SHROUD	
MATERIAL FINISH		APPLICATION SPEC —		SIZE	RESTRICTED TO
SEE TABLE		WEIGHT —		CAGE CODE	
		CUSTOMER DRAWING		DRAWING NO	
		A1		00779	—
		SCALE		4:1	
		SHEET		1 OF 1	
		REV		K3	