



Photoelectric sensors
W4-3, Photoelectric proximity sensor,
Background suppression

WTB4-3P2261



SICK
Sensor Intelligence.


Model Name > [WTB4-3P2261](#)Part No. > [1028100](#)

Illustration may differ

At a glance

- Intense light spot with PinPoint LED technology
- Sensor with IR light available upon request
- Sensing range of 4 - 150 mm
- Background suppression sensor available with laser-like light spot
- Adjustment either via teach-in pushbutton, 5-turn potentiometer, cable or IO-Link
- Second emitter LED designed for suppression of shiny backgrounds
- Flexible sensing ranges and hysteresis settings
- Key lock function, remote teach, quality monitoring

Your benefits

- Reliable detection of objects regardless of color and consistency
- Smart machine design ensures low-cost integration due to mounting flexibility in areas with limited space
- Best-in-class background suppression and a high immunity to ambient light, ensuring reliable object detection
- Rugged mounting system with M3 threaded metal inserts reduces maintenance costs due to a long service life
- Precise detection with a high level of repeat accuracy due to an intense light spot with PinPoint LED technology
- Quick and easy format adjustment
- Easy monitoring of sensor status
- Key lock function and parameter download prevent incorrect settings

**Features**

Sensor/detection principle:	Photoelectric proximity sensor, Background suppression
Dimensions (W x H x D):	16 mm x 39.5 mm x 12 mm
Housing design (light emission):	Rectangular
Sensing range max.:	4 mm ... 150 mm ¹⁾
Sensing range:	15 mm ... 150 mm ²⁾
Type of light:	Visible red light ³⁾
Light source:	PinPoint LED
Wave length:	650 nm
Adjustment:	Potentiometer, 5-turn
Light spot size (distance):	Ø 7 mm (50 mm)


¹⁾ ²⁾ Object with 90 % reflectance (referred to standard white DIN 5033) ³⁾ Average service life of 100,000 h at $T_A = +25^\circ\text{C}$

Mechanics/electronics

Supply voltage:	10 V DC ... 30 V DC ¹⁾
Ripple:	< 5 Vpp ²⁾
Power consumption:	≤ 20 mA ³⁾
Switching output:	PNP
Output function:	Complementary
Switching mode:	Light/dark-switching
Output current I _{max.} :	≤ 100 mA
Response time:	< 0.5 ms ⁴⁾
Switching frequency:	1,000 Hz ⁵⁾
Connection type:	Connector M8, 4-pin
Circuit protection:::	A, C, D ^{6) 7) 8)}
Protection class:	III
Weight:	30 g
Housing material:	ABS, Plastic
Optics material:	PMMA
Enclosure rating:	IP 67 IP 66
Ambient operating temperature:	-40 °C ... 60 °C
Ambient storage temperature:	-40 °C ... 75 °C
UL File No.:	NRKH.E181493 & NRKH7.E181493


1) Limit values 2) May not exceed or fall short of V_S tolerances 3) Without load 4) Signal transit time with resistive load 5) With light/dark ratio 1:1 6) A = V_S
connections reverse-polarity protected 7) C = interference suppression 8) D = outputs overcurrent and short-circuit protected

Dimensional drawing




- [1] Standard direction of the material being scanned
- [2] Optical axis, sender
- [3] Optical axis, receiver
- [4] Status indicator LED, yellow: Status of received light beam
- [5] Status indicator LED green: power on
- [6] Potentiometer
- [7] Threaded mounting hole M3
- [8] Connection


Connection diagram




Characteristic curve



Connection type



Sensing range diagram



1 Scanning range on black, 6 % remission

2 Scanning range on grey, 18 % remission

3 Scanning range on white, 90 % remission

Australia Phone +61 3 9457 0600 1800 334 802 – tollfree E-Mail sales@sick.com.au	Norge Phone +47 67 81 50 00 E-Mail austefjord@sick.no
Belgium/Luxembourg Phone +32 (0)2 466 55 66 E-Mail info@sick.be	Österreich Phone +43 (0)22 36 62 28 8-0 E-Mail office@sick.at
Brasil Phone +55 11 3215-4900 E-Mail sac@sick.com.br	Polška Phone +48 22 837 40 50 E-Mail info@sick.pl
Canada Phone +1 905 771 14 44 E-Mail information@sick.com	România Phone +40 356 171 120 E-Mail office@sick.ro
Ceská Republika Phone +420 2 57 91 18 50 E-Mail sick@sick.cz	Russia Phone +7-495-775-05-30 E-Mail info@sick.ru
China Phone +86 4000 121 000 E-Mail info.china@sick.net.cn Phone +852-2153 6300 E-Mail ghk@sick.com.hk	Schweiz Phone +41 41 619 29 39 E-Mail contact@sick.ch
Danmark Phone +45 45 82 64 00 E-Mail sick@sick.dk	Singapore Phone +65 6744 3732 E-Mail admin@sicksdp.com.sg
Deutschland Phone +49 211 5301-301 E-Mail kundenservice@sick.de	Slovenija Phone +386 (0)1-47 69 990 E-Mail office@sick.si
España Phone +34 93 480 31 00 E-Mail info@sick.es	South Africa Phone +27 11 472 3733 E-Mail info@sickautomation.co.za
France Phone +33 1 64 62 35 00 E-Mail info@sick.fr	South Korea Phone +82 2 786 6321/4 E-Mail info@sickkorea.net
Great Britain Phone +44 (0)1727 831121 E-Mail info@sick.co.uk	Suomi Phone +358-9-25 15 800 E-Mail sick@sick.fi
India Phone +91-22-4033 8333 E-Mail info@sick-india.com	Sverige Phone +46 10 110 10 00 E-Mail info@sick.se
Israel Phone +972-4-6801000 E-Mail info@sick-sensors.com	Taiwan Phone +886-2-2375-6288 E-Mail sales@sick.com.tw
Italia Phone +39 02 27 43 41 E-Mail info@sick.it	Türkiye Phone +90 (216) 528 50 00 E-Mail info@sick.com.tr
Japan Phone +81 (0)3 3358 1341 E-Mail support@sick.jp	United Arab Emirates Phone +971 (0) 4 8865 878 E-Mail info@sick.ae
Magyarország Phone +36 1 371 2680 E-Mail office@sick.hu	USA/México Phone +1(952) 941-6780 1 800-325-7425 – tollfree E-Mail info@sickusa.com
Netherlands Phone +31 (0)30 229 25 44 E-Mail info@sick.nl	More representatives and agencies at www.sick.com