




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		H	REVISE PER ECN 0G3B-0124-00	26APR00	SU	GS
			H1	REVISED PER ECO-10-000443	13JAN10	KK	AEG

1. MATES WITH MATE-N-LOK II PLUG CONNECTOR
USING PART NUMBER 193797-1 OR 193842-1
SOCKET CONTACTS.
2. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT P.C. LAYOUT.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED LAYOUT FOR P.C. BOARD

3 OBSOLETE	TUBE	1.57 [.062]	3.68 [.145]	194002-3
	BULK	3.17 [.125]	5.20 [.205]	194002-2
	BULK	1.57 [.062]	3.68 [.145]	194002-1
PACKAGING		PC BOARD THICKNESS	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	06/SEP/94	AMP AMP Incorporated Harrisburg, PA 17105-3608	
		CHK	16/MAY/94		
DIMENSIONS:		APVD	16/MAY/94	NAME	
mm [in]		PRODUCT SPEC			
		APPLICATION SPEC		HIGH CURRENT VERT. PIN HEADER ASSY; MATE-N-LOK II, 6 CIRCUIT	
		WEIGHT			
MATERIAL		CUSTOMER DRAWING		SIZE	CAGE CODE
-		FINISH		A2	00779
TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH -		DRAWING NO	
				C-194002	
				SCALE	SHEET
				-	1 OF 1
					REV H1