



HONEYWELL PART NUMBER
1SX44-T
PRODUCT CODE VDA3900

REV	DOCUMENT	CHANGED BY	CHECK
6	0038446	KVB 20MAY08	BLR



NOTE -
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
2- TERMINALS ARE PLATED FOR SOLDERING
3- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
4- SWITCH HAS A GREATER OVERTRAVEL THAN STANDARD CONSTRUCTION
ADDITIONAL OVERTRAVEL WILL TEND TO REDUCE MECHANICAL LIFE

RELEASE NO. SR 12836

REPLACES -

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 		DRAWN	SPK	03DEC07	Honeywell					
OPERATING FORCE — — — 5 OZ MAX		CONTACT ARRANGEMENT SPDT					CHECK	RJ	03DEC07						
RELEASE FORCE— — — — 1 OZ MIN		28 VOLTS DC RATING					THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC					
DIFFERENTIAL TRAVEL— — — .005 MAX			SEA LEVEL	50,000 FT											
OVERTRAVEL — — — — — .007 MIN		INDUCTIVE	4 AMP	2.5 AMP											
		RESISTIVE	7 AMP	7 AMP				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
		APPROVALS	KEMA, CE	7A 250V ~ T125 5E4 				RASTER			B	I	1SX44-T		6
			UL, CSA	7A 250 VAC   BRAND L7											
											SCALE	-	WEIGHT:.003 LB MAX	SHEET 1 OF 1	