

Consolidated Electronic Wire & Cable

11044 King St

Franklin Park, IL 60131 US

Phone: 847-455-8830 **Fax:** 847-455-8837**Toll-free:** 800-621-4278**Email:** info@conwire.com **Website:** http://www.conwire.com

Part # 30 PE, 30 AWG Plain Enamel Magnet Wire (PE)

**30 AWG Plain Enamel Magnet Wire (PE)****Product Construction****Construction 30 AWG (PE):**

- Solid bare copper conductor
- Polyurethane / Polyamide (Nylon)
- (PE) Plain Enamel Magnet Wire
- Solderable:
 - 14-24 AWG at 430°C
 - 25-40 AWG at 360°C

Characteristics:

- Temperature: 14-24 AWG -30°C to +130°C
- MIL JW-1177/9, MW 28-C, Class 130
- Temperature: 25-40 AWG -30°C to +155°C
- MIL JW-1177/42, MW80-C, Class 155

Packing

- 1/4 lb. spools
- 1/2 lb. spools
- 1 lb. spools
- Also available on bulk spools

Sold in standard packages of five spools per gauge size and spool put-up.

SPECIFICATIONS

Conductor Size	30 AWG
Nominal O.D.	0.0109 in.
Spool Put-Up	1/4 lbs 1/2 lbs 1 lbs
Temperature	-30 to +155 °C