

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

52045-2945

Status:

Active

Overview:

FFC-FPC (Through-Hole)

Description:

FFC/FPC Connector, Non-ZIF, Vertical Receptacle, 29 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-52045-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Overview

Product Name

UPC

FFC/FPC Connectors

52045

FFC-FPC (Through-Hole)

N/A

800753571624

Physical

Circuits (Loaded)

Color - Resin

Contact Position

Entry Angle

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Retention

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to PCB

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

Wire/Cable Type

29

Gray

N/A

Vertical

8.00mm

Phosphor Bronze

Tin

Tin

Polyester

2275.500/mg

1

Vertical

3.50mm

None

Tray

1.25mm

0.914µm

0.914µm

Yes

No

No

-40°C to +85°C

Through Hole - Kinked Pin

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

1A

200V

Material Info


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-52045-001, RPS-52045-003, RPS-52045-006

SD-52045-**45



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

52045Series

This document was generated on 07/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[52045-2945](#)