



P-Channel JFETs

2N5460

SST5460

2N5461

SST5461

2N5462

SST5462

PRODUCT SUMMARY

Part Number	$V_{GS(off)}$ (V)	$V_{(BR)GSS}$ Min (V)	g_{fs} Min (mS)	I_{DSS} Min (mA)
2N/SST5460	0.75 to 6	40	1	-1
2N/SST5461	1 to 7.5	40	1.5	-2
2N/SST5462	1.8 to 9	40	2	-4

FEATURES

- High Input Impedance
- Very Low Noise
- High Gain: $A_V = 80$ @ 20 μ A
- Low Capacitance: 1.2 pF Typical

BENEFITS

- Low Signal Loss/System Error
- High System Sensitivity
- High-Quality Low-Level Signal Amplification


APPLICATIONS

- Low-Current, Low-Voltage Amplifiers
- High-Side Switching
- Ultrahigh Input Impedance Pre-Amplifiers


DESCRIPTION

The 2N/SST5460 series are p-channel JFETs designed to provide all-around performance in a wide range of amplifier and analog switch applications.

The 2N series, TO-226AA (TO-92), and SST series, TO-236 (SOT-23), plastic packages provide low cost options, and are available in tape-and-reel for automated assembly, (see Packaging Information).



2N5460
2N5461
2N5462



SST5460 (B0)*
SST5461 (B1)*
SST5462 (B2)*

*Marking Code for TO-236

ABSOLUTE MAXIMUM RATINGS

Gate-Drain Voltage 40 V
Gate-Source Voltage 40 V
Gate Current -10 mA
Storage Temperature -65 to 150°C
Operating Junction Temperature -55 to 150°C

Lead Temperature ($1/16$ " from case for 10 sec.) 300°C
Power Dissipation^a 350 mW

Notes

a. Derate 2.8 mW/°C above 25°C







SPECIFICATIONS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)







Parameter	Symbol	Test Conditions	Typ ^a	Limits						Unit	
				2N/SST5460		2N/SST5461		2N/SST5462			
				Min	Max	Min	Max	Min	Max		
Static											
Gate-Source Breakdown Voltage	V _{(BR)GSS}	I _G = 10 μA , V _{DS} = 0 V	55	40		40		40		V	
Gate-Source Cutoff Voltage	V _{GS(off)}	V _{DS} = −15 V, I _D = −1 μA		0.75	6	1	7.5	1.8	9		
Saturation Drain Current ^b	I _{DSS}	V _{DS} = −15 V, V _{GS} = 0 V		−1	−5	−2	−9	−4	−16	mA	
Gate Reverse Current	I _{GSS}	V _{GS} = 20 V, V _{DS} = 0 V	0.003		5		5		5	nA	
		T _A = 100°C	0.0003		1		1		1	μA	
Gate Operating Current	I _G	V _{DG} = −20 V, I _D = −0.1 mA	3							pA	
Drain Cutoff Current	I _{D(off)}	V _{DS} = −15 V, V _{GS} = 10 V	−5								
Gate-Source Voltage	V _{GS}	V _{DS} = −15 V	I _D = −0.1 mA	1.3	0.5	4				V	
			I _D = −0.2 mA	2.3			0.8	4.5			
			I _D = −0.4 mA	3.8					1.5		6
Gate-Source Forward Voltage	V _{GS(F)}	I _G = −1 mA , V _{DS} = 0 V	−0.7								
Dynamic											
Common-Source Forward Transconductance	g _{fs}	V _{DS} = −15 V, V _{GS} = 0 V f = 1 kHz		1	4	1.5	5	2	6	mS	
Common-Source Output Conductance	g _{os}				75		75		75	μS	
Common-Source Reverse Transfer Capacitance	C _{iss}	V _{DS} = −15 V, V _{GS} = 0 V f = 1 MHz	2N	4.5		7		7		pF	
			SST	4.5							
Common-Source Reverse Transfer Capacitance	C _{rss}			1.2							
Common-Source Output Capacitance	C _{oss}		2N	1.5		2		2			2
			SST	1.5							
Equivalent Input Noise Voltage	ē _n		2N	15		115		115			115
		SST	15								
Noise Figure	NF	2N	0.2		2.5		2.5		2.5	dB	
		SST	0.2								







Notes

- a. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.
b. Pulse test: $PW \leq 300\ \mu\text{s}$ duty cycle $\leq 2\%$.

PSCIB

**TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)****Drain Current and Transconductance
vs. Gate-Source Cutoff Voltage****On-Resistance and Output Conductance
vs. Gate-Source Cutoff Voltage****Output Characteristics****Output Characteristics****Output Characteristics****Output Characteristics**

TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)


**TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)**



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.