




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	V	REDRAWN/REVISED PER ECO-17-001755	20NOV2017	KS	JO








BASIC DIMENSIONS FOR
EVEN NO OF SPACES
(SEE TABLE)



BASIC DIMENSIONS FOR
ODD NO OF SPACES
(SEE TABLE)

- 1 CONTACT AREAS PLATED WITH 0.76µm GOLD;SOLDER TAILS
PLATED WITH 3.81µm TIN-LEAD,ALL OVER 1.27µm NICKEL
2. NOTE DELETED.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION
OF THE POST AND HOUSING.
- 4 CONTACT AREAS PLATED WITH 0.76µm GOLD; SOLDER TAILS
PLATED WITH 3.81µm TIN,ALL OVER 1.27µm NICKEL.
- 5 FINISH: 0.03µm MIN GOLD ON GOLD PLATED AREA, 3.81µm MATTE
TIN LEAD ON TIN PLATE AREA. UNDER PLATING SHOULD BE
1.27µm NICKEL ON ENTIRE CONTACT.
- 6 FINISH: 0.03µm MIN GOLD ON GOLD PLATED AREA, 3.81µm MATTE TIN
ON TIN PLATE AREA. UNDER PLATING SHOULD BE 1.27µm NICKEL ON
ENTIRE CONTACT.
7. NOTE DELETED.
8. NOTE DELETED.
9. NOTE DELETED.
- 10 MATERIAL- HOUSING:LCP, COLOR:BLACK
POST: COPPER ALLOY



6	62.23	49	67.16	100	7-104076-8
	30.48	24	35.41	50	7-104076-7
	17.78	14	22.71	30	7-104076-6
	5.08	4	10.01	10	7-104076-5
	49.53	39	54.46	80	7-104076-4
	24.13	19	29.06	40	7-104076-3
	36.83	29	41.76	60	7-104076-2
	11.43	9	16.36	20	7-104076-1
4	62.23	49	67.16	100	5-104076-8
	30.48	24	35.41	50	5-104076-7
	17.78	14	22.71	30	5-104076-6
	5.08	4	10.01	10	5-104076-5
	49.53	39	54.46	80	5-104076-4
	24.13	19	29.06	40	5-104076-3
	36.83	29	41.76	60	5-104076-2
	11.43	9	16.36	20	5-104076-1
FINISH	DIM_C	B SPACES	DIM_A	NO OF POSN	PART NUMBER

5	62.23	49	67.16	100	2-104076-8
	30.48	24	35.41	50	2-104076-7
	17.78	14	22.71	30	2-104076-6
	5.08	4	10.01	10	2-104076-5
	49.53	39	54.46	80	2-104076-4
	24.13	19	29.06	40	2-104076-3
	36.83	29	41.76	60	2-104076-2
	11.43	9	16.36	20	2-104076-1
1	62.23	49	67.16	100	104076-8
	30.48	24	35.41	50	104076-7
	17.78	14	22.71	30	104076-6
	5.08	4	10.01	10	104076-5
	49.53	39	54.46	80	104076-4
	24.13	19	29.06	40	104076-3
	36.83	29	41.76	60	104076-2
	11.43	9	16.36	20	104076-1
FINISH	DIM_C	B SPACES	DIM_A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±" 1 PLC ±.3 2 PLC ±.3 3 PLC ±0.13 4 PLC ±" ANGLES ±0.5°

MATERIAL 10

SEE TABLE

DWN R. SHRISHAIL 20NOV2017

CHK J. OLSON 20NOV2017

APVD J. OLSON 20NOV2017

PRODUCT SPEC 108-1093

APPLICATION SPEC 114-25031

WEIGHT -

CUSTOMER DRAWING

NAME

SIZE CAGE CODE DRAWING NO

RESTRICTED TO

TE Connectivity

HEADER ASSEMBLY, VERTICAL, SHROUDED, WITH SLOT, AMPMODU System 50

A100779C=104076

SCALE 6:1 SHEET 1 OF 1 REV V