

5Vdc • SINE OUTPUT, FULL-SIZE DIP CRYSTAL CLOCK OSCILLATORS

ACOS



RoHS
Compliant



20 x 12.6 x 5.08 mm

FEATURES:

- Sine wave output.
- Wide Frequency Range.
- Low harmonic distortion.

APPLICATIONS:

- Provide clock signals for microprocessors and digital circuits.
- High Output drive capability applications.
- Great for low EMI applications.

STANDARD SPECIFICATIONS:

PARAMETERS

Frequency Range	8MHz - 40MHz
Operating Temperature	0°C to +70°C (see options)
Storage Temperature	-55°C to +125°C
Frequency Stability	±100ppm max. (See Options)
Supply Voltage	5.0Vdc ±10%
Output load	50W
Output power	0dBm min.
Harmonics	-25dBc min.
Aging	±5ppm/yr. max.

Please see environmental, and mechanical specifications, see appendix C. Group 1.


Marking, see appendix B. Recommended handling, see appendix F.

Test circuits and waveform, see appendix B.

Application notes, see appendix A.

Value added, see appendix D.

OUTLINE DIMENSIONS:



Dimensions: Inches (mm)

Pin Number	Function
1	NC
7	GND / Case
8	Output
14	Vcc

OPTIONS & PART IDENTIFICATION:

ACOS - Frequency - Temperature - Overall Frequency Stability - Value Added - Packaging

XX.XXXMHz

-D for -10°C to +60°C
-E for -20°C to +70°C
-F for -30°C to +70°C
-N for -30°C to +85°C
-L for -40°C to +85°C

-R for ± 25ppm max
-K for ± 30ppm max
-H for ± 35ppm max
-C for ± 50ppm max

-G Gull Wing
-QXX (Trimmed Leads)

-TY for Tray packing

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale **Revised: 10.23.10**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 fax 949-546-8001 www.abracon.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ACO-40.000MHZ-EK](#) [ACO-12.000MHZ-EK](#) [ACO-8.000MHZ-EK](#) [ACO-27.000MHZ-EK](#) [ACO-14.31818MHZ-EK](#)
[ACO-48.000MHZ-EK](#) [ACO-3.6864MHZ-EK](#) [ACO-25.000MHZ-EK](#) [ACO-10.000MHZ-EK](#) [ACO-32.768MHZ-EK](#) [ACO-](#)
[20.000MHZ-EK](#) [ACO-32.000MHZ-EK](#) [ACO-18.432MHZ-EK](#) [ACO-24.576MHZ-EK](#)