

RED INDICATES ORIGINAL

DATA CONTAINED IN THIS DOCUMENT IS
PROPRIETARY TO TROMPETER ELECTRONICS INC.
AND SHALL NOT BE DISCLOSED, COPIED OR USED
FOR PROCUREMENT OR MANUFACTURE WITHOUT
EXPRESS WRITTEN PERMISSION.





REVISIONS

3-0083

SH 1

REV	EO	DESCRIPTION	DWN	APPROVED	DATE
J	11958	ADDED SHT 2, DIM .610 $\pm$.010 WAS .675 $\pm$.005; SEE ECO	DBN	Bm; <i>FA</i>	3/31/97

INCH	MM
.005	0.13
.030	0.76
.041	1.04
.090	2.29
.140	3.56
.281	7.14
.284	7.21
.414	10.52
.630	16.00
.635	16.13
.750	19.05
.800	20.32
.865	21.97
.866	22.00
1.365	34.67



RECOMMENDED
PANEL CUTOUT
SCALE: 1/1

- MAX PANEL THK .140
- CONCENTRIC TWINAX/TRIAX TRB REAR MOUNTING
INSULATED BULKHEAD SOLDER POT RECEPTACLE
- FINISH: TFS-1A (NICKEL)
- ALL DIM ARE IN INCHES

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED	TROMPETER ELECTRONICS, INC.	BJ75	
.XX $\pm$.XXX $\pm$.005 .XXXX $\pm$ ANGLES $\pm$			
DWN	DBN	3/21/97	MATERIAL
CHK	Bm	3/28/97	CODE IDENT
ENGR	FA	3/28/97	14949
APPR	FA	3/28/97	DRAWING NO.
			3-0083
			REV J
NEXT ASSY	SCALE 2/1	DATE 10/14/82	SHEET 1 OF 2