

## ISL8485, ISL8490, ISL8491

5V, Low Power, High Speed, RS-485/RS-422 Transceivers

The [ISL8485](#), [ISL8490](#), and [ISL8491](#) RS-485/RS-422 devices are BiCMOS 5V powered, single transceivers that meet both the RS-485 and RS-422 standards for balanced communication. Unlike competitive devices, this family is specified for 10% tolerance supplies (4.5V to 5.5V).

The ISL8485, ISL8490, and ISL8491 feature data rates up to 5Mbps.

All devices present a single unit load to the RS-485 bus, which allows up to 32 transceivers on the network.

The receiver (Rx) inputs feature a “fail-safe if open” design, which ensures a logic high Rx output if the Rx inputs are floating.

The driver (Tx) outputs are short-circuit protected, even for voltages exceeding the power supply voltage. Additionally, on-chip thermal shutdown circuitry disables the Tx outputs to prevent damage if power dissipation becomes excessive.

The ISL8490 and ISL8491 are configured for full duplex (separate Rx input and Tx output pins) applications. Half duplex configurations (ISL8485) multiplex the Rx inputs and Tx outputs to allow transceivers with Rx and Tx disable functions in 8 Ld packages.

### Features


- Specified for 10% tolerance supplies
- Class 3 ESD protection (HBM) on all pins: 7kV
- High data rates: up to 5Mbps
- Single unit load allows up to 32 devices on the bus
- Low quiescent current: 500μA
- -7V to +12V common-mode input voltage range
- Three state Rx and Tx outputs (except ISL8490)
- 30ns propagation delays, 5ns skew
- Full duplex and half duplex pinouts
- Operation from a single +5V supply (10% tolerance)
- Current limiting and thermal shutdown for driver overload protection
- Pb-free plus anneal (RoHS compliant)

### Applications


- Factory automation
- Security networks
- Building environmental control systems
- Industrial/process control networks
- Level translators (for example, RS-232 to RS-422)
- RS-232 “extension cords”

## Typical Operating Circuits


ISL8485



ISL8490



ISL8491



To calculate the resistor values, refer to [TB509](#).

TABLE 1. SUMMARY OF FEATURES

| PART NUMBER | HALF/FULL DUPLEX | NO. OF DEVICES ALLOWED ON BUS | DATA RATE (Mbps) | SLEW-RATE LIMITED? | RECEIVER/ DRIVER ENABLE? | QUIESCENT $I_{CC}$ ( $\mu$ A) | LOW POWER SHUTDOWN? | PIN COUNT |
|-------------|------------------|-------------------------------|------------------|--------------------|--------------------------|-------------------------------|---------------------|-----------|
| ISL8485     | Half             | 32                            | 5                | No                 | Yes                      | 500                           | No                  | 8         |
| ISL8490     | Full             | 32                            | 5                | No                 | No                       | 500                           | No                  | 8         |
| ISL8491     | Full             | 32                            | 5                | No                 | Yes                      | 500                           | No                  | 14        |


## Ordering Information

| PART NUMBER ( <a href="#">Notes 2, 3</a> )                               | PART MARKING | PACKAGE DESCRIPTION (RoHS COMPLIANT) | PKG. DWG. # | Carrier Type ( <a href="#">Note 1</a> ) | TEMP. RANGE  |
|--------------------------------------------------------------------------|--------------|--------------------------------------|-------------|-----------------------------------------|--------------|
| ISL8485CBZ                                                               | 8485         | 8 Ld SOIC                            | M8.15       | Tube                                    | 0 to +70°C   |
| ISL8485CBZ-T                                                             | CBZ          |                                      |             | Reel, 2.5k                              |              |
| ISL8485CPZ (No longer available, recommended replacement: ISL8485ECBZ-T) | ISL 8485CPZ  | 8 Ld PDIP ( <a href="#">Note 4</a> ) | E8.3        | Tube                                    | -40 to +85°C |
| ISL8485IBZ                                                               | 8485         | 8 Ld SOIC                            | M8.15       | Tube                                    |              |
| ISL8485IBZ-T                                                             | IBZ          |                                      |             | Reel, 2.5k                              |              |
| ISL8485IPZ (No longer available, recommended replacement: ISL8485EIBZ-T) | ISL 8485IPZ  | 8 Ld PDIP ( <a href="#">Note 4</a> ) | E8.3        | Tube                                    |              |
| ISL8490IBZ                                                               | 8490         | 8 Ld SOIC                            | M8.15       | Tube                                    |              |
| ISL8490IBZ-T                                                             | IBZ          |                                      |             | Reel, 2.5k                              |              |
| ISL8491IBZ                                                               | 8491IBZ      | 14 Ld SOIC                           | M14.15      | Tube                                    |              |

### NOTE:

- See [TB347](#) for details about reel specifications.
- Pb-free plus anneal products employ special Pb-free material sets; molding compounds/die attach materials and 100% matte tin plate termination finish, which are RoHS compliant and compatible with both SnPb and Pb-free soldering operations. Pb-free products are MSL classified at Pb-free peak reflow temperatures that meet or exceed the Pb-free requirements of IPC/JEDEC J STD-020.
- For Moisture Sensitivity Level (MSL), see the [ISL8485](#), [ISL8490](#), and [ISL8491](#) product information pages. For more information about MSL, see [TB363](#).
- Pb-free PDIPs can be used for through hole wave solder processing only. They are not intended for use in Reflow solder processing applications.

Pinouts



Pin Descriptions

| PIN | FUNCTION                                                                                                                                    |
|-----|---------------------------------------------------------------------------------------------------------------------------------------------|
| RO  | Receiver output: RO is high if A > B by at least 0.2V; RO is low if A < B by 0.2V or more; RO = high if A and B are unconnected (floating). |
| RE  | Receiver output enable. RO is enabled when RE is low; RO is high impedance when RE is high.                                                 |
| DE  | Driver output enable. The driver outputs Y and Z are enabled by bringing DE high. They are high impedance when DE is low.                   |
| DI  | Driver input. A low on DI forces output Y low and output Z high. Similarly, a high on DI forces output Y high and output Z low.             |
| GND | Ground connection.                                                                                                                          |
| A/Y | Noninverting receiver input and noninverting driver output. Pin is an input (A) if DE = 0; pin is an output (Y) if DE = 1.                  |
| B/Z | Inverting receiver input and inverting driver output. Pin is an input (B) if DE = 0; pin is an output (Z) if DE = 1.                        |
| A   | Noninverting receiver input.                                                                                                                |
| B   | Inverting receiver input.                                                                                                                   |
| Y   | Noninverting driver output.                                                                                                                 |
| Z   | Inverting driver output.                                                                                                                    |
| VCC | System power supply input (4.5V to 5.5V).                                                                                                   |
| NC  | No connection.                                                                                                                              |

Truth Tables

| TRANSMITTING |    |    |         |        |
|--------------|----|----|---------|--------|
| INPUTS       |    |    | OUTPUTS |        |
| RE           | DE | DI | Z       | Y      |
| X            | 1  | 1  | 0       | 1      |
| X            | 1  | 0  | 1       | 0      |
| 0            | 0  | X  | High-Z  | High-Z |

| RECEIVING |                |                |             |        |
|-----------|----------------|----------------|-------------|--------|
| INPUTS    |                |                |             | OUTPUT |
| RE        | DE Half Duplex | DE Full Duplex | A-B         | RO     |
| 0         | 0              | X              | ≥ +0.2V     | 1      |
| 0         | 0              | X              | ≤ -0.2V     | 0      |
| 0         | 0              | X              | Inputs Open | 1      |
| 1         | 1              | 1              | X           | High-Z |

**Absolute Maximum Ratings**

|                                      |                              |
|--------------------------------------|------------------------------|
| $V_{CC}$ to Ground                   | 7V                           |
| Input Voltages                       |                              |
| DI, DE, $\overline{RE}$              | -0.5V to ( $V_{CC} + 0.5V$ ) |
| Input/Output Voltages                |                              |
| A, B, Y, Z                           | -8V to +12.5V                |
| RO                                   | -0.5V to ( $V_{CC} + 0.5V$ ) |
| Short Circuit Duration               |                              |
| Y, Z                                 | Continuous                   |
| ESD Rating                           |                              |
| HBM (Per MIL-STD-883, Method 3015.7) | >7kV                         |

**Thermal Information**

|                                                       |                           |
|-------------------------------------------------------|---------------------------|
| Thermal Resistance (Typical, <a href="#">Note 5</a> ) | $\theta_{JA}$ (°C/W)      |
| 8 Ld SOIC Package                                     | 170                       |
| 8 Ld PDIP Package ( <a href="#">Note 6</a> )          | 140                       |
| 14 Ld SOIC Package                                    | 120                       |
| Moisture Sensitivity (see <a href="#">TB363</a> )     |                           |
| All Packages                                          | Level 1                   |
| Maximum Junction Temperature (Plastic Package)        | +150°C                    |
| Maximum Storage Temperature Range                     | -65°C to +150°C           |
| Pb-Free Reflow Profile (SOIC only)                    | see <a href="#">TB493</a> |

**Operating Conditions**

|                   |                |
|-------------------|----------------|
| Temperature Range |                |
| ISL84XXCX         | 0°C to +70°C   |
| ISL84XXIX         | -40°C to +85°C |

**CAUTION:** Stresses above those listed in Absolute Maximum Ratings can permanently damage the device. This is a stress only rating. Operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

**NOTE:**

- $\theta_{JA}$  is measured with the component mounted on a low-effective thermal conductivity test board in free air. See [TB379](#) for details.
- Pb-free PDIPs can be used for through hole wave solder processing only. They are not intended for use in Reflow solder processing applications.

**Electrical Specifications** Test Conditions:  $V_{CC} = 4.5V$  to  $5.5V$ ; unless otherwise specified. Typical values are at  $V_{CC} = 5V$ ,  $T_A = +25^\circ C$ , [Note 7](#)

| PARAMETER                                                                                   | SYMBOL           | TEST CONDITIONS                                | TEMP (°C)             | MIN  | TYP  | MAX             | UNIT |    |
|---------------------------------------------------------------------------------------------|------------------|------------------------------------------------|-----------------------|------|------|-----------------|------|----|
| DC CHARACTERISTICS                                                                          |                  |                                                |                       |      |      |                 |      |    |
| Driver Differential V <sub>OUT</sub> (No Load)                                              | V <sub>OD1</sub> |                                                | Full                  | -    | -    | V <sub>CC</sub> | V    |    |
| Driver Differential V <sub>OUT</sub> (with Load)                                            | V <sub>OD2</sub> | R = 50Ω (RS-422), <a href="#">Figure 1</a>     | Full                  | 2    | 3    | -               | V    |    |
|                                                                                             |                  | R = 27Ω (RS-485), <a href="#">Figure 1</a>     | Full                  | 1.5  | 2.3  | 5               | V    |    |
| Change in Magnitude of Driver Differential V <sub>OUT</sub> for Complementary Output States | ΔV <sub>OD</sub> | R = 27Ω or 50Ω, <a href="#">Figure 1</a>       | Full                  | -    | 0.01 | 0.2             | V    |    |
| Driver Common-Mode V <sub>OUT</sub>                                                         | V <sub>OC</sub>  | R = 27Ω or 50Ω, <a href="#">Figure 1</a>       | Full                  | -    | -    | 3               | V    |    |
| Change in Magnitude of Driver Common-Mode V <sub>OUT</sub> for Complementary Output States  | ΔV <sub>OC</sub> | R = 27Ω or 50Ω, <a href="#">Figure 1</a>       | Full                  | -    | 0.01 | 0.2             | V    |    |
| Logic Input High Voltage                                                                    | V <sub>IH</sub>  | DE, DI, $\overline{RE}$                        | Full                  | 2    | -    | -               | V    |    |
| Logic Input Low Voltage                                                                     | V <sub>IL</sub>  | DE, DI, $\overline{RE}$                        | Full                  | -    | -    | 0.8             | V    |    |
| Logic Input Current                                                                         | I <sub>IN1</sub> | DI (ISL8485, ISL8490, ISL8491)                 | Full                  | -2   | -    | 2               | μA   |    |
|                                                                                             | I <sub>IN1</sub> | DE, $\overline{RE}$ (ISL8485, ISL8491)         | Full                  | -25  | -    | 25              | μA   |    |
| Input Current (A, B), <a href="#">Note 10</a>                                               | I <sub>IN2</sub> | DE = 0V, V <sub>CC</sub> = 0V or 4.5 to 5.5V   | V <sub>IN</sub> = 12V | Full | -    | -               | 1    | mA |
|                                                                                             |                  |                                                | V <sub>IN</sub> = -7V | Full | -    | -               | -0.8 | mA |
| Receiver Differential Threshold Voltage                                                     | V <sub>TH</sub>  | -7V ≤ V <sub>CM</sub> ≤ 12V                    | Full                  | -0.2 | -    | 0.2             | V    |    |
| Receiver Input Hysteresis                                                                   | ΔV <sub>TH</sub> | V <sub>CM</sub> = 0V                           | 25                    | -    | 70   | -               | mV   |    |
| Receiver Output High Voltage                                                                | V <sub>OH</sub>  | I <sub>O</sub> = -4mA, V <sub>ID</sub> = 200mV | Full                  | 3.5  | -    | -               | V    |    |
| Receiver Output Low Voltage                                                                 | V <sub>OL</sub>  | I <sub>O</sub> = -4mA, V <sub>ID</sub> = 200mV | Full                  | -    | -    | 0.4             | V    |    |
| Three-State (high impedance) Receiver Output Current                                        | I <sub>OZR</sub> | 0.4V ≤ V <sub>O</sub> ≤ 2.4V                   | Full                  | -    | -    | ±1              | μA   |    |
| Receiver Input Resistance                                                                   | R <sub>IN</sub>  | -7V ≤ V <sub>CM</sub> ≤ 12V                    | Full                  | 12   | -    | -               | kΩ   |    |

# Electrical Specifications

Test Conditions:  $V_{CC} = 4.5V$  to  $5.5V$ ; unless otherwise specified. Typical values are at  $V_{CC} = 5V$ ,  $T_A = +25^{\circ}C$ , [Note 7](#) (Continued)

| PARAMETER                                                    | SYMBOL             | TEST CONDITIONS                                                           | TEMP (°C) | MIN | TYP | MAX | UNIT    |
|--------------------------------------------------------------|--------------------|---------------------------------------------------------------------------|-----------|-----|-----|-----|---------|
| No-Load Supply Current, <a href="#">Note 8</a>               | $I_{CC}$           | ISL8490, ISL8491, DE, DI, $\overline{RE} = 0V$ or $V_{CC}$                | Full      | -   | 500 | 565 | $\mu A$ |
|                                                              |                    | ISL8485, DI, $\overline{RE} = 0V$ or $V_{CC}$                             | Full      | -   | 700 | 900 | $\mu A$ |
|                                                              |                    |                                                                           | Full      | -   | 500 | 565 | $\mu A$ |
| Driver Short-Circuit Current, $V_O = \text{High or Low}$     | $I_{OSD1}$         | DE = $V_{CC}$ , $-7V \leq V_Y$ or $V_Z \leq 12V$ , <a href="#">Note 9</a> | Full      | 35  | -   | 250 | mA      |
| Receiver Short-Circuit Current                               | $I_{OSR}$          | $0V \leq V_O \leq V_{CC}$                                                 | Full      | 7   | -   | 85  | mA      |
| <b>SWITCHING CHARACTERISTICS (ISL8485, ISL8490, ISL8491)</b> |                    |                                                                           |           |     |     |     |         |
| Driver Input to Output Delay                                 | $t_{PLH}, t_{PHL}$ | $R_{DIFF} = 54\Omega$ , $C_L = 100pF$ , <a href="#">Figure 2</a>          | Full      | 18  | 30  | 50  | ns      |
| Driver Output Skew                                           | $t_{SKEW}$         | $R_{DIFF} = 54\Omega$ , $C_L = 100pF$ , <a href="#">Figure 2</a>          | Full      | -   | 2   | 10  | ns      |
| Driver Differential Rise or Fall Time                        | $t_R, t_F$         | $R_{DIFF} = 54\Omega$ , $C_L = 100pF$ , <a href="#">Figure 2</a>          | Full      | 3   | 11  | 25  | ns      |
| Driver Enable to Output High                                 | $t_{ZH}$           | $C_L = 100pF$ , SW = GND, <a href="#">Figure 3</a>                        | Full      | -   | 17  | 70  | ns      |
| Driver Enable to Output Low                                  | $t_{ZL}$           | $C_L = 100pF$ , SW = $V_{CC}$ , <a href="#">Figure 3</a>                  | Full      | -   | 14  | 70  | ns      |
| Driver Disable from Output High                              | $t_{HZ}$           | $C_L = 15pF$ , SW = GND, <a href="#">Figure 3</a>                         | Full      | -   | 19  | 70  | ns      |
| Driver Disable from Output Low                               | $t_{LZ}$           | $C_L = 15pF$ , SW = $V_{CC}$ , <a href="#">Figure 3</a>                   | Full      | -   | 13  | 70  | ns      |
| Receiver Input to Output Delay                               | $t_{PLH}, t_{PHL}$ | <a href="#">Figure 4</a>                                                  | Full      | 30  | 40  | 150 | ns      |
| Receiver Skew   $t_{PLH} - t_{PHL}$                          | $t_{SKD}$          | <a href="#">Figure 4</a>                                                  | 25        | -   | 5   | -   | ns      |
| Receiver Enable to Output High                               | $t_{ZH}$           | $C_L = 15pF$ , SW = GND, <a href="#">Figure 5</a>                         | Full      | -   | 9   | 50  | ns      |
| Receiver Enable to Output Low                                | $t_{ZL}$           | $C_L = 15pF$ , SW = $V_{CC}$ , <a href="#">Figure 5</a>                   | Full      | -   | 9   | 50  | ns      |
| Receiver Disable from Output High                            | $t_{HZ}$           | $C_L = 15pF$ , SW = GND, <a href="#">Figure 5</a>                         | Full      | -   | 9   | 50  | ns      |
| Receiver Disable from Output Low                             | $t_{LZ}$           | $C_L = 15pF$ , SW = $V_{CC}$ , <a href="#">Figure 5</a>                   | Full      | -   | 9   | 50  | ns      |
| Maximum Data Rate                                            | $f_{MAX}$          | <a href="#">Note 11</a>                                                   | Full      | 5   | -   | -   | Mbps    |

## NOTES:

- All currents into device pins are positive; all currents out of device pins are negative. All voltages are referenced to device ground unless otherwise specified.
- Supply current specification is valid for loaded drivers when DE = 0V.
- Applies to peak current. See ["Typical Performance Curves" on page 10](#) for more information.
- Devices meeting these limits are denoted as "single unit load (1 UL)" transceivers. The RS-485 standard allows up to 32 unit loads on the bus.
- Ensured by characterization, but not tested.

Test Circuits and Waveforms




FIGURE 1. DRIVER V<sub>OD</sub> AND V<sub>OC</sub>




FIGURE 2A. TEST CIRCUIT




FIGURE 2B. MEASUREMENT POINTS

FIGURE 2. DRIVER PROPAGATION DELAY AND DIFFERENTIAL TRANSITION TIMES

Test Circuits and Waveforms (Continued)




FIGURE 3A. TEST CIRCUIT




FIGURE 3B. MEASUREMENT POINTS

FIGURE 3. DRIVER ENABLE AND DISABLE TIMES (EXCLUDING ISL8490)




FIGURE 4A. TEST CIRCUIT




FIGURE 4B. MEASUREMENT POINTS

FIGURE 4. RECEIVER PROPAGATION DELAY




FIGURE 5A. TEST CIRCUIT




FIGURE 5B. MEASUREMENT POINTS

FIGURE 5. RECEIVER ENABLE AND DISABLE TIMES (EXCLUDING ISL8490)

## Application Information

RS-485 and RS-422 are differential (balanced) data transmission standards for use in long haul or noisy environments. RS-422 is a subset of RS-485, so RS-485 transceivers are also RS-422 compliant. RS-422 is a point-to-multipoint (multidrop) standard, which allows only one driver and up to 10 receivers on each bus, assuming one unit load devices. RS-485 is a true multipoint standard, which allows up to 32 one unit load devices (any combination of drivers and receivers) on each bus. To allow multipoint operation, the RS-485 specification requires that drivers must handle bus contention without sustaining any damage.

An important advantage of RS-485 is the extended Common-Mode Range (CMR), which specifies that the driver outputs and receiver inputs withstand signals that range from +12V to -7V. RS-422 and RS-485 are intended for runs as long as 4000ft, so the wide CMR is necessary to handle ground potential differences, as well as voltages induced in the cable by external fields.

### Receiver Features

These devices use a differential input receiver for maximum noise immunity and common-mode rejection. Input sensitivity is  $\pm 200\text{mV}$ , as required by the RS-422 and RS-485 specifications.

Receiver input impedance surpasses the RS-422 specification of  $4\text{k}\Omega$ , and meets the RS-485 unit load requirement of  $12\text{k}\Omega$  minimum.

Receiver inputs function with common-mode voltages as great as  $\pm 7\text{V}$  outside the power supplies (+12V and -7V), making them ideal for long networks in which induced voltages are a realistic concern.

All the receivers include a “fail-safe if open” function that ensures a high level receiver output if the receiver inputs are unconnected (floating).

Receivers easily meet the data rates supported by the corresponding driver.

The ISL8485 and ISL8491 receiver outputs are three-statable using the active low  $\overline{\text{RE}}$  input.

### Driver Features

The RS-485/RS-422 driver is a differential output device that delivers at least 1.5V across a  $54\Omega$  load (RS-485), and at least 2V across a  $100\Omega$  load (RS-422). The drivers feature low propagation delay skew to maximize bit width and to minimize EMI.

The ISL8485 and ISL8491 drivers are three-statable using the active high DE input.

The ISL8485 and ISL8491 driver outputs are not limited, so faster output transition times allow data rates of at least 5Mbps.

## Data Rate, Cables, and Terminations

RS-485/RS-422 are intended for network lengths up to 4000ft, but the maximum system data rate decreases as the transmission length increases. Devices operating at 5Mbps are limited to lengths less than 100ft.

Twisted pair cable is the cable of choice for RS-485/422 networks. Twisted pair cables tend to pick up noise and other electromagnetically induced voltages as common-mode signals, which are effectively rejected by the differential receivers in these ICs.

Proper termination is imperative to minimize reflections when using the 5Mbps devices.

In point-to-point networks or point-to-multipoint (single driver on bus) networks, terminate the main cable in its characteristic impedance (typically  $120\Omega$ ) at the end farthest from the driver. In multi-receiver applications, stubs connecting receivers to the main cable should be kept as short as possible. In multipoint (multi-driver) systems, terminate the main cable in its characteristic impedance at both ends. Keep stubs connecting a transceiver to the main cable as short as possible.

### Built-In Driver Overload Protection

The RS-485 specification requires that drivers survive worst case bus contentions undamaged. The ISL84XX devices meet this requirement using driver output short circuit current limits and on-chip thermal shutdown circuitry.

The driver output stages incorporate short-circuit current limiting circuitry that ensures the output current never exceeds the RS-485 specification, even at the common-mode voltage range extremes. These devices also use a foldback circuit that reduces the short-circuit current, and thus the power dissipation, whenever the contending voltage exceeds either supply.

In the event of a major short-circuit condition, the ISL84XX devices' thermal shutdown feature disables the drivers whenever the die temperature becomes excessive. This eliminates the power dissipation, allowing the die to cool. The drivers automatically re-enable after the die temperature drops about  $15^{\circ}\text{C}$ . If the condition persists, the thermal shutdown/re-enable cycle repeats until the fault is cleared. Receivers stay operational during thermal shutdown.

**Typical Performance Curves**  $V_{CC} = 5V$ ,  $T_A = 25^\circ C$ , ISL8485, ISL8490, ISL8491; unless otherwise specified




FIGURE 6. DRIVER OUTPUT CURRENT vs DIFFERENTIAL OUTPUT VOLTAGE




FIGURE 7. DRIVER DIFFERENTIAL OUTPUT VOLTAGE vs TEMPERATURE




FIGURE 8. DRIVER OUTPUT CURRENT vs SHORT CIRCUIT VOLTAGE




FIGURE 9. SUPPLY CURRENT vs TEMPERATURE




FIGURE 10. DRIVER PROPAGATION DELAY vs TEMPERATURE




FIGURE 11. DRIVER SKEW vs TEMPERATURE


**Typical Performance Curves**  $V_{CC} = 5V$ ,  $T_A = 25^\circ C$ , ISL8485, ISL8490, ISL8491; unless otherwise specified (Continued)


FIGURE 12. DRIVER AND RECEIVER WAVEFORMS, LOW TO HIGH




FIGURE 13. DRIVER AND RECEIVER WAVEFORMS, HIGH TO LOW

**Die Characteristics**

SUBSTRATE POTENTIAL (POWERED UP):

GND

TRANSISTOR COUNT:

518

PROCESS:

Si Gate CMOS


## Revision History

The revision history provided is for informational purposes only and is believed to be accurate, but not warranted. Please visit our website to make sure that you have the latest revision.

| DATE         | REVISION | CHANGE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|--------------|----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Oct 2, 2023  | 10.02    | Updated POD M8.15 to the latest version (corrected typo).                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Oct 14, 2021 | 10.01    | Fixed the formatting on Ordering table.<br>Removed Related Literature section.<br>Updated POD M8.15 to the latest version, changes are as follows:<br>-Added the coplanarity spec into the drawing.<br>Updated POD M14.15 to the latest version, changes are as follows:<br>-Added lead length dimension (1.27 – 0.40)<br>-Changed angle of the lead to 0-8 degrees.                                                                                                                                                                                                                       |
| Oct 18, 2018 | 10.00    | Removed ISL8483, ISL8488, and ISL8489 information from the datasheet.<br>Updated Typical Operating Circuits on page 2.<br>Updated Features bullets on page 1.<br>Added Related Literature section to page 1.<br>Updated Ordering Information table on page 3:<br>-Added Tape and Reel column.<br>-Added information about replacements for the ISL8485CPZ and ISL8485IPZ.<br>Removed About Intersil section and updated Renesas disclaimer.                                                                                                                                                |
| Feb 16, 2016 | 9.00     | Added Rev History and About Intersil verbiage.<br>Updated "Ordering Information" table on page 3.<br><br>Updated following PODs to current revisions listing POD updates:<br><b>POD M8.15:</b><br>Updated to new POD format by removing table and moving dimensions onto drawing and adding land pattern<br>Changed in Typical Recommended Land Pattern the following:<br>2.41(0.095) to 2.20(0.087)<br>0.76 (0.030) to 0.60(0.023)<br>0.200 to 5.20(0.205)<br>Changed Note 1 "1982" to "1994"<br><br><b>POD M14.15</b><br>Added land pattern and moved dimensions from table onto drawing |

## Package Outline Drawings

For the most recent package outline drawing, see [E8.3](#).



### NOTES:

- Controlling Dimensions: INCH. In case of conflict between English and Metric dimensions, the inch dimensions control.
- Dimensioning and tolerancing per ANSI Y14.5M-1982.
- Symbols are defined in the "MO Series Symbol List" in Section 2.2 of Publication No. 95.
- Dimensions A, A1 and L are measured with the package seated in JEDEC seating plane gauge GS-3.
- D, D1, and E1 dimensions do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.010 inch (0.25mm).
- E and  $e_A$  are measured with the leads constrained to be perpendicular to datum  $-C-$ .
- $e_B$  and  $e_C$  are measured at the lead tips with the leads unconstrained.  $e_C$  must be zero or greater.
- B1 maximum dimensions do not include dambar protrusions. Dambar protrusions shall not exceed 0.010 inch (0.25mm).
- N is the maximum number of terminal positions.
- Corner leads (1, N, N/2 and N/2 + 1) for E8.3, E16.3, E18.3, E28.3, E42.6 will have a B1 dimension of 0.030 - 0.045 inch (0.76 - 1.14mm).

E8.3 (JEDEC MS-001-BA ISSUE D)  
8 LEAD DUAL-IN-LINE PLASTIC PACKAGE (PDIP)

| SYMBOL | INCHES    |       | MILLIMETERS |       | NOTES |
|--------|-----------|-------|-------------|-------|-------|
|        | MIN       | MAX   | MIN         | MAX   |       |
| A      | -         | 0.210 | -           | 5.33  | 4     |
| A1     | 0.015     | -     | 0.39        | -     | 4     |
| A2     | 0.115     | 0.195 | 2.93        | 4.95  | -     |
| B      | 0.014     | 0.022 | 0.356       | 0.558 | -     |
| B1     | 0.045     | 0.070 | 1.15        | 1.77  | 8, 10 |
| C      | 0.008     | 0.014 | 0.204       | 0.355 | -     |
| D      | 0.355     | 0.400 | 9.01        | 10.16 | 5     |
| D1     | 0.005     | -     | 0.13        | -     | 5     |
| E      | 0.300     | 0.325 | 7.62        | 8.25  | 6     |
| E1     | 0.240     | 0.280 | 6.10        | 7.11  | 5     |
| e      | 0.100 BSC |       | 2.54 BSC    |       | -     |
| $e_A$  | 0.300 BSC |       | 7.62 BSC    |       | 6     |
| $e_B$  | -         | 0.430 | -           | 10.92 | 7     |
| L      | 0.115     | 0.150 | 2.93        | 3.81  | 4     |
| N      | 8         |       | 8           |       | 9     |


Rev. 0 12/93

For the most recent package outline drawing, see [M8.15](#).

M8.15

8 Lead Narrow Body Small Outline Plastic Package

Rev 7, 9/2023



Notes:



1. Dimensioning and tolerancing conform to ASME Y14.5M-1994.
2. Package length does not include mold flash, protrusion or gate burrs. Mold flash, protrusion and gate burrs shall not exceed 0.15mm (0.006 inch) per side.
3. Package width does not include interlead flash or protrusions. Interlead flash and protrusions shall not exceed 0.25mm (0.010 inch) per side.
4. The chamfer on the body is optional. If it is not present, a visual index feature must be located within the crosshatched area.
5. Terminal numbers are shown for reference only.
6. The lead width as measured 0.36mm (0.014 inch) or greater above the seating plane, shall not exceed a maximum value of 0.61mm (0.024 inch).
7. Controlling dimension: MILLIMETER. Converted inch dimension are not necessarily exact.
8. This outline conforms to JEDEC publication MS-012-AA ISSUE C.

For the most recent package outline drawing, see [M14.15](#).

M14.15

14 Lead Narrow Body Small Outline Plastic Package

Rev 2, 6/20



Typical Recommended Land Pattern

Notes:

1. Dimensions are in millimeters.  
Dimensions in ( ) for reference only.
2. Dimensioning and tolerancing conform to ASME Y14.5m-1994.
3. Datums A and B are determined at Datum H.
4. Dimension does not include interlead flash or protrusions.  
Interlead flash or protrusions shall not exceed 0.25mm per side.
5. The pin #1 identifier can be either a mold or mark feature.
6. Does not include dambar protrusion. Allowable dambar protrusion shall be 0.10mm total in excess of lead width at maximum condition.
7. Reference to JEDEC MS-012-AB.

## IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers skilled in the art designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only for development of an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising out of your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.0 Mar 2020)

### Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,  
Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

### Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:  
[www.renesas.com/contact/](http://www.renesas.com/contact/)

### Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.