



SAW Components

Datasheet B9014

Data Sheet

An abstract graphic featuring the word "EPCOS" in large, glowing, 3D letters. The letters are white with a blue glow and are positioned diagonally across the frame. In the background, there is a faint, stylized globe with circuitry patterns, suggesting a global network or technological theme. The overall color scheme is dark with blue and white highlights.



SAW Components

B9014

Low-Loss Filter for Mobile Communication

1880,0 MHz

Datasheet




Chip Sized SAW Package DCS4G

Features

- Low-loss RF filter for mobile telephone PCS systems, transmit path
- High selectivity
- Usable passband 60 MHz
- Unbalanced to unbalanced operation
- No external matching required
- Package for Surface Mounted Technology (SMT)

Terminals


- Gold-plated Ni



Dimensions in mm, approx weight 0,007g

Pin configuration

- 1 Input
- 3 Output
- 2, 4 To be grounded



Type	Ordering code	Marking and Package according to	Packing according to
B9014	B39192-B9014-E910	C61157-A7-A105	F61074-V8152-Z000

Electrostatic Sensitive Device (ESD)

Maximum ratings

Operable temperature range	T	- 30 /+ 85	°C	source impedance 50 Ω
Storage temperature range	T_{stg}	- 40 /+ 85	°C	
Input Power max.	P_{IN}	15	dBm	machine model, 10 pulses
DC voltage	V_{DC}	5	V	
ESD voltage	V_{ESD}^*	50*	V	

* acc. to JEESD22-A115A (Machine Model), 10 negative & 10 positive pulses



SAW Components

B9014

Low-Loss Filter for Mobile Communication

1880,0 MHz

Datasheet



Characteristics

Operating Temperature Range: $T = 25 \pm 2^\circ\text{C}$
Terminating source impedance: $Z_S = 50\ \Omega$
Terminating load impedance: $Z_L = 50\ \Omega$

		min.	typ.	max.	
Center frequency	f_C	—	1880,0	—	MHz
Maximum insertion attenuation 1850,0 ... 1910,0MHz	$\alpha_{\max}$	—	2,3	2,9	dB
Amplitude ripple (p-p) 1850,0 ... 1910,0MHz	$\Delta\alpha$	—	0,9	1,5	dB
Attenuation	α				
DC ... 1550,0MHz		32	34	—	dB
1550,0 ... 1580,0MHz		35	39	—	dB
1580,0 ... 1770,0MHz		30	35	—	dB
1770,0 ... 1830,0MHz		21	24	—	dB
1930,0 ... 1990,0MHz		35	45 ¹⁾	—	dB
1990,0 ... 2032,0MHz		35	41	—	dB
2032,0 ... 2500,0MHz		35	42	—	dB
2500,0 ... 3820,0MHz		25	28	—	dB
3820,0 ... 6000,0MHz		15	19	—	dB
Input return loss 1850,0 ... 1910,0MHz		8	10	—	dB
Output return loss 1850,0 .. 1910,0MHz		8	10	—	dB

¹⁾ Valid for frequencies from 1935 MHz to 1990 MHz



SAW Components

B9014

Low-Loss Filter for Mobile Communication

1880,0 MHz

Datasheet



Characteristics

Operating Temperature Range: $T = -30$ to $+85^{\circ}\text{C}$
Terminating source impedance: $Z_S = 50\ \Omega$
Terminating load impedance: $Z_L = 50\ \Omega$

		min.	typ.	max.	
Center frequency	f_C	—	1880,0	—	MHz
Maximum insertion attenuation 1850,625 ... 1909,375MHz	$\alpha_{\max}$	—	3,3 ¹⁾	3,9 ¹⁾	dB
Amplitude ripple (p-p) 1850,625 ... 1909,375MHz	$\Delta\alpha$	—	2,0	2,5	dB
Attenuation	α				
DC ... 1550,0MHz		32	34	—	dB
1550,0 ... 1580,0MHz		35	39	—	dB
1580,0 ... 1770,0MHz		30	35	—	dB
1770,0 ... 1830,0MHz		14	20	—	dB
1930,625 ... 1989,375MHz		32	45 ²⁾	—	dB
1990,0 ... 2032,0MHz		35	41	—	dB
2032,0 ... 2500,0MHz		35	42	—	dB
2500,0 ... 3820,0MHz		25	28	—	dB
3820,0 ... 6000,0MHz		15	19	—	dB
Input return loss 1850,625 ... 1909,375MHz		7	10	—	dB
Output return loss 1850,625 ... 1909,375MHz		7	10	—	dB

¹⁾ Valid in temperature range -30°C to $+75^{\circ}\text{C}$. Guaranteed for $+85^{\circ}\text{C}$: 4,2dB

²⁾ Valid for frequencies from 1935 MHz to 1990 MHz



SAW Components

B9014



Low-Loss Filter for Mobile Communication

1880,0 MHz

Datasheet



Transfer Function (Specification for T=25°C)





SAW Components	B9014
Low-Loss Filter for Mobile Communication	1880,0 MHz
Datasheet	SMD

Published by EPCOS AG

Surface Acoustic Wave Components Division, SAW MC WT

P.O. Box 80 17 09, D-81617 München

© EPCOS AG 2004. All Rights Reserved. Reproduction, publication and dissemination of this brochure and the information contained therein without EPCOS' prior express consent is prohibited.

The information contained in this brochure describes the type of component and shall not be considered as guaranteed characteristics. Purchase orders are subject to the General Conditions for the Supply of Products and Services of the Electrical and Electronics Industry recommended by the ZVEI (German Electrical and Electronic Manufacturers' Association), unless otherwise agreed.

This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.