


Pulse Withstanding Chip Resistors

PWC Series

- Excellent pulse withstand performance
- Improved working voltage
- Improved power rating
- Standard chip sizes (0805 to 2512)
- Custom designs available
- Anti-sulphur version available




Electrical Data

Size		0805	1206		2010		2512	
Power @70°C	W	0.125	0.33	0.5	0.75	1	1.5	2
Resistance range	Ohms	1R0 to 10M						
Tolerance	%	10R to 1M: 0.5, All values: 1, 5						
LEV	V	150	200		400		500	
TCR	ppm/°C	<10R:200 ≥10R:100						
Operating temperature	°C	-55 to +155						
Thermal Impedance	°C/W	220	160	145	80	70	55	40
Pad / trace area *	mm²	40	50	125	60	250	100	500
Values		E96 preferred - other values to special order						
Pulse Capability		See graphs – full application note available on request						

*Recommended minimum pad & adjacent trace area for each termination for rated power dissipation on FR4 PCB

Physical Data

Dimensions of PWC resistors are given below in mm and weight in g							
	L	W	T max	A	B	C	Wt.
0805	2.0±0.3	1.25±0.2	0.6	0.3±0.15	0.9 min	0.3±0.1	0.009
1206	3.2±0.4	1.6±0.2	0.7	0.4±0.2	1.7 min	0.4±0.15	0.020
2010	5.1±0.3	2.5±0.2	0.8	0.6±0.3	3.0 min	0.6±0.25	0.036
2512	6.5±0.3	3.2±0.2	0.8	0.6±0.3	4.4 min	0.6±0.25	0.055



Construction

Thick film resistor material, overglaze and organic protection are screen printed on a 96% alumina substrate. Wrap-around terminations have an electroplated nickel barrier and solder coating, this ensures excellent 'leach' resistance properties and solderability.

Note that anti-sulphur version parts below 100R are produced in flip-chip format with the resistor element on the underside.

Marking

Components are not marked. Reels are marked with type, value, tolerance, date code and quantity.

Solvent Resistance

The body protection is resistant to all normal industrial cleaning solvents suitable for printed circuits.

General Note

TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.

Performance Data



Size		Maximum	Typical
Load at rated power: 1000 hours at 70°C	ΔR%	1	0.25
Shelf life test: 12 months at room temperature	ΔR%	0.1	0.02
Derating from rated power at 70°C		Zero at 155°C	
Overload: 6.25 x rated power for 2 seconds	ΔR%	1	0.1
Dry heat: 1000 hours at 155°C	ΔR%	1	0.2
Long term damp heat	ΔR%	1	0.25
Temperature rapid change	ΔR%	0.25	0.05
Resistance to solder heat	ΔR%	0.25	0.05
Resistance to sulphur-bearing gas (AS version only): ASTM-B-809		0.25	0.05
Voltage proof	Volts	500	

Note: A 0.01 Ohm addition to be added to the performance of all resistors <10 Ohms.

Pulse Performance Data

Lightning Surge

lightning surge resistors are tested in accordance with IEC 60 115-1 using both 1.2/50μs and 10/700μs pulse shapes. 10 pulses are applied. The limit of acceptance is a shift in resistance of less than 1% from the initial value.



General Note

TT electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT electronics' own data and is considered accurate at time of going to print.




Pulse Performance Data

Single Impulse

The single impulse graph is the result of 50 impulses of rectangular shape applied at one minute intervals. The limit of acceptance was a shift in resistance of less than 1% from the initial value.

Continuous Load Due to Repetitive Pulses


The continuous load graph was obtained by applying repetitive rectangular pulses where the pulse period was adjusted so that the average power dissipated in the resistor was equal to its rated power at 70°C. Again the limit of acceptance was a shift in resistance of less than 1% from the initial value.



General Note

TT electronics reserves the right to make changes in product specification without notice or liability.
All information is subject to TT electronics' own data and is considered accurate at time of going to print.

Thermal Performance Data



Packaging

0805 and 1206 PWC series resistors are supplied on 8mm carrier tape and 7 inch reels as per IEC 286-3, quantity per reel; 3000. 2010 and 2512 PWC series resistors are supplied on 12mm carrier tape and 7 inch reels as per IEC 286-3, quantity per reel; 2010 : 3000pcs; 2512 : 1800pcs.

Reels of 1000pcs are available on request.

Application Notes

PWC resistors are ideally suited for handling by automatic methods due to their rectangular shape and the small dimensional tolerances. Electrical connection to a ceramic substrate or to a printed circuit board can be made by reflow or wave soldering of wrap-around terminations.

Wrap-around terminations provide good leach properties and ensure reliable contact. Due to the robust construction, the PWC can be immersed in the solder bath for 30 seconds at 260°C. This enables the resistor to be mounted on one side of a printed circuit board and wire-leaded components applied on the other side.

PWC resistors themselves can operate at a maximum temperature of 155°C. For soldered resistors, the joint temperature should not exceed 110°C. This condition is met when the stated power levels at 70°C and recommended pad and trace areas are used. Allowance should be made if smaller areas of copper are used.

A full Application Note on the PWC Series is available.

Ordering Procedure

Example: PWC2512 at 2.0 kilohms and 5% tolerance on a reel of 1800 pieces -

Type	PWC	2512	2K0	J	I											
Size																
Termination																
	<table><tr><td></td><td>Standard terminations</td></tr><tr><td>AS</td><td>Anti-sulphur terminations</td></tr></table>						Standard terminations	AS	Anti-sulphur terminations							
	Standard terminations															
AS	Anti-sulphur terminations															
Value (use IEC62 code)																
Tolerance (use IEC62 code)																
	<table><tr><td>D</td><td>0.5%</td></tr><tr><td>F</td><td>1%</td></tr></table>	D	0.5%	F	1%	J	5%									
D	0.5%															
F	1%															
Packing.....																
	<table><tr><td>I</td><td>Tape</td><td>0805, 1206 or 2010</td><td>3000/reel</td><td rowspan="3">Standard</td></tr><tr><td></td><td></td><td>2512</td><td>1800/reel</td></tr><tr><td>T1</td><td></td><td>All sizes</td><td>1000/reel</td></tr></table>	I	Tape	0805, 1206 or 2010	3000/reel	Standard			2512	1800/reel	T1		All sizes	1000/reel		
I	Tape	0805, 1206 or 2010	3000/reel	Standard												
		2512	1800/reel													
T1		All sizes	1000/reel													

General Note

TT electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT electronics' own data and is considered accurate at time of going to print.