

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECO-12-006972	23AUG2012	KH	JE

- 2

PHOSPHOR BRONZE
- 3

GLASS FILLED POLYESTER
- 4

FINISH:
CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER BASE PLATING.
- 5

CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6




REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 7

APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD
- 8



DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 9

CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- 10

HOLE DIAMETER SHOULD BE 3.10 WHEN USING FEED THROUGH GUIDE PIN P/N 120759
CLEARANCE FOR A M3x0.5 THREAD



RECOMMENDED
PRINTED CIRCUIT BOARD
LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD



5.50	9.7	5120678-2
5.50	8.2	5120678-1
M	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO	07DEC04	NAME B. CARBO	
DIMENSIONS:		CHK R. PATTERSON	07DEC04		
mm		APVD R. PATTERSON	07DEC04	PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		RESTRICTED TO	
0 PLC ±		WEIGHT		SIZE	
1 PLC ±		CAGE CODE		DRAWING NO	
2 PLC ±0.13		A1		00779	
3 PLC ±0.05		CUSTOMER DRAWING		©=5120678	
4 PLC ±		SCALE		5:1	
ANGLES ±		SHEET		1	
FINISH		OF		1	
MATERIAL		REV		B	
HOUSING: 3					
CONTACTS: 2					
SIGNAL CONTACT: 4					