



3.4 mini threaded length

PC board drilling dimensions (after plating)
(thickness ≤ 3.20 ± 0.30mm)



SHELL	A ± 0.38	B ± 0.12	C ± 0.10	DH ± 0.25	E ± 0.07	TIN LEAD	TIN LEAD	TIN LEAD	LEAD FREE	LEAD FREE	LEAD FREE
PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S90C6G*00L	D09S90C6G*00L	D09S90C6G*00L	D09S90C6G*00L	D09S90C6G*00L	D09S90C6G*00L
15	39.14	33.32	25.18	24.54	19.18	D15S90C6G*00L	D15S90C6G*00L	D15S90C6G*00L	D15S90C6G*00L	D15S90C6G*00L	D15S90C6G*00L
25	53.03	47.04	39.12	38.25	33.12	D25S90C6G*00L	D25S90C6G*00L	D25S90C6G*00L	D25S90C6G*00L	D25S90C6G*00L	D25S90C6G*00L
37	69.32	63.50	55.68	54.71	49.68	D37S90C6G*00L	D37S90C6G*00L	D37S90C6G*00L	D37S90C6G*00L	D37S90C6G*00L	D37S90C6G*00L
						gold flash	0.76µ gold	1.27µ gold	gold flash	0.76µ gold	1.25µ gold

Threaded ØT M3 = L
Threaded ØT 4.40 = X

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

SEE DRAWING C01-8646-0001										European Views																				
www.fciconnect.com					surface			tolerance std			projection		 mm																	
					150 1302			150 406 150 1101																						
					TOLERANCES UNLESS OTHERWISE SPECIFIED																									
Dr		JARRY	1994/09/21		ANGULAR			0.X			±0.1			size		A3		Scale		2										
Eng		JARRY	1994/09/21		LINEAR			0.XX			±0.1																			
Chr		-	-		0.X' ±2'			0.XXX			±0.1			ECN		LS08-0226														
Appr		LEGARE	1994/09/21		Product family										D-SUB		Spec ref		-											
					FEMALE CONNECTOR DELTA LOW										oz		C01-8646-0310										Rev.		J	
					PROFIL STRAIGHT PRESS-FIT										oz															
					catalog no										-		CUSTOMER										sheet		1 of 1	



FEMALE CONNECTOR DELTA LOW
PROFIL STRAIGHT PRESS-FIT

rev	ech no	dr	date
E	-	ATC	2000/12/22
F	L505-004	LMA	2005/01/12
G	L506-0097	L60	2006/07/29
H	L506-0140	L60	2006/09/22
J	L508-0226	MPE	2008/12/09
-	-	-	-
-	-	-	-