

**General ordering data**

Order No.	1896110000
Part designation	PDU 2.5/4
Version	Feed-through terminal, 4 mm ² , Push-In, Wemid, dark beige, TS 35
EAN	4032248511150
Qty.	100 pc(s).

Product notes

Note, ordering data	For use with 4 mm ² conductors, with wire-end ferrules and cross-section-optimized plastic collars (order no. 9203630000)
Note, technical data	4 mm ² conductors should be processed after crimp, in compliance with Euro-Norm EN 60947-1, for example with the PZ6/5 (order no. 9011460000).
Note, accessories	Detailed information for working with twin ferrules can be found in the P Series Accessories section.

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA06ATEX0177U
Download, German	KEMA06ATEX0177U_d.pdf
Download English	KEMA06ATEX0177U_e.pdf
IECEX Certificate of Conformity	IECEXKEM06.0032U
Download	IECEXKEM06.0032U_e.pdf
ATEX voltage	550 V
ATEX current	29 A
ATEX conductor cross-section	4 mm ²
IECEX voltage	550 V
IECEX current	29 A
IECEX conductor cross-section	4 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEX-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	dark beige
Connection direction	top
End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No
No. of levels	1
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Type of connection	Plugged
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0
Version	Feed-through terminal

Conductors for clamping (rated connection)

Clamping range, min.	0.13 mm²
Clamping range, max.	6 mm²
Type of connection	Push-In
Connection direction	top
Stripping length	12 mm
Blade size	3.0 x 0.5 mm
Solid, min.	0.5 mm²
Solid, max.	6 mm²
Flexible, min.	0.5 mm²
Flexible, max.	4 mm²
Flexible, min.	0.21 mm²
Flexible, max.	4 mm²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm²
Flexible with ferrule, max. (DIN 46228/1)	4 mm²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	2.5 mm²
Twin wire-end ferrule, min.	0.5 mm²
Twin wire end ferrule, max.	2.5 mm²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 10

Dimensions

Width	5.1 mm
Height of lowest version	38 mm
Length	53 mm
TS 35 offset	26 mm

Rating data

Rated cross-section	4 mm²
Rated voltage	800 V
Rated impulse voltage	8 kV
Rated current	32 A

Rating data

Standards	IEC 60947-7-1
Pollution severity	3

Approvals

Approvals institutes

**Downloads**

STEP	1896110000_41628_PDU_2.5_4_2AN_STP.stp
------	--

Classifications

eClass 4.1	27-14-11-20
eClass 5.0	27-14-11-20
eClass 5.1	27-14-11-20

Similar products

Order No.	Part designation	Version
1896120000	PDU 2.5/4/3AN	Feed-through terminal, 4 mm ² , Push-In, Wemid, dark beige, TS 35
1896240000	PDU 2.5/4/3AN BL	Feed-through terminal, 4 mm ² , Push-In, Wemid, blue, TS 35
1896130000	PDU 2.5/4/4AN	Feed-through terminal, 4 mm ² , Push-In, Wemid, dark beige, TS 35
1896250000	PDU 2.5/4/4AN BL	Feed-through terminal, 4 mm ² , Push-In, Wemid, blue, TS 35
1896230000	PDU 2.5/4 BL	Feed-through terminal, 4 mm ² , Push-In, Wemid, blue, TS 35