

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191930151

Status:

Active

Description:

VersaKrimp™ Ring Tongue Terminal for 8 AWG Wire, Stud Size 10, Mylar Tape Carrier

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Ring and Spade Terminals
Series	19193
Mil-Spec	N/A
Product Name	VersaKrimp™
Type	Ring
Physical	
Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Termination Interface: Style	Crimp or Compression
Wire Size AWG	8
Wire Size mm²	6.60 - 10.5
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	D-350-10T
Reference - Drawing Numbers	
Sales Drawing	SD-19193-016




image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19193Series

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
ATP Perishable Tool Kit used in ATP presses that process product on tape	0190270105
ATP Perishable Tool Kit used in ATP presses that process product on tape	0190270111
ATP Tooling Kit for ATP-100 and ATP-300 Series Air Crimping Press for	0190270117

Mylar Tape Mounted
Terminals
ATP Tooling Kit 0190270120
for ATP-100 and
ATP-300 Series Air
Crimping Press for
Mylar Tape Mounted
Terminals
ATP Perishable Tool 0190270245
Kit Used in ATP
Presses that Process
Product on Tape
Crimp Dies for the 0190472000
ATP-201™ Air
Crimping Press for
Mylar Tape Mounted
Terminals

This document was generated on 02/03/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION