




PANEL THICKNESS	X dimension
0.75-1.25 [.030-.049]	19.2-0.1 [.756]
1.25-2.0 [.049-.079]	19.4-0.1 [.764]
2.0-3.0 [.079-.118]	19.8-0.1 [.780]




PANEL CUTOUT
NOT TO SCALE



SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
<ON>	OFF	<ON>
1-1a	OPEN	1-1b


()=MOMENTARY



CIRCUIT: SPDT

NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERMINAL NUMBERS FOR REF ONLY
- RATING: 15A @ 125VAC OR
6A @ 250VAC
- APPROVALS: UL, CSA, NEMKO, FEMKO, DEMKO, SEMKO
- MATERIALS: TERMINALS: Silver Plated Copper Alloy
CONTACTS: Coin Silver, Silver Plated
- ELECTRIC LIFE: 10,000 cycles
- CONTACT RESISTANCE: <20 Mega-ohm
- INSULATION RESISTANCE: >1000 Mega-ohm
- DIELECTRIC STRENGTH: >1500 V 1 minute
>3000 V between poles



E-SWITCH®

TITLE

R1966I BLK BLK BF

SCALE

1.5:1

DATE

4/16/02

DR

CB

DWG

M306211

REV

C

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

C	12061	REVISED MARKING	5/02/02	CJB
REV.	ECN No.	DESCRIPTION	DATE	CHKD