




**ENERGIZER NH22-175****9V****Industry Standard Dimensions**

mm (inches)

**Discharge Characteristics**

Typical Performance at 21°C (70°F)



<b>Classification:</b>	Rechargeable
<b>Chemical System:</b>	Nickel-Metal Hydride (NiMH)
<b>Designation:</b>	ANSI-7.2H5
<b>Nominal Voltage:</b>	8.4 Volts
<b>Rated Capacity:</b>	175 mAh* at 21°C (70°F)
<b>Typical Weight:</b>	42.0 grams (1.5 oz.)
<b>Typical Volume:</b>	22.0 cubic centimeters (1.3 cubic inch)
<b>Terminals:</b>	Snap
<b>Jacket:</b>	Plastic

\* Based on 35 mA (0.2C rate) continuous discharge to 1.0 volts.

**Specifications****Internal Resistance:**

The internal resistance of the cell varies with state of charge, as follows:

<u>Cell Charged</u>	<u>Cell 1/2 Discharged</u>
1000 milliohms	1500 milliohms
(tolerance of $\pm 20\%$ applies to above values)	

**AC Impedance (no load):**

The impedance of the charged cell varies with frequency, as follows:

<u>Frequency (Hz)</u>	<u>Impedance (milliohms)</u> (charged cell)
1000	950

Above values based on AC current set at 1.0 ampere.  
Value tolerances are  $\pm 20\%$ .**Operating and Storage Temperatures:**

To maintain maximum performance, observe the following general guidelines regarding environmental conditions:

Charge:	0°C to 40°C (32°F to 104°F)
Discharge:	0°C to 50°C (32°F to 122°F)
Storage:	-20°C to 30°C (-4°F to 86°F)
Humidity:	65 $\pm$ 20%

**NOTE:** Operating at extreme temperatures, will significantly impact battery cycle life.**Important Notice**

This data sheet contains typical information specific to products manufactured at the time of its publication.  
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Energizer:](#)

[NH22NBP](#)