







PRODUCT NUMBER
55444-XY
55444-XYLF



PLATING IN CONTACT AREA

DASH NUMBER	PERFORMANCE LEVEL	NOTES
-1YY	TELCORDIA CO	-
-2YY	TELECOM CLASS	-
-3YY	IEC CLASS I	-
-5YY	TELCORDIA UE	-
-9YY	0.76 GXT	-
-1YYLF	TELCORDIA CO	SEE NOTE 8
-2YYLF	TELECOM CLASS	SEE NOTE 8
-5YYLF	TELCORDIA UE	SEE NOTE 8


mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI	
ltr	ecr no.	dr	date	linear	0.X ±0.3	0.XX ±0.13	.XXX ±.051	COPY	projection	www.fciconnect.com	
A	V02565	TAB	10/02/00	angles	0° ±2°					title	
B	V10907	CGD	02/22/01							METRAL SIGNAL HEADER	
C	V11659	CGD	06/04/01							4 MOD, 5 ROW SPECIAL STB	
D	V20758	CGD	04/25/02	dr	T.BRUNGARD	11/19/99				product family	
E	V21671	TAB	10/21/02	enrg	M.STRAWER	11/19/99				METRAL	
F	V05-0393	DAI	04/26/05	chr	M.STRAWER	11/19/99				code	
G	V06-0492	DCH	2006-05-23	appd	M.STRAWER	02/29/00				213	
sheet index		revision	G	G	G	G	G	G	G	size	
		sheet	1	2	3	4	5	6		dwg no	
										55444	
										1 of 6	



REQUIRED PC BOARD LAYOUT
COMPONENT SIDE

SEE PRINT 58351 FOR
ADDITIONAL PCB INFORMATION

KEY		
CODE	DIMENSIONS	
	DIM "A" MATE	DIM "B" TAIL
1	5.00	4.25
2	5.75	4.25
3	6.50	4.25

mat'l code				tolerances unless otherwise specified		CUSTOMER		 www.fciconnect.com				
ltr	ecr no.	dr	date	linear	0. X ± 0.3	COPY			title METRAL SIGNAL HEADER 4 MOD, 5 ROW SPECIAL STB			
G					0. XX ± 0.13							
					. XXX ± .051							
				angles	0° ± 2°							
				dr	T.BRUNGARD	11/19/99	 MM scale	product family		METRAL	code	
				enr	M. STAWSE	11/19/99		size	dwg no		213	
				chr	M. STAWSE	11/19/99		55444		sheet		
				appd	M. STAWSE	02/29/00	1 : 1	A			2	
sheet index	revision sheet											

cage code 22526

Pro/E

PDM: Rev:G

STATUS: Released Printed: May 16, 2009

[illegible]

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X02	E	OBSOLETE																							
SEE NOTE 9 LEAD FREE OPTION	D																								
	C																								
	B																								
	A																								

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X03 SEE NOTE 9 LEAD FREE OPTION	E	OBSOLETE																							
	D																								
	C																								
	B																								
	A																								

[illegible]

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

B

[illegible]

B

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X05 SEE NOTE 9 LEAD FREE OPTION	E	OBSOLETE																							
	D																								
	C																								
	B																								
	A																								

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X06 SEE NOTE 9 LEAD FREE OPTION	E	OBSOLETE																							
	D																								
	C																								
	B																								
	A																								

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X07	E	OBSOLETE																							
SEE NOTE 9 LEAD FREE OPTION	D																								
	C																								
	B																								
	A																								

[illegible]

A

Pro/E

cage code	22526
-----------	-------

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X13	E	OBSOLETE																							
SEE NOTE 9 LEAD FREE OPTION	D																								
	C																								
	B																								
	A																								

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2						MOD. 3						MOD. 4						
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X14	E	OBSOLETE																							
SEE NOTE 9 LEAD FREE OPTION	D																								
	C																								
	B																								
	A																								

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X15	E	SEE NOTE 9 LEAD FREE OPTION OBSOLETE																							
	D																								
	C																								
	B																								
	A																								

A

4

METRAL P/N	ROW	CONTACT CODE MOD. 1						MOD. 2					MOD. 3					MOD. 4							
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X16	E																								
	D																								
SEE NOTE 9 LEAD FREE OPTION	C																								
	B																								
	A																								



This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.

B

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCi www.fciconnect.com											
lfr	ecn no.	dr	date	linear	0. X $\pm$ 0.3		COPY projection 	title METRAL SIGNAL HEADER 4 MOD, 5 ROW SPECIAL STB											
G					0. XX $\pm$ 0.13														
					.XXX $\pm$.051														
				angles	0° $\pm$ 2°		 scale 1:1	product family						METRAL		code			
				dr	T.BRUNGARD 11/19/99			size				dwg no		213 sheet 4					
				enrg	M.STRAWSER 11/19/99			55444											
				chr	M.STRAWSER 11/19/99														
				appd	M.STRAWSER 02/29/00														
sheet index		revision sheet																	

[illegible]


This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCi.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCi.
Copyright FCi.



A

METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X17 SEE NOTE 9 LEAD FREE OPTION	E	OBSOLETE																							
	D																								
	C																								
	B																								
	A																								
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X18 SEE NOTE 9 LEAD FREE OPTION	E	OBSOLETE																							
	D																								
	C																								
	B																								
	A																								
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X19 SEE NOTE 9 LEAD FREE OPTION	E	OBSOLETE																							
	D																								
	C																								
	B																								
	A																								
METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X20 SEE NOTE 9 LEAD FREE OPTION	E	OBSOLETE																							
	D																								
	C																								
	B																								
	A																								

B

mat'l code				- -		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0. X ±0.3			COPY			title		
G					0. XX ±0. 13			projection			METRAL SIGNAL HEADER		
					. XXX ±. 051						4 MOD, 5 ROW SPECIAL STB		
				angles	0° ±2°						product family		
					dr T. BRUNGARD 11/19/99						METRAL		
					enrg M. STRAWSE 11/19/99						code		
				chr	M. STRAWSE 11/19/99			scale		A	size		dwg no
					M. STRAWSE 11/19/99			1 : 1			55444		
					appd M. STRAWSE 02/29/00						213		
sheet index		revision sheet											sheet 5

A


B



METRAL P/N	ROW	CONTACT CODE MOD. 1					MOD. 2					MOD. 3					MOD. 4								
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
55444-X25	E	OBSOLETE																							
SEE NOTE 9 LEAD FREE OPTION	D																								
	C																								
	B																								
	A																								

NOTES:

- FOR DIM A AND B SEE SHEET 2 AND UP.
- BODY MATERIAL: LIQUID CRYSTAL
POLYMER 30 % GLASS.
FLAME RETARDANT ACC. UL 94-V0.
- PIN MATERIAL:
PHOSPHOR BRONZE.
- PLATING ON PRESS-FIT TAIL:
55444 -XXX IS SnPb
55444-XYLIF IS SN (LEAD FREE)
PLATING ON CONTACT AREA CONFORMS TO PERFORMANCE
LEVEL SHOWN IN TABLE.
- PRODUCT MARKING:
PART NUMBER DESIGNATION & BATCH I.D.
- ALL PRODUCTS WITH PART NUMBERS SHOWN IN
SUBSEQUENT TABLES WILL BE PACKAGED IN TUBES.
IF TRAY PACKAGING IS REQUIRED, A SUFFIX "P"
WILL BE ADDED TO THE END OF THE PART NUMBER.
EXAMPLE: XXXXX-XXXP OR XXXXX-XXXPLF
- PRODUCT SPECIFICATION GS-12-180
APPLICATION SPECIFICATION BUS-20-075
- THE PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET THE
EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS
AS DESCRIBED IN GS-22-008.
- FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX.
EXAMPLE: 55444-X01LF
- ALL PRODUCTS EXCEPT THOSE WITH PART NUMBERS CONTAINING
(DRAWING NO.)-N1--- OR (DRAWING NO.)-N5---WILL WITHSTAND EXPOSURE
TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR
VAPOR PHASE REFLOW OVEN. PART NUMBERS (DRAWING NO.)-N1---
AND (DRAWINGS NO.)-N5---WILL NOT WITHSTAND REFLOW AND Au CONTACT
SURFACE OF THE CONTACTS SHALL BE EXPOSED TO A MAXIMUM 140°C FOR
NO LONGER THAN 15 SECONDS IN A WAVE SOLDER APPLICATION.

mat'l code				--		tolerances unless otherwise specified		CUSTOMER				www.fciconnect.com									
ltr	ecr no.	dr	date	linear	0. X ±0.3				COPY			title METRAL SIGNAL HEADER 4 MOD, 5 ROW SPECIAL STB									
G					0. XX ±0.13																
					.XXX ±.051																
				angles	0° ±2°																
				dr	T.BRUNGARD		11/19/99		 MM scale		product family				METRAL				code		
				enrg	M.STRAWSE		11/19/99				size		dwg no				213				
				chr	M.STRAWSE		11/19/99				A		55444				sheet				
				appd	M.STRAWSE		02/29/00		1:1						6						
sheet index		revision sheet																			