


**Part Number: 500027-5082**

0.40mm Pitch Board-to-Board SlimStack™ Plug, Surface Mount, Dual Row, Vertical, 0.95mm Mated Height, without Friction Lock, Lead-Free, 50 Circuits



Series image - Reference only

Status:**OBSOLETE****Replacement:**

Contact Molex

Series:

500027

Category:

PCB Headers

Overview:

SlimStack™ 0.40mm Pitch Board-to-Board Connectors

Mates With Part(s):[500024](#) SlimStack™ Board-to-Board Receptacle**Product Environmental Compliance****EU RoHS:** ELV and RoHS Compliant**China RoHS:** **REACH SVHC:****Low-Halogen Status:** Not Reviewed

Part Detail**General**

Status	Obsolete
Category	PCB Headers
Series	500027
Application	Board-to-Board, Signal
Comments	Solder Tab Plating: Lead-Free, Tin
Overview	SlimStack™ 0.40mm Pitch Board-to-Board Connectors
Product Name	SlimStack™

Physical

Breakaway	No
Circuits (Loaded)	50
Circuits (maximum)	50
Color - Resin	Natural
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	0.95mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Vertical
PC Tail Length	0.47mm
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.40mm
Pitch - Termination Interface	0.40mm
Plating min - Mating	0.102µm
Plating min - Termination	0.102µm
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Surface Mount

Electrical**(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.1A
Voltage - Maximum	50V

Material Info

UPC	822348313518
-----	--------------

Reference - Drawing Numbers

Product Specification	PS-500024-008
Sales Drawing	SD-500027-018, SD-500027-025

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)