







Recommended P.C. Board Layout
(Top View)

Part Number	Contact Area Plating Finish
K11-E9P-N	Gold Flash (standard)
K11-E9P-N15	15u" Gold (15 option)
K11-E9P-N30	30u" Gold (30 option)

Material And Finish

Shell- Steel, zinc plated or tin plated

Insulator- PBT, 30% glass-fiber reinforced
UL 94V-0,color black

Contact Material:
Plug- Brass

Contact Plating Options:

30 Option- .000030" [0.00076mm] gold on mating end, tin-lead on termination end, with entire contact nickel

15 Option- .000015" [0.00038mm] gold on mating end, tin-lead on termination end, with entire contact nickel

Standard- Gold flash on mating end, tin-lead on termination end, with entire contact nickel

Specifications

Rated Current- 2.5A

Rated Voltage- 300V DC

Withstanding Voltage- 500V(r.m.s.) AC for 1 minute

Insulation Resistance- More than 1000 Megohm at 500V DC

Contact Resistance- 15milliohm max.

Dielectric Strength- 1000V for 1 minute

Operating Temperature- -55°C to +105°C



Tolerances
X.X ± 0.5
X.XX ± 0.2
Unless Stated Otherwise

REVISION	DATE	DESCRIPTION	DRAWN BY	CHECKED BY	UNITS
A2	7/14/99	Rev. Dimensions	K. Wallace		mm [in]
A3	11/9/00	ECO #99-188	REVISED BY	APPROVED BY	DATE
A4	7/18/01	ECO #01-010	E. Cruz		6/22/99

K11-E9P-N

D-Sub, 9 pin male

Compact Footprint (0.200")



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[K11-E9P-N](#) [K11-E9P-NJ30](#) [K11-E9P-N15](#) [K11-E9P-N30](#) [K11-E9P-NJ15](#) [K11-E9P-NJ](#) [K11-E9P-NR](#)