


Technical Data

- ? through-hole or SMD
- ? 50mA/24VDC
- ? single pole/momentary
- ? 10.000.000 operations life time
- ? IP67 sealing
- ? temperature range:
low temp: -40/+115°C
high temp: -40/+160°C



Dimensions (through-hole)	Dimensions w/LED in switch (1C)	Dimensions w/LED PCB mounted (2B)	Dimensions (SMD)
PCB layout	PCB layout (top view)	PCB layout (top view)	PCB layout

How to order

3 A			+	1 B		+	2 A		
Switch	Mounting	L 6 low temp. H 9 high temp.		Cap	00 blue 02 green 03 grey 04 yellow 06 white 08 red 09 black		Bezel	00 blue 02 green 03 grey 04 yellow 06 white 08 red 09 black	For 1B and 2A only: 30 ultra blue 40 dusty blue 42 aqua blue 32 mint green 33 tele grey 34 melon 38 noble red 50 metal dark blue 53 metal light grey 57 metal dark grey 58 metal bordeaux

3 A	T		+	1 C		+		+	2 A	
Switch	Mounting T through-hole	L 6 low temp. H 9 high temp.		LED 00 blue 20 green 40 yellow 80 red	Cap	00 blue 02 green 03 grey 04 yellow 06 white 08 red 09 black		Lens 1 transparent 2 green 4 yellow 8 red	Bezel	00 blue 02 green 03 grey 04 yellow 06 white 08 red 09 black
3 A			+	1 B		+	2 B			
Switch	Mounting T through-hole S surface mount	L 6 low temp. H 9 high temp.		Cap	00 blue 02 green 03 grey 04 yellow 06 white 08 red 09 black		Bezel	00 blue 02 green 03 grey 04 yellow 06 white 08 red 09 black	Lens 1 transparent 2 green 4 yellow 6 frosted white 8 red	
						+	2 B X X X			
							LED for 2B bezel	20 green 40 yellow 80 red		

Keycaps and bezels shown on this page can also be used on
illumecc™ switch 4A - see page 9. Part nos. for bezels for 4A are 2C and 2D.

Ordering example: 3ATL640 + 1C094 + 2A04

For updates of products and/or changes of specifications please see www.mec.dk

multimec®

3A + 1A/1H/1M/1ZA

Technical Data

- through-hole or SMD
- 50mA/24VDC
- single pole/momentary
- 10.000.000 operations life time
- IP67 sealing
- temperature range:
low temp: -40/+115°C
high temp: -40/+160°C



Dimensions (through-hole) 1A	Dimensions (w/LED) 1H	Dimensions (SMD) 1ZA	Dimensions (SMD) 1M

How to order

3 A	☐	☐	+	1 A	☐		
Switch	Mounting	L 6 low temp. H 9 high temp.		Cap	00 blue 02 green 03* grey 04 yellow 06* white 08 red 09* black	30* ultra blue 40* dusty blue 42* aqua blue 32 mint green 33 tele grey 34 melon 38 noble red	50* metal dark blue 53* metal light grey 57* metal dark grey 58* metal bordeaux
	T through-hole S surface mount			1 Z A			
				Cap			

3 A	☐	☐	+	1 M	☐
Switch	Mounting	L 6 low temp. H 9 high temp.		Cap	00 blue 02 green 03 grey 04 yellow 06 white 08 red 09 black
	T through-hole S surface mount				

3 A	T	☐	+	1 H	☐
Switch	Mounting	L 6 low temp. H 9 high temp.		Cap	Lens
	T through-hole			LED 00 blue 20 green 40 yellow 80 red	1 transparent 2 green 4 yellow 6 frosted white 8 red

Keycaps shown on this page can also be used on
illumecc™ switch 4A - see page 9

Ordering example: 3ATL680 + 1H098

For updates of products and/or changes of specifications please see www.mec.dk


multimec[®] Navimec[™]

Technical Data

- through-hole or SMD
- 50mA/24VDC
- single pole/momentary
- 10.000.000 operations life time
- IP67 sealing
- temperature range:
low temp: -40/+115°C
high temp: -40/+160°C




Dimensions 1ZB (through-hole)



PCB layout

Dimensions 1ZC (SMD)




PCB layout


Recommended panel cut-out:

ø35.0-35.5 Depending on application

PCB layout TH



PCB layout SMD



How to order

3 A	☐	☐	☐	☐	☐
Switch	Mounting	L 6 low temp.	Cap 1ZB	03 grey	
	T through-hole	H 9 high temp.		06 white	
	S surface mount			09 black	
				30 ultra blue	
				40 dusty blue	
				42 aqua blue	
				50 metal dark blue	
				53 metal light grey	
				57 metal dark grey	
				58 metal bordeaux	

Navimec[™] Module

Part No. 9508000	Navimec[™] Module excl. keycaps
Part No. 950XXYY	Navimec[™] Module incl. keycaps
Part No. 9509XXYYYY	Navimec[™] Module incl. keycaps with legends

The module can be delivered with keycaps (4 x 1ZB and 1 x 1ZC) in solid colours or black keycaps with white legends.


For module incl. keycaps in solid colours (950XXYY) please indicate colour code for 1ZBXX and colour code for 1ZCYY.

For module incl. keycaps with legends (9509XXYYYY) please indicate legends for 1ZBXXX and legends for 1ZCYYY. All Caps are black with white legends. Please see legends available on page 23.

Examples: Module with 5 switches (4x3ATL6+1x3FTL6) mounted with 4x1ZB30 ultra blue and 1x1ZC42 aqua blue = 9503042.


Module with 5 switches (4x3ATL6+1x3FTL6) mounted with 4x1ZB09XD136 (legend arrow) and 1x1ZC09118 (legend OK) = 9509136118.

Dimensions Navimec[™] Module



Dimensions (mm)

Circuit Diagram Navimec[™] Module (Front side View)



The plug on the Navimec[™] module is JST SMT S10B-PH-SM3-TB or similar.
We recommend using
Cable socket: JST PHR-10 or similar
Contact: JST SPH-002T-PO.5S or similar.

Ordering example: 4x3ATL6+1ZB53 and 1x3FTL6+1ZC58 or Navimec[™] Module 9505358

For updates of products and/or changes of specifications please see www.mec.dk


multimec® illumec™ 4F

Technical Data


- through-hole or SMD
- 50mA/24VDC
- single pole/momentary
- 10.000.000 operations life time
- IP67 sealing
- temperature range:
high temp. switch; -40/+160°C
LED: -30/+85°C



Dimensions (through-hole)




Top View





PCB layout and Circuit Diagram


1 LED




2 LEDS



Dimensions (SMD)




Top View





PCB layout and Circuit Diagram

1 LED



2 LEDS



Technical specifications for 4F switch and LEDs see pages 35 and 36

How to order

Switch	Mounting	LED	Illuminated Cap	
4 F				
SH9	surface mount	01		1D
TH9	through-hole	22		1K,1KB,1KC
		42		1N
		61		1S
		82		1T
		2242		1U
		8222		1V
		8242		1WA,1WD,1WP
				1X

Colour code

	Cap	Solid Colour	Illuminated Lens
11,16			
11,16			
10,12,14,16,18			1E Solid Colour + lens 1,2,4,6,8
11			1F Solid Colour + lens 1,2,4,6,8
16			1Q Solid Colour + lens 1,6
16			1R Solid Colour + lens 1,6
16			
16			
11			

Colour codes

LEDs	Illuminated Caps	Lenses
01 blue	10 frosted blue	1 transparent
22 green	11 transparent	2 green
42 yellow	12 frosted green	4 yellow
61 white	14 frosted yellow	6 frosted white
82 red	16 frosted white	8 red
2242 green/yellow	18 frosted red	
8222 red/green		
8242 red/yellow		

Solid Colours

1E,1F	1Q,1R
00 blue	00 blue
02 green	03 grey
03 grey	08 red
04 yellow	09 black
06 white	
08 red	
09 black	

Dimensions

Caps	See Page
1D,1E,1F	15
1K,1KB,1KC	16
1N	14
1Q,1R	18
1S	21
1T,1U,1V	19
1WA,1WD,1WP	17
1X	20

Ordering example: 4FSH98242 + 1D11 or 4FTH922 + 1T16

For updates of products and/or changes of specifications please see www.mec.dk

multimec®


3F + 1D/1E/1F

Technical Data


- through-hole or SMD
- 50mA/24VDC
- single pole/momentary
- 10.000.000 operations life time
- IP67 sealing
- temperature range:
low temp: -40/+115°C
high temp: -40/+160°C




Dimensions (through-hole)




PCB layout




Dimensions (w/LED)




PCB layout (top view)



Dimensions (SMD)



PCB layout



How to order

3 F

Switch

T

Mounting

T through-hole
S surface mount

L 6

L 6 low temp.
H 9 high temp.

1 D

Cap



00

00 blue
02 green
03 grey
04 yellow
06 white
08 red
09 black

30 ultra blue
40 dusty blue
42 aqua blue
32 mint green
33 tele grey
34 melon
38 noble red

50 metal dark blue
53 metal light grey
57 metal dark grey
58 metal bordeaux

3 F

Switch

T

Mounting

T through-hole

L 6

L 6 low temp.
H 9 high temp.

LED

00 blue
20 green
40 yellow
60 white
80 red
2040 green/yellow
8020 red/green
8040 red/yellow

+

Cap 1D



Cap 1E



Cap 1F



11

11 transparent
16 frosted white

Lens

00 blue
02 green
03 grey
04 yellow
06 white
08 red
09 black

1 transparent
2 green
4 yellow
6 frosted white
8 red

Keycaps shown on this page can also be used on
illumec™ switch 4F - see page 13


Ordering example: 3FTL620 + 1E032

For updates of products and/or changes of specifications please see www.mec.dk

multimec® 3F + 1K/1KB/1KC

Technical Data

- through-hole or SMD
- 50mA/24VDC
- single pole/momentary
- 10.000.000 operations life time
- IP67 sealing
- temperature range:
low temp: -40/+115°C
high temp: -40/+160°C



How to order

3 F			+	1 K	1 6	+	2 K	
Switch	Mounting	L 6 low temp. H 9 high temp.		Cap	00 blue 02 green 03 grey 04 yellow 06 white 08 red 09 black		Bezel	03 grey 06 white 08 red 09 black

3 F	T			+	1 1 1 6	+	2 K	
Switch	Mounting	L 6 low temp. H 9 high temp.	LED		Cap frosted white		Bezel	03 grey 06 white 08 red 09 black
	T through-hole S surface mount		23 green 45 yellow 88 red		1K			
					1KB			
					1KC			

The 1K caps consist of a transparent lid and a diffuser lens.
It is possible to make your own customized legend by placing a foil between the lid and the lens.

Keycaps shown on this page can also be used on
illumec™ switch 4F - see page 13

Ordering example: 3FTL688 + 1K1116

For updates of products and/or changes of specifications please see www.mec.dk


multimec® 3F + 1S + 2S

Technical Data


- through-hole or SMD
- 50mA/24VDC
- single pole/momentary
- 10.000.000 operations life time
- IP67 sealing
- temperature range:
low temp: -40/+115°C
high temp: -40/+160°C




Dimensions (through-hole)




Dimensions (w/LED)



Dimensions (SMD)



How to order

3 F	☐	☐	+	1 S 0 9 - . . .	+	2 S 0 9 - . . .
Switch	Mounting	L 6 low temp. H 9 high temp.		Cap black	Height	Extender black Height
	T through-hole S surface mount				16.0 19.0 22.5	 05.0 (Optional) 06.0 Adds 5-10mm to total height 07.0 08.0 09.0 10.0

3 F	T	☐	+	☐	1 S 1 1 - . . .
Switch	Mounting	L 6 low temp. H 9 high temp.		LED	Cap Transparent Height
	T through-hole			00 blue 20 green 40 yellow 60 white 80 red 2040 green/yellow 8020 red/green 8040 red/yellow	 16.0 19.0 22.5

Customised Heights:

3F+1S is available in any height from 12.0 to 24 mm.

3F+1S+2S is available in any height from 17.0 to 34 mm.

Min. height for 1S11 is 16.0 and for 1S09 min height is 12.0 mm.

Min. order qty. for custom heights is 2.000 pcs.

For heights less than 12.0 mm, please refer to 3E switch range.

Keycaps shown on this page can also be used on
illumec™ switch 4F - see page 13


Ordering example: 3FTL640 + 1S11-19.0

For updates of products and/or changes of specifications please see www.mec.dk




All standard legends are white on black caps.
The size of the legends listed may not correspond to the actual size. Please ask your local distributor, if you do not find what you need on the list. New legends may have been added after this catalogue was printed.
Custom legends and other colour combinations are available, please contact your local distributor.

Note!



For 1A/1B the orientation shown above is standard.

Please consider the switch orientation you require before specifying legend orientation.



For the 1D and 1F caps the orientation shown above is standard.








Please consider the switch orientation you require before specifying legend orientation.









Standard Keycap Legends

	Part no.							
LEGEND	1A09XU_	1A09XD_	1B09XU_	1B09XD_	1D09_	1F096_	1ZB09XD_	1ZC09_
0	000	000	000	000	000	000		
1	001	001	001	001	001	001		
2	002	002	002	002	002	002		
3	003	003	003	003	003	003		
4	004	004	004	004	004	004		
5	005	005	005	005	005	005		
6	006	006	006	006	006	006		
7	007	007	007	007	007	007		
8	008	008	008	008	008	008		
9	009	009	009	009	009	009		
A	010	010	010	010				
B	011	011	011	011				
C	012	012	012	012				
D	013	013	013	013				
#	107	107	107	107	107	107		
*	019	019	019	019	019	019		
⇧	016	016	016	016				
→	033	033	033	033	033			
←	133	133	133	133	133			
↑	034	034	034	034	034			
↓	134	134	134	134	134			
↶	135	135	135	135	135	135		
+	054	054	054	054				
-	059	059	059	059				
•	056	056	056	056				
▲							136	
⏻	123	123	123	123	123	123		123*
START	031	031	031	031				
CLEAR	036	036	036	036				
LOAD	037	037	037	037				
RESET	038	038	038	038				038
CANCEL	048	048	048	048				
ENTER								105
OK								118
SET								119
MENU								120
FUNC								121
HOME								122





* Also on 1ZC16 for illumination

multimec® basic switch modules

Through-hole Versions						
3A	3C	3E	3F	3F	3F	3F
For 1A/1B/1M/1ZA/1ZB	w/LED for 1C/1H	For 3E actuators/Varimec	For 1D/1K/1N/1P/1S/1T/1U/1V/1WA/1WD/1WG/1WP/1X/1ZC/1GA/1GC	w/LED for 1D/1E/1F/1N/1Q/1R/1S/1X	w/LED for 1K/1KB/1KC/1T/1U/1V/1WA/1WD/1WP	
						
Standard Versions						
3ATL6 3ATH9	3ATL600/20/40/80	3CTL6/3CTL9 3CTH9	3ETLXX-H* 3ETHXX-H*	3FTL6 3FTH9	3FTL600/20/40/60/80/ 2040/8020/8040	3FTL623/45/88
* 3E available in 6 standard heights: 08.0, 09.5, 10.4, 11.0, 12.0, 15.0 mm. Other heights between 08.0 and 15.0 mm are available upon request.						
Specials: Gold contacts, quiet version and actuation force other than 3.0N						


Surface Mount Versions				illumec™ Through-hole Versions		illumec™ Surface Mount Versions	
3A	3C	3E	3F	4AT w/LEDs	4FT w/LEDs	4AS w/LEDs	4FS w/LEDs
For 1A/1B/1M/1ZA/1ZB		For 3E actuators/Varimec	For 1D/1K/1N/1P/1S/1T/1U/1V/1WA/1WD/1WP/1X/1ZC/1GA/1GC	For 1C/1H	For 1D/1E/1F/1K/1KB/1KC/1N/1Q/1R/1S/1T/1U/1V/1WA/1WD/1WP/1X	For 1C/1H	For 1D/1E/1F/1K/1KB/1KC/1N/1Q/1R/1S/1T/1U/1V/1WA/1WD/1WP/1X
							
Standard Versions				Standard Versions			
3ASH9/3ASH9R	3CSH9/3CSH9R	3ESH9/3ESH9R	3FSH9/3FSH9R	4ATH901/22/42/61/82/ 2242/8222/8242	4FTH901/22/42/61/82/ 2242/8222/8242	4ASH901/22/42/61/82/ 2242/8222/8242	4FSH901/22/42/61/82/ 2242/8222/8242

Co-planarity = ≤ 0.05

Right Angle Versions			
3C	3E	3F	3F w/LED
	For 3E actuators/Varimec	For 1D/1K/1N/1P/1S/1T/1U/1V/1W/1WA/1WD/1WP/1X/1ZC/1GA/1GC	For 1D/1E/1F/1N/1Q/1R/1S/1X
			
Standard Versions			
3CTL6RAS	3ETXX-X.XRAS	3FTL6RAS	3FTL600/20/40/60/80/ 2040/8020/8040RAS


DIMENSIONS (mm) Unless otherwise specified, all tolerances ± 0.2

multimec® Cross Section


For updates of products and/or changes of specifications please see www.mec.dk

multimec® basic switches and tape & reel

Recommended PCB layout



Operating Force (typical example)



Tape and reel is available for the parts listed and has the following specifications:

Reel diameter $\phi 330\text{mm}$
Tape width 24mm
Pitch see list
Tape and reel material antistatic or better
Quantity per reel see list

3A/3C/3E/3F multimec® tape & reel


Part No.	Ordering Code	Pitch	Quantity per reel
3ASH9	3ASH9R	16	500
3CSH9	3CSH9R	16	500
3ESH9	3ESH9R	16	500
3ESH9-08.0	3ESH9R08.0	20	250
3ESH9-09.5	3ESH9R09.5	20	250
3ESH9-10.4	3ESH9R10.4	20	250
3ESH9-11.0	3ESH9R11.0	20	250
3ESH9-12.0	3ESH9R12.0	20	250
All varimec below 12.5	R after the part no.	20	250
3FSH9	3FSH9R	20	250

4F illumec™ tape & reel


Part No.	Ordering Code	Pitch	Quantity per reel
4FSH901	4FSH901R	20	250
4FSH922	4FSH922R	20	250
4FSH942	4FSH942R	20	250
4FSH961	4FSH961R	20	250
4FSH982	4FSH982R	20	250
4FSH92242	4FSH92242R	20	250
4FSH98222	4FSH98222R	20	250
4FSH98242	4FSH98242R	20	250

Specifications are according to EIA 600481-3 and IEC 60286-3


Circuit Diagram



How to Assemble



Mounting Tool for Through-hole versions




Specifications are subject to change without notice.

For updates of products and/or changes of specifications please see www.mec.dk


multimec® spacing

Basic switch spacing

through-hole




surface-mount




Recommended switch/cap spacing


Switch spacing



Cap dimension





Panel cut-out



Panel Cut-out







1N 1V

1T



Spacing in mm

Spacing examples

multimec®
3AT + 1B/C + 2A/Bmultimec®
3AS + 1B + 2A/B
4AS + 1B/1C + 2C/2Dmultimec®
3AT + 1A/Hmultimec®
3AT + 1Mmultimec®
1N + 1N + 1Nmultimec®
1V + 1T + 1V

Cap series	Recommended* min. switch spacing AxB	Nominal cap dimension W x H	Recommended min. panel cut-out
1A	12.7 x 10.16	12.6 x 10.1	13.0 x 10.5
1B/1C+2A/2B	15.24 x 15.24	15.1 x 15.1	15.5 x 15.5
1D/1E/1F	12.7 x 12.7	ø9.6	ø10.0
1K	15.24 x 15.24	14.3 x 14.3	14.7 x 14.7
1M	25.4 x 10.16	25.0 x 10.1	25.7 x 10.5
1N	12.7 x 12.7	ø9.8/□4.9	ø10.2/□5.1
1P/1Q/1R	15.24 x 10.16	6.5 x 12.5	7.0 x 13.0, R Max. 1.0
1S	12.7 x 10.16	ø6.5	ø7.0
1T	12.7 x 12.7	10.6 x 10.6	11.0 x 11.0
1U	12.7 x 12.7	ø10.6	ø11.0
1V (pointing outwards)	12.7 x 12.7	10.6 x 13.25	11.0 x 13.65
1X	12.7 x 12.7	9.4 x 7.4	9.8 x 7.9

*A dimension with surface mount version is min. 15.24. Depending on manufacturing technology it may be necessary either to reduce pad dimension, or to increase spacing.

In all applications the total assembly tolerance must be analysed by the user (board tolerance, front panel, assembly accuracy), to secure enough room for a free switch movement in the final product. The specifications on this page are to be considered as an aid only. MEC cannot be held responsible for the final assembly.

For updates of products and/or changes of specifications please see www.mec.dk

multimec®

technical specifications

RoHS Compatible

	3A-3C-3E-3F Low Temperature Versions SilverGold		3A-3C-3E-3F High Temperature Versions SilverGold		illumec™ 4A - 4F High Temperature Versions SilverGold	
Electrical Specifications						
Contact resistance	<30m Ω - typ. 10m Ω		<30m Ω - typ. 10m Ω		<30m Ω - typ. 10 m Ω	
Insulation resistance	>10M Ω		>10M Ω		>10M Ω	
Recommended load	0.5-50mA 24VDC	0.5μ-50mA 24VDC	0.5-50mA 24VDC	0.5μ-50mA 24VDC	0.5-50mA 24VDC	0.5μ-50mA 24VDC
Contact bounce	<2mS - typically 0.5mS		<2mS - typically 0.5mS		<2mS - typically 0.5mS	
Mechanical Specifications						
Standard actuation force (switch)	3.0N typ.		3.0N typ.		3.0N typ.	
Max. actuation force without cap	100N for 10 sec.		100N for 10 sec.		100N for 10 sec.	
Key travel (switch)	1 mm		1 mm		1 mm	
Life time (switch)	>10.000.000 cycles		>10.000.000 cycles		>10.000.000 cycles	
Temperature Range						
Working temperature	Min. -40°C Max. +115°C		Min. -40°C Max. +160°C		Min. -30°C Max. +85°C*	
Storage temperature	Min. -40°C Max. +115°C		Min. -40°C Max. +160°C		Min. -30°C Max. +85°C*	
Soldering IEC 68-2-20	Wave - max. 260°C for max. 10 sec., please refer to usage guidelines. Soldering iron - max. 350°C for max. 3 sec. Flux tight.		Infrared, vapour phase, wave - max. 240°C for max. 40 sec. or max. 260°C for max. 30 sec. Soldering iron - max. 350°C for max. 3 sec. Flux tight.		Infrared, vapour phase, wave - max. 240°C for max. 40 sec. or max. 260°C for max. 30 sec. Soldering iron - max. 350°C for max. 3 sec. Flux tight.	
Environmental Endurance IEC 68-2-3						
Temperature	+40°C		+40°C		+40°C	
Humidity	93% RH		93% RH		93% RH	
Duration	56 Days		56 Days		56 Days	
Temperature Cycling IEC 68-2-14						
Temperature limit	Min. -40°C - Max. +125°C		Min. -40°C - Max. +125°C		Min. -40°C - Max. +125°C	
Number of cycles	10		10		10	
Exposure time at each temperature	30 min.		30 min.		30 min.	
Recovery time before measurements	16 hrs.		16 hrs.		16 hrs.	
Sealing IEC 529	IP-67		IP-67		IP-67	
Cleaning	Standard methods - see usage guidelines		Standard methods - see usage guidelines		Standard methods - see usage guidelines	
Vibration Test IEC 68-2-6						
Cycles					10	
Cycles time					2 hrs.	
Material Specifications - Switches						
Housing	PBT UL94VO		PPS UL94VO		PPS UL94VO	
Actuator	PBT UL94VO		PPS UL94VO		PPS UL94VO	
Sealing + spring	Silicone rubber		Silicone rubber		Silicone rubber	
Contact spring	Stainless steel + 3μAg	Stainless steel + 1μAu	Stainless steel + 3μAg	Stainless steel + 1μAu	Stainless steel + 3μAg	Stainless steel + 1μAu
Fixed contacts	SnCu + 2μNI + 3μAg	SnCu + 2μNI + 1μAu	SnCu + 2μNI + 3μAg	SnCu + 2μNI + 1μAu	SnCu + 2μNI + 3μAg	SnCu + 2μNI + 1μAu
Terminals	SnCu + 2μNI + 3μSn100	SnCu + 2μNI + 3μSn100	SnCu + 2μNI + 3μSn100	SnCu + 2μNI + 3μSn100	SnCu + 2μNI + 3μSn100	SnCu + 2μNI + 3μSn100
Material Specifications - Caps & Bezels						
Material	Parts			Temp limit	UL rating	
ABS	1A, 1B, 1C, 1D, 1E, 1F, 1H, 1K, 1M, 1N, 1P, 1Q, 1R, 1T, 1U, 1V, 1WA, 1WD, 1WP, 1X, 1ZA, 1ZB, 1ZC.			Max. 65°C	UL94HB	
Polycarbonate	All lenses, 3E coloured actuators			Max. 85°C	UL94V1	
LCP	Black actuator of 3E			Max. 160°C	UL94VO	
PPS	1S, 2S			Max. 160°C	UL94VO	
Polyamide	Actuator of Varimec™, 1GA/1GC			Max. 160°C	UL94VO	
Legends Adhesion ISO Class: 1/ASTM Class: 4B DIN EN ISO 2409						

* LED max. working temperature

Specifications are subject to change without notice.

For updates of products and/or changes of specifications please see www.mec.dk

For 3A switches

3AXXX (for 1C/1H)

2BXXX

Colour		B	G	Y	R	G	Y	R	
Colour Codes		00	20	40	80	20	40	80	
Absolute Maximum Ratings (Ta=25°C)									
Power	mW	105	100	60	100	75	60	60	
Current forward	mA	30	30	20	30	20	20	20	
Forward peak current	mA	150	120	80	120	60**	60**	60**	
Voltage reverse	V	5	5	5	5	3	3	3	
Operating temperature	°C	-40 - +85	-55 - +100			-25 - +85			
Storage temperature	°C	-40 - +85	-55 - +100			-30 - +100			
Soldering temperature	°C	260/5 sec.	260 for max. 3 sec.			260 for max. 5 sec.			
Electrical-Optical Characteristics (Ta=25°C)									
Voltage forward	Typ. V	3.8	2.1*	2.1*	2.0*	2.1	2.1	2.0	
	Max. V	4.5	2.8*	2.8*	2.8*	3.0	3.0	3.0	
Current reverse (VR = 5V)	µA	10	100	100	100	10	10	10	
Wave length	nm	466	565	585	630	563	585	650	
Spread	Δnm	30	30	35	40	40	40	40	
Spread angle	degree	40	90	90	90	45	45	45	
Luminous Intensity	Min. mcd	4	0.7	1.7	1.1	9.0	5.6	5.6	
	Typ. mcd	10	2.5	5.6	3.7	25	16	16	
Orientation	The longer pin is the anode, the shorter is the cathode								

*/F = 20mA, **Pulse width 1ms Duty cycle 1:5

For 3F switches

3FXXX (for 1E-1F-1N-1Q-1R-1S-1X)

3FXXX (for 1K-1T-1U-1V-1W)

Colour		B	G	Y	W	R	G/Y	R/G	R/Y	G	Y	R
Colour Codes		00	20	40	60	80	2040	8020	8040	24	45	89
Absolute Maximum Ratings (Ta=25°C)												
Power	mW	105	70	60	114	60	120	120	120	60	130	80
Current forward	mA	30	20	20	30	20	25	25	25	25	40	30
Forward peak current	mA	200	60**	60**	100	60**	150	150	150	100	500	1000
Voltage reverse	V	5	3	3	5	3	5	5	5	5	12	12
Operating temperature	°C	-25 - +85			-40 - +85	-25 - +85	-40 - +85			-40 - +85	-55 - +100	
Storage temperature	°C	-30 - +100			-40 - +100	-30 - +100	-40 - +85			-40 - +100	-55 - +100	
Soldering temperature	°C	260 for max. 5 sec.			260 for max. 2 sec.	260 for max. 5 sec.	260 for max. 2 sec.			260 for max. 5 sec.		
Electrical-Optical Characteristics (Ta=25°C)												
Voltage Forward	Typ. V	2.1	2.1	2.1	3.3	2.0	2.1	2.1	2.1	2.0*	2.3***	2.0***
	Max. V	2.8	3.0	3.0	3.8	3.0	2.8	2.8	2.8	2.4*	2.5***	2.3***
Current reverse (VR = 5V)	µA	2	10	10	0.01	10	2	2	2	10	10	10
Wave length	nm	460	563	585	NA	650	565/590	625/565	625/590	573	587	633
Spread	Δnm	40	40	40	NA	40	35	35	35	20	45	16
Spread angle	degree	20	45	45	34	45	60	60	60	100	90	85
Luminous Intensity	Min. mcd	20	9.0	5.6	280	5.6	8	8	8	10****	71****	180****
	Typ. mcd	25	25	16	600	16	25	25	25	20****	112****	355****
Orientation	The longer pin is the anode, the shorter is the cathode. For bicolor LEDs the anode for the first colour (ex. 2080) is the longer pin.											

IF = 50mA, *Luminous Flux mlm

For 4A/4F switches

illumece™ LEDs specifications

Colour		B	G	Y	W	R	
Colour Codes		01	22	42	61	82	
Absolute Maximum Ratings (Ta=25°C)							
Power	mW	60	65	65	80	65	
Current forward	mA	20	25	25	15	25	
Forward peak current	mA	150	150	100	200	100	
Voltage reverse	V	5	12	12	5	12	
Operating temperature	°C	-30 - +85					
Storage temperature	°C	-30 - +85					
Soldering temperature	°C	245 for max. 10 sec.					
Electrical-Optical Characteristics (Ta=25°C)							
Voltage forward	Typ. V	3.35	2.2	2	3.05	2	
	Max. V	3.5	2.5	2.5	3.2	2.5	
Current reverse (VR = 5V)	µA	0.01	0.02	0.01	0.01	0.01	
Wave length	nm	470	570	588	n.a.	633	
Spread	Δnm	n.a.	30	16	n.a.	16	
Spread angle	degree	145	160	160	138	160	
Luminous Intensity	Min. mcd	30	28	112	28	112	
	Typ. mcd	35	70	150	35	150	
Optical Intensity	Lm/w	4			2.5		

B= Blue, G= Green, Y= Yellow, R= Red, W= White, G/Y= Green/Yellow, R/G= Red/Green, R/Y= Red/Yellow
 Specifications are subject to change without notice.

For updates of products and/or changes of specifications please see www.mec.dk