



TFP SIDE-MOUNT

INDUSTRY STANDARDS

UL 508A Component Recognized; File No. E61997
 TFP# Models: Type 1
 TFP# UL 12 Models: Type 12

CSA certified (fan only)
 CE

APPLICATION

- Industrial automation
- Automotive assembly
- Package handling equipment
- Food and beverage process controls
- Wind energy systems

FEATURES

- Cooling Fan Package includes fan, air filter, composite air plenum, finger guard and grille
- Exhaust Package includes air filter, filter retainer with integral finger guard and grille
- EMC Upgrade Kit includes a grille standoff collar and a special EMC shielding grille
- Reliable cooling for enclosures with limited space requiring simple filtered airflow for basic cooling
- 24 VDC, 115 VAC and 230 VAC options available
- Washable foam (Type 1) or disposable (Type 12) filter in fan

- Dynamically-balanced fan impellers molded from polycarbonate material
- 4-in. fan is thermally protected and uses permanently-lubricated ball bearings
- 6- and 10-in. fans have ball bearing construction and split-capacitor motors that are thermally protected to avoid premature failure
- Fans have lead wires for power connection with ends stripped 1/2 in. (12 mm)
- All mounting hardware and installation instructions are furnished

SPECIFICATIONS

- Free airflow from 45 CFM (76 m³/hr.) to 215 CFM (365 m³/hr.)
- Maximum operating temperature 158 F / 70 C
- Engineered for 50,000 hours of continuous operation without lubrication or service (a monthly maintenance schedule is recommended to ensure optimal cooling performance)

FINISH

- Stainless steel grilles have brushed finish.
- ABS composite grille is black.

ACCESSORIES

Aluminum Type 1 and Hi-Density Type 12 Filters

EMC Upgrade Kit

Grille Options:


- Stainless Steel
- Black ABS Plastic

Performance Data TFP4 Models


ELECTRICAL DATA			
	24 VDC	115 VAC	230 VAC
Rated Voltage			
Frequency [Hz]		50/60	
Nominal Current Maximum @ 50/60 Hz [Amps]	.35	.26/.21	.14/.11
Power Consumption Maximum @ 50/60 Hz [Watts]	8.4	17/15	16/14
Power Connection		Stripped Leadwires	
CATALOG NUMBERS			
Composite Type 1	TFP424	TFP41	TFP42
Catalog Number			
Stainless Steel Type 1	—	TFP41SS	TFP42SS
Catalog Number			
Composite Type 12	—	TFP41UL12	TFP42UL12
Catalog Number			
Free Airflow @ 50/60 Hz [CFM]*	55	45/55	45/55
Free Airflow @ 50/60 Hz [m ³ /hr.]*	93	76/93	76/93
UNIT CONSTRUCTION			
Noise SIL @ 50/60 Hz (dBA)	65	37/41	37/41
Maximum Operating Temperature (°F/°C)		158/70	
Unit Dimensions - H x W x D [in./mm]	6.29 x 7.37 x 2.65/160 x 187 x 67		
Cutout Dimensions - H x W [in./mm]	5.66 x 5.66/144 x 144		
Weight (lb./kg)	4.2/1.90	4.2/1.90	4.3/1.95
EXHAUST GRILLE CATALOG NUMBERS			
Composite Type 1		TEP4	
Catalog Number			
Stainless Steel Type 1		TEP4SS	
Catalog Number			
Composite Type 12		TEP4UL12	
Catalog Number			

*CFM with single exhaust grille installed.


TFP4 Models



BACK VIEW





SIDE VIEW



CUTOUT DIMENSIONS

TEP4 EXHAUST GRILLE



89084706

Exhaust grille included with fan package

Performance Data TFP6 Models
ELECTRICAL DATA

Rated Voltage	24 VDC	115 VAC	230 VAC
Frequency (Hz)		50/60	
Nominal Current Maximum @ 50/60 Hz (Amps)	.88	.45/.36	.23/.18
Power Consumption Maximum @ 50/60 Hz (Watts)	21.1	36/32	39/35
Power Connection		Stripped Leadwires	






CATALOG NUMBERS

Composite Type 1			
Catalog Number	TFP624	TFP61	TFP62
Stainless Steel Type 1	—	TFP61SS	TFP62SS
Catalog Number	—	TFP61UL12	TFP62UL12
Composite Type 12			
Catalog Number	—	117/140	117/140
Free Airflow @ 50/60 Hz (CFM)*	140	199/238	199/238
Free Airflow @ 50/60 Hz (m ³ /hr.)*	238		
UNIT CONSTRUCTION			
Noise SIL @ 50/60 Hz (dBA)	62.5	50/56	50/56
Maximum Operating Temperature (°F/°C)		158/70	
Unit Dimensions - H x W x D (in./mm)		7.80 x 8.87 x 3.75/198 x 225 x 95	
Cutout Dimensions - H x W (in./mm)		7.16 x 7.16/182 x 182	
Weight (lb./kg)	5.3/2.40	5.3/2.40	5.4/2.45

EXHAUST GRILLE CATALOG NUMBERS

Composite Type 1		
Catalog Number	TEP6	
Stainless Steel Type 1		
Catalog Number	TEP6SS	
Composite Type 12		
Catalog Number	TEP6UL12	

*CFM with single exhaust grille installed.

TFP6 Models

BACK VIEW

SIDE VIEW

CUTOUT DIMENSIONS
TEP6 EXHAUST GRILLE


Exhaust grille included with fan package

89084710

Performance Data TFP10 Models


ELECTRICAL DATA

Rated Voltage	115 VAC	230 VAC
Frequency (Hz)	50/60	50/60
Nominal Current Maximum @ 50/60 Hz (Amps)	.58/.70	.29/.35
Power Consumption Maximum @ 50/60 Hz (Watts)	64/80	64/80
Power Connection		Stripped Leadwires
CATALOG NUMBERS	TFP101	TFP102
Composite Type 1	TFP101	TFP102
Catalog Number		
Stainless Steel Type 1	TFP101SS	TFP102SS
Catalog Number		
Composite Type 12	TFP101UL12	TFP102UL12
Catalog Number		
Free Airflow @ 50/60 Hz (CFM)*	180/215	180/215
Free Airflow @ 50/60 Hz (m ³ /hr.)*	306/365	306/365
UNIT CONSTRUCTION		
Noise SIL @ 50/60 Hz (dBA)	54/61	54/61
Maximum Operating Temperature (°F/°C)	167/75	167/75
Unit Dimensions - H x W x D (in./mm)	11.81 x 12.99 x 5.25/300 x 330 x 133	
Cutout Dimensions - H x W (in./mm)	11.16 x 11.16/283 x 283	
Weight (lb./kg)	12.0/2.45	11.4/5.17


EXHAUST GRILLE CATALOG NUMBERS

Composite Type 1	TEP10
Catalog Number	
Stainless Steel Type 1	TEP10SS
Catalog Number	
Composite Type 12	TEP10UL12
Catalog Number	


*CFM with single exhaust grille installed.

TFP10 Models

BACK VIEW




SIDE VIEW



FAN GRILLE OUTLINE

CUTOUT DIMENSIONS


TEP10 EXHAUST GRILLE

89084711

Exhaust grille included with fan package

TFP EXHAUST GRILLES


	Nominal Fan Size in./mm
CATALOG NUMBERS	
TEP4 Models	
TEP4	4
TEP4SS	4
TEP4UL12	4
TEP6 Models	
TEP6	6
TEP6SS	6
TEP6UL12	6
TEP10 Models	
TEP10	10
TEP10SS	10
TEP10UL12	10

TFP OPTIONAL GRILLES AND REPLACEMENT FILTERS


Optional grilles offer the choice of stainless steel or black ABS plastic. These grilles replace the standard RAL 7035 gray composite or stainless steel grilles on both fan and exhaust packages. Standard replacement filters are washable foam (Type 1) or disposable (Type 12). To maintain UL Type 12 rating on the enclosure, UL Type 12 filters must be used on the fan package inlet. Washable aluminum filters are also available. Aluminum filters are compatible with Type 1 systems only. *Type 12 air filters are not washable.*

CATALOG NUMBERS	Description	Fits Fan and Exhaust Nominal Size	Fits Fan and Exhaust Grill Size (in./mm)
4-inch Fan Models			
TG4SS			
	Brushed stainless steel grille	4	6.29 x 7.31 x .81 160 x 186 x 21
TG4B	Black ABS plastic grille	4	6.29 x 7.37 x .81 160 x 187 x 21
AFLTR4	Type 1 filter replacement (5/package)	4	—
AFLTR4AL	Aluminum filter replacement (5/package)	4	—
TFLT4UL12	Type 12 filter replacement (5/package)	4	—
6-inch Fan Models			
TG6SS	Brushed stainless steel grille	6	7.80 x 8.81 x .75 198 x 224 x 19
TG6B	Black ABS plastic grille	6	7.80 x 8.87 x .49 198 x 225 x 12
AFLTR6	Foam filter replacement (5/package)	6	—
AFLTR6AL	Aluminum filter replacement (5/package)	6	—
TFLT6UL12	UL 12 filter replacement (5/package)	6	—
10-inch Fan Models			
TG10SS	Brushed stainless steel grille	10	11.81 x 12.92 x .75 300 x 328 x 19
TG10B	Black ABS plastic grille	10	11.81 x 12.99 x .75 300 x 330 x 19
AFLTR10	Foam filter replacement (5/package)	10	—
AFLTR10AL	Aluminum filter replacement (5/package)	10	—
TFLT10UL12	UL 12 filter replacement (5/package)	10	—

Replacement filter for Type 12 fan package only (models TFF_UL12). For Type 12 exhaust package use replacement filter AFLTRX. Filters fit all fan and exhaust packages according to their size.

TFP EMC UPGRADE KIT

With the addition of this kit, the cooling fan and exhaust packages are upgraded to provide EMC (electromagnetic compatibility) protection. Consult Hoffman for shielding effectiveness (dB attenuation vs. frequency).

Separate kits must be installed on both the inlet and outlet. Cooling fan and exhaust package must be ordered separately. EMC upgrade kit will not work with stainless steel grille option.

CATALOG NUMBERS	Fits Cooling Fan Package	Fits Exhaust Grille
4-inch Fan Models		
T4EMC	TFP41/TFP42	TEP4
6-inch Fan Models		
T6EMC	TFP61/TFP62	TEP6
10-inch Fan Models		
T10EMC	TFP101/TFP102	TEP10

