




10 9 8 7 6 5 4 3 2 1

注記
NOTES :


1. そり長さ25. 4に対して0.2MAX.
CAMBER MUST BE WITHIN 0.2MAX.
PER 25.4 .
2. 材料 (MATERIAL)
ウエハー: ポリアミド, UL94V-0
WAFER: POLYAMIDE, UL94V-0
ピン: $\square 0.635$ 黄銅, 銅下地錫メッキ
PIN: $\square 0.635$ BRASS, TIN OVER COPPER
PLATING.
3. 全極数が偶数の場合のみ適用。
APPLY FOR EVEN CIRCUITS PRODUCT ONLY.
4. ELV 及び RoHS 適合品
ELV AND RoHS COMPLIANT.



(公差非累積)
(NON-ACCUMULATIVE)

2.5±0.1
(ピッチ)
(PITCH)

$\phi 1.2^{+0.05}$



基板取付穴推奨寸法 (±1.6)
RECOMMENDED P.C. BOARD HOLE DIM.

49.5	47.5	22 05	I202	20
47	45		I192	19
44.5	42.5		I182	18
42	40		I172	17
39.5	37.5		I162	16
37	35		I152	15
34.5	32.5		I142	14
32	30		I132	13
29.5	27.5		I122	12
27	25		I112	11
24.5	22.5		I102	10
22	20		I092	9
19.5	17.5		I082	8
17	15		I072	7
14.5	12.5		I062	6
12	10		I052	5
9.5	7.5		I042	4
7	5		I032	3
4.5	2.5	22 05	I022	2
(B)	(A)	ORDER No.	極数 CKT.	

MODEL No. : 5046-**A

REVISED EC NO: J2012-0974 2012/01/30 DRWN:KASHIO CHKD:KASAKAWA APPR:NUKITA 2013/06/03 J	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	±0.2	DRAWN BY Y. MIZUNO	DATE 1992/01/09	TITLE KK2.5 R/A WAFER ASSY				
		10 OVER 30 UNDER	±0.25	CHECKED BY H. HIRAMOTO	DATE 1994/11/1					
		30 OVER	±0.3	APPROVED BY		molex				
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.				SHEET NO.
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-5046-NA				1 OF 1	
	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

C