



LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN
		J		ECO-07-021032	13SEP07	MB


- 1

THE NOTCHED EDGES AND POST TIPS WILL NOT BE PLATED.
- 2

0.00254-0.00508 [.000100-.000200] MATTE TIN OVER
0.00127 [.000050] MIN NICKEL.



DETAIL W
30:1



RECOMMENDED TIN PLATED HOLE SIZE
SCALE 10:1

OBSOLETE	35.56	[1.400]	6-147070-2
	25.40	[1.000]	6-147070-1
	25.15	[.990]	6-147070-0
	24.89	[.980]	5-147070-9
	24.64	[.970]	5-147070-8
	24.38	[.960]	5-147070-7
	24.13	[.950]	5-147070-6
	23.88	[.940]	5-147070-5
	23.62	[.930]	5-147070-4
	23.37	[.920]	5-147070-3
	23.11	[.910]	5-147070-2
	22.86	[.900]	5-147070-1
	22.61	[.890]	5-147070-0
	22.35	[.880]	4-147070-9
	22.10	[.870]	4-147070-8
	21.84	[.860]	4-147070-7
	21.59	[.850]	4-147070-6
	21.34	[.840]	4-147070-5
	21.08	[.830]	4-147070-4
	20.83	[.820]	4-147070-3
	20.57	[.810]	4-147070-2
	20.32	[.800]	4-147070-1
	20.07	[.790]	4-147070-0
	19.81	[.780]	3-147070-9
	19.56	[.770]	3-147070-8
	19.30	[.760]	3-147070-7
	19.05	[.750]	3-147070-6
	18.80	[.740]	3-147070-5
	18.54	[.730]	3-147070-4
	18.28	[.720]	3-147070-3
	18.03	[.710]	3-147070-2
	17.78	[.700]	3-147070-1
	17.53	[.690]	3-147070-0
	17.27	[.680]	2-147070-9
	17.02	[.670]	2-147070-8
	16.76	[.660]	2-147070-7
	16.51	[.650]	2-147070-6
	16.26	[.640]	2-147070-5
	16.00	[.630]	2-147070-4
	15.75	[.620]	2-147070-3
	15.49	[.610]	2-147070-2
	15.24	[.600]	2-147070-1
	14.99	[.590]	2-147070-0
	14.73	[.580]	1-147070-9
	14.48	[.570]	1-147070-8
	14.22	[.560]	1-147070-7
	13.97	[.550]	1-147070-6
	13.72	[.540]	1-147070-5
	13.46	[.530]	1-147070-4
	13.21	[.520]	1-147070-3
	12.95	[.510]	1-147070-2
	12.70	[.500]	1-147070-1
	12.45	[.490]	1-147070-0
	12.19	[.480]	147070-9
	11.94	[.470]	147070-8
	11.68	[.460]	147070-7
	11.43	[.450]	147070-6
	11.18	[.440]	147070-5
	10.92	[.430]	147070-4
	10.67	[.420]	147070-3
	10.41	[.410]	147070-2
	10.16	[.400]	147070-1
A			PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG B. HAYMAKER	23JUN00	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		CHK M. CHIANG	4SEP98		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPROD M. CHIANG		NAME	
		PRODUCT SPEC		.045 SQUARE CONTINUOUS POST, TIN	
	0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± 0.13 [.005] 4. PLC ± - ANGLES ± -	APPLICATION SPEC		SIZE	
		114-13011		CAGE CODE DRAWING NO	
MATERIAL BRASS	FINISH 	WEIGHT -		A1 00779 C 147070	
		CUSTOMER DRAWING		RESTRICTED TO -	
			SCALE 10:1	SHEET 1 OF 1	REV J