

HMC601LP4 / 601LP4E

v01.0509




75 dB, FAST SETTLING, LOGARITHMIC DETECTOR / CONTROLLER 10 - 4000 MHz

Typical Applications

The HMC601LP4(E) is ideal for IF and RF applications in:

- Cellular/PCS/3G
- WiMAX, WiBro & Fixed Wireless
- Power Monitoring & Control Circuitry
- Receiver Signal Strength Indication (RSSI)
- Automatic Gain & Power Control Circuits

Functional Diagram



Features

Wide Dynamic Range: up to 75 dB

Fast Pulse Response: 15/34ns (Rise/Fall Time)

Flexible Supply Voltage: +2.7V to +5.5V

Power-Down Mode

Excellent Stability over Temperature

Compact 4x4mm Leadless SMT Package

General Description

The HMC601LP4(E) Logarithmic Detector/Controller converts RF signals at its input, to a proportional DC voltage at its output. The HMC601LP4(E) employ a successive compression topology which delivers extremely high dynamic range and conversion accuracy over a wide input frequency range. As the input power is increased, successive amplifiers move into saturation one by one creating an accurate approximation of the logarithm function. The output of a series of square law detectors is summed, converted into voltage domain and buffered to drive the LOGOUT output. For detection mode, the LOGOUT pin is shorted to the VSET input, and will provide a nominal logarithmic slope of 19mV/dB and an intercept of -100dBm. The HMC601LP4(E) can also be used in the controller mode where an external voltage is applied to the VSET pin, to create an AGC or APC feedback loop. The HMC601LP4(E) provides a 15/34ns (rise/fall time) response time enabling RF burst detection to a pulse rate beyond 20 MHz.

Electrical Specifications, $T_A = +25C$, PWD = 0V, Vcc1, Vcc2 = +3.3V [1]

| Parameter | Тур. | Тур. | Тур. | Тур. | Тур. | Тур. | Тур. | Тур. | Units |
|---|------|------|------|------|-------|-------|------|------|--------|
| Input Frequency | 50 | 100 | 500 | 900 | 1900 | 2500 | 3500 | 4000 | MHz |
| ±3 dB Dynamic Range | 74 | 74 | 74 | 74 | 70 | 68 | 54 | 52 | dB |
| ±3 dB Dynamic Range Center | -31 | -31 | -31 | -31 | -31.5 | -31.5 | -27 | -23 | dBm |
| ±1 dB Dynamic Range | 68 | 68 | 69 | 69 | 67 | 65 | 47 | 46 | dB |
| Output Slope | 19.5 | 19.4 | 19.2 | 19.1 | 19.0 | 19.4 | 20.9 | 19.6 | mV/dB |
| Output Intercept | -99 | -99 | -100 | -100 | -98 | -96 | -85 | -79 | dBm |
| Temperature Sensitivity @ -10 dBm Input [2] | -4.2 | -3.8 | -3.5 | -2.4 | -0.8 | -0.8 | -4.4 | -3.5 | mdB/°C |

[1] Detector mode measurements; LOGOUT (Pin 17) is shorted to VSET (Pin 16).

[2] Measured from $T_A = -40C$ to $T_A = +85C$

| Parameter | Conditions | Min. | Тур. | Max. | Units |
|---------------------|---------------------------------------|------|------|------|-------|
| RF Input (INP) | | | | | |
| Return Loss | F = 10 - 4000 MHz, Zo = 50Ω, See plot | | 10 | | dB |
| LOGOUT Interface | | | | | |
| Open Loop Impedance | (Simulated) | | 12 | | kΩ |

HMC601* PRODUCT PAGE QUICK LINKS

Last Content Update: 11/29/2017

COMPARABLE PARTS 🖵

View a parametric search of comparable parts.

EVALUATION KITS

• HMC601LP4 Evaluation Board

DOCUMENTATION

Data Sheet

• HMC601 Data Sheet

TOOLS AND SIMULATIONS 🖳

HMC601 S-Parameters

REFERENCE MATERIALS 🖵

Product Selection Guide

 RF, Microwave, and Millimeter Wave IC Selection Guide 2017

Quality Documentation

- Package/Assembly Qualification Test Report: LP4, LP4B, LP4C, LP4K (QTR: 2013-00487 REV: 04)
- Package/Assembly Qualification Test Report: Plastic Encapsulated QFN (QTR: 05006 REV: 02)
- Semiconductor Qualification Test Report: BiCMOS-A (QTR: 2013-00235)

DESIGN RESOURCES

- HMC601 Material Declaration
- PCN-PDN Information
- · Quality And Reliability
- · Symbols and Footprints

DISCUSSIONS

View all HMC601 EngineerZone Discussions.

SAMPLE AND BUY 🖵

Visit the product page to see pricing options.

TECHNICAL SUPPORT

Submit a technical question or find your regional support number.

DOCUMENT FEEDBACK \Box

Submit feedback for this data sheet.

This page is dynamically generated by Analog Devices, Inc., and inserted into this data sheet. A dynamic change to the content on this page will not trigger a change to either the revision number or the content of the product data sheet. This dynamic page may be frequently modified.





75 dB, FAST SETTLING, LOGARITHMIC DETECTOR / CONTROLLER 10 - 4000 MHz


Electrical Specifications, (continued)

| Parameter | Conditions | Min. | Тур. | Max. | Units |
|---|---------------------------------------|-----------|------------|-----------|-------|
| Current Drive (Source) | | | 0.55 | | mA |
| Current Drive (Sink) | For 1% change in the output voltage | | 4.8 | | mA |
| Output Voltage Range | | 0 | | Vcc -0.13 | V |
| Small Signal Response Time (10% to 90%) | Pin = -60 to -57 dBm | | 8 | | ns |
| Large Signal Response Time (±0.5 dB Settling) | Pin = No Signal to 0 dBm | | 50 | | ns |
| Output Rise Time | From 0% to 90% | | 15 | | ns |
| Ripple | Fin = 100 MHz | | <4 | | mVpp |
| VSET Interface | | | | | |
| Input Impedance | | | 30 | | kΩ |
| Input Voltage Range | | | 0.6 to 1.9 | | V |
| Low Frequency Gain | VSET to LOGOUT | | 75 | | dB |
| Open Loop Corner Frequency | | | 4.4 | | kHz |
| Power Down (PWD) Interface | | | | | |
| Voltage Range for Normal Mode | | 0 | | 0.2 x Vcc | V |
| Voltage Range for Shutdown Mode | | 0.8 x Vcc | | Vcc | V |
| Threshold Voltage | | | Vcc/2 | | V |
| Power-up Response Time | 50% PWD to ±0.5 dB Settling of LOGOUT | | 19.9 | | μs |
| Power-Down Response Time | 50% PWD to 10% Icc | | 2.2 | | μs |
| Power Supply (Vcc1, Vcc2) | | | | | |
| Operating Voltage Range | | 2.7 | | 5.5 | V |
| Supply Current in Normal Mode | Vcc = +3.3V, PWD = 0V | | 30 | 36 | mA |
| Supply Current in Power Down Mode | Vcc = +3.3V, PWD = Vcc | | 1 | | mA |


Test Conditions

| Parameter | Condition | |
|---|-----------|--|
| Vcc1, Vcc2 | +3.3V | |
| Input Zo | 50Ω | |
| T _A | +25C | |
| Fin 900 MHz | | |
| INN Port connected to ground through a 1000pF capacitor | | |

LOGOUT Voltage & Error vs. Input Power, Fin = 10 MHz



LOGOUT Voltage & Error vs. Input Power, Fin = 50 MHz



Unless otherwise noted: Vcc1, Vcc2 = +3.3V, TA = +25C

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.


For price, delivery, and to place orders: Analog Devices, Inc., One Technology Way, P.O. Box 9106, Norwood, MA 02062-9106 Phone: 781-329-4700 • Order online at www.analog.com Application Support: Phone: 1-800-ANALOG-D






75 dB, FAST SETTLING, LOGARITHMIC DETECTOR / CONTROLLER 10 - 4000 MHz

LOGOUT Voltage & Error vs. Input Power, Fin = 100 MHz




v01.0509


LOGOUT Voltage & Error vs. Input Power, Fin = 500 MHz




LOGOUT Voltage & Error vs. Input Power, Fin = 900 MHz




LOGOUT Voltage & Error vs. Input Power, Fin = 1900 MHz



LOGOUT Voltage & Error vs. Input Power, Fin = 2500 MHz



LOGOUT Voltage & Error vs. Input Power, Fin = 3500 MHz




Unless otherwise noted: Vcc1, Vcc2 = +3.3V, $T_A = +25C$

ANALOGDEVICES

ROHS√


75 dB, FAST SETTLING, LOGARITHMIC DETECTOR / CONTROLLER 10 - 4000 MHz

LOGOUT Voltage & Error vs. Input Power, Fin = 4000 MHz




v01.0509


LOGOUT Slope vs. Frequency, Vcc = 3.3V




LOGOUT Slope vs. Supply Voltage, $T_A = +25C$




LOGOUT Intercept vs. Frequency, Vcc = 3.3V



LOGOUT Intercept vs. Supply Voltage $T_A = +25C$




LOGOUT Error vs. Input Power, Normalized [2], Fin = 1900 MHz




Unless otherwise noted: Vcc1, Vcc2 = +3.3V, $T_A = +25C$

75 dB, FAST SETTLING, LOGARITHMIC **DETECTOR / CONTROLLER 10 - 4000 MHz**




Input Return Loss vs. Frequency



Absolute Maximum Ratings

| Vcc1, Vcc2 | 0V to +5.5V |
|---|----------------|
| PWD | 0V to +5.5V |
| VSET Input Voltage | 0V to +5.5V |
| LOGOUT Output Current | 3 mA |
| RF Input Power | +12 dBm |
| Junction Temperature | 125 °C |
| Continuous Pdiss (T = 85°C) (Derate 7.95 mW/°C above 85°C) | 0.32 Watts |
| Thermal Resistance (R _{th}) (junction to lead) | 126 °C/W |
| Storage Temperature | -65 to +150 °C |
| Operating Temperature | -40 to +85 °C |
| ESD Sensitivity (HBM) | Class 1C |
| | |

LOGOUT Voltage vs. Input Power & Frequency, $T_A = +25C$





4. PAD BURR LENGTH SHALL BE 0.15mm MAXIMUM.

PAD BURR HEIGHT SHALL BE 0.05mm MAXIMUM.

5. PACKAGE WARP SHALL NOT EXCEED 0.05mm.

ELECTROSTATIC SENSITIVE DEVICE OBSERVE HANDLING PRECAUTIONS

[1] Unless otherwise noted: Vcc1, Vcc2 = +3.3V, $T_A = +25C$ [2] This data is relative to the room temperature performance of the HMC601LP4

Outline Drawing

.003[0.08] C

BOTTOM VIEW .161 4.10 .153 3.90 -.016 [0.40] REF 0.30 .008 [0.20] MIN 19 PIN 1 <u>HNNN</u> XXXX 13 EXPOSED LOT NUMBER **GROUND** PADDLE **SQUARE** NOTES: 0.05 1. LEADFRAME MATERIAL: COPPER ALLOY 2. DIMENSIONS ARE IN INCHES [MILLIMETERS]. SEATING 3. LEAD SPACING TOLERANCE IS NON-CUMULATIVE

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

PLANE

-C-

6. ALL GROUND LEADS AND GROUND PADDLE MUST BE SOLDERED TO PCB RF GROUND. 7. REFER TO HITTITE APPLICATION NOTE FOR SUGGESTED PCB LAND PATTERN.







75 dB, FAST SETTLING, LOGARITHMIC DETECTOR / CONTROLLER 10 - 4000 MHz

Package Information

| Part Number | Package Body Material | Lead Finish | MSL Rating | Package Marking [3] |
|-------------|--|---------------|------------|---------------------|
| HMC601LP4 | Low Stress Injection Molded Plastic | Sn/Pb Solder | MSL1 [1] | H601 XXXX |
| HMC601LP4E | RoHS-compliant Low Stress Injection Molded Plastic | 100% matte Sn | MSL1 [2] | H601 XXXX |

- [1] Max peak reflow temperature of 235 $^{\circ}\text{C}$
- [2] Max peak reflow temperature of 260 °C
- [3] 4-Digit lot number XXXX

Pin Descriptions


| Pin Number | Function | Description | Interface Schematic |
|--------------------------|------------|---|---|
| 1, 6, 7-13, 15, 18-24 | N/C | These pins are not connected internally; however, this product is specified with these pins connected to RF/DC ground. | |
| 2, 5 | Vcc1, Vcc2 | Bias supply. Connect supply voltage to both pins. | Vcc 1, O |
| 3, 4 | INP, INN | RF Input pins. Connect RF to INP, and AC couple INN to ground for single-ended operation. | INP 0 50Ω INNO |
| 14 | PWD | Apply PWD >0.8xVcc to initiate a power saving shutdown mode. To ensure proper start-up apply the power-up sequence shown in the "Power-Up Timing Diagram" attached to the application circuit. | PWD O———————————————————————————————————— |
| 16 | VSET | VSET input in controller mode. Short this pin to LOGOUT for detector mode. | LOGOUT 15KO |
| 17 | LOGOUT | Logarithmic output that converts the input power to a DC level in detector mode. Short this pin to VSET for detector mode. | VSET |
| Package Base | GND | Exposed paddle must be connected to RF and DC ground. | GND = |





75 dB, FAST SETTLING, LOGARITHMIC DETECTOR / CONTROLLER 10 - 4000 MHz

Evaluation PCB



List of Materials for Evaluation PCB 115242 [1]

| Item | Description | |
|---------|---|--|
| J1 - J4 | PC Mount SMA Connector | |
| J5 - J8 | DC Pin | |
| C1, C2 | 1000 pF Capacitor, 0402 Pkg. | |
| C3, C4 | 0.1μF Capacitor, 0402 Pkg. | |
| R1, R2 | 5.6Ω Resistor, 0603 Pkg. | |
| R3-R5 | 0Ω Resistor, 0603 Pkg. | |
| U1 | HMC601LP4 / HMC601LP4E Logarithmic Detector / Controller | |
| PCB [2] | 115244 Evaluation PCB | |

[1] Reference this number when ordering complete evaluation PCB

[2] Circuit Board Material: Rogers 4350


The circuit board used in the final application should use RF circuit design techniques. Signal lines should have 50 ohm impedance while the package ground leads and exposed paddle should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation circuit board shown is available from Hittite upon request.





75 dB, FAST SETTLING, LOGARITHMIC DETECTOR / CONTROLLER 10 - 4000 MHz

Application & Evaluation PCB Schematic



Notes

- Note 1: The HMC601LP4 & HMC601LP4E evaluation boards are pre-assembled for single-ended input, and detector/RSSI mode.
- Note 2: For single-ended input operation, use the INP port and make no connection to INN. INN is AC coupled to ground by C2
- Note 3: For differential input, remove C2, and install a 1000pF capacitor in series with INN at location shown.
- Note 4: For detector mode, connect high impedence volt meter to the LOGOUT port, and make no connection to VSET. LOGOUT is shorted to VSET by R3, as required for detector mode.
- Note 5: For controller mode, remove R3 and make appropriate connection to LOGOUT and VSET. In controller mode, the LOGOUT output can be used to drive a variable gain amplifier, or a variable attenuator, either directly or through a buffer or microcontroller. VSET should be connected to an external supply, typically between +0.6 and +1.9V.

Power-Up Timing Diagram

