



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19

© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

M	LOC	DIST	P	F	REVISIONS				
					ZONE	LTR	DESCRIPTION	DATE	APPD
-	GP	00				G	REV PER OUE0-0037-01	17OCT01	JR



1 TO PREVENT THREAD STRIPPING, SCREW TORQUE SHOULD NOT EXCEED 9 IN LBS.

2 TAP HOLE IS 6-32UNC-2B, TWO MIN THREADS.

.050±.005 DIA

SECTION A-A

SCALE 10:1

10 PLACES

SUPSD BY -2	YES	55673-2
	NO	55673-1
	SCREW	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± 3 PLC DEC ± .010 ANGLES ±	DR L. BRINER 4/1/97	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
	CHK H. JAMSHIDIAN 4/1/97		
	APPD H. JAMSHIDIAN 4/1/97	NAME TAP ASSEMBLY, POWER DISTRIBUTION	
	APPD H. JAMSHIDIAN 4/1/97		
MATERIAL HOUSING: NYLON TAP: COPPER ALLOY 725, .025 THICK	PRODUCT SPEC	SIZE B	FSCM NO 00779
FINISH TAP: .000150 TIN-LEAD OVER .000050 NICKEL	APPLICATION SPEC	DRAWING NO 55673	
	WEIGHT	SCALE 4:1	SHEET 1 OF 1