



PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
70229-X01/X01LF	1.6	2.90
70229-X11/X11LF	2.4	3.53




NOTE 8




PLATING CONTACT AREA:

PRODUCT NR:	PERFORMANCE LEVEL:
70229-1YZ/1YZLF	TELCORDIA CD
70229-2YZ/2YZLF	CUSTOMER SPECIAL
70229-3YZ/3YZLF	CUSTOMER SPECIAL




PRODUCT AFTER HOT RIVETTING.



NOTES:


- BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- TERMINAL MATERIAL: PHOSPHOR BRONZE.
- PLATING SOLDER TAILS 2-8 μ m SnPb 90-97 OR 2-8 鎢 PURE Sn
- INDICATED HOLES ARE UNPLATED.
- PRODUCT MARKING: PART NUMBER & BATCH ID.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK
TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER
APPLICATION.
- DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE
BOTH SIDES OF PRODUCT.




RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltr	ecdn	nddr	date	linear		projection	title	www.fciconnect.com	
K	DG04-0104	CLU	04/221						
L	DG06-0477	Cenh	11/20/06						
M	DG07-0168	Cenh	05/08/07	angles					
N	DG09-0068	Cenh	06/06/09	dr	Avan Zanten	900918			
				engr	H. Bouwknegt	940308			
H	V00578	LLA	000316	chr	A van Zanten	900918			
J	V00847	LLA	000530	app	H van Voensel	900918			
sheet	revision	N	N	N					
index	sheet	1	2	3					

PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM"A"
70229-X02/X02LF	1.6	2.90
70229-X12/X12LF	2.4	3.53





NOTE 10




PLATING CONTACT AREA:

PRODUCT NR:	PERFORMANCE LEVEL:
70229-1YZ/1YZLF	TELCORDIA CO
70229-2YZ/2YZLF	CUSTOMER SPECIAL
70229-3YZ/3YZLF	CUSTOMER SPECIAL




PRODUCT AFTER HOT RIVETTING.



NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 μ m SnPb 90-97 OR 2-8 鍍 PURE Sn
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PARTNUMBER & BATCH ID.
- 6 SET BACK FOR PRESS BLOCK.
- 7 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
- 8 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 9 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
10. DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.



14.64 REF. SEE NOTE 6




RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
ltn	ecn	addr	date	linear	projection	title	www.fciconnect.com
N					1	RA FEMALE SIGNAL STB 48 mm VERSION	
				angles	mm	product family METRAL(tm)	code 213
		dr	D. de Bil	970529		size dwg no	sheet 2 of 2
		engr	P. Schalk	970529		scale 5:1	
		chr	P. Schalk	970529			
		appd	H. Coolmans	970529			
sheet	revision						
Index	sheet						


PC BOARD VERSIONS		
PRODUCTNR:	PCB THICKNESS	DIM "A"
70229-X03/X03LF	1.6	2.90
70229-X13/X13LF	2.4	3.53



PLATING CONTACT AREA:	
PRODUCT NR:	PERFORMANCE LEVEL:
70229-1YZ/1YZLF	TELCORDIA CO
70229-2YZ/2YZLF	CUSTOMER SPECIAL
70229-3YZ/3YZLF	CUSTOMER SPECIAL




PRODUCT AFTER HOT RIVETTING.



NOTES:

- BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS
FLAME RETARDANT ACC. UL 94-V0
- TERMINAL MATERIAL: PHOSPHOR BRONZE.
- PLATING SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn
- INDICATED HOLES ARE UNPLATED.
- PRODUCT MARKING: PART NUMBER & BATCH ID.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.
- DIAMOND LOCATION PEG ARE ONLY EXISTED ON THE BOTH SIDES OF PRODUCT.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
l	tr	ec	n	dd	date	linear	projection
N							title
						angles	RA FEMALE SIGNAL
						dr Heaven Cen 11/20/06	STB 48 mm VERSION
						engr Collins Lu 11/20/06	product family METRAL(tm)
						chr Beer Fu 11/20/06	code 213
						appd Joseph Hsia 11/20/06	sheet 3 of-
sheet	revision	scale 5:1		A2	70229		
index	sheet						