



19

LOC		DIST		REVSIONS			
P	F	ZONE	LTR	DESCRIPTION	DATE	APPO	1 ST DAP
			A	REV & REDRAWN PER 0720-0008-93	2-2-93		



1 STAMP AMP APPROX AS SHOWN

AMP WIRE RANGE	 E13288 Listed
26-22 AWG STRANDED	NOT LISTED

 LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.1-0.41mm ² [202-810] CIR MILS STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE CONTROLLING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm (INCHES) TOLERANCES ON : 2 PLC DEC # - 3 PLC DEC # - ANGLES # -		DR 2-2-93 TA BRINKMAN CHK 2-2-93 DA PATTERSON APPD 2-2-93 DE MILLER APPD 2-2-93 JL MECKLEY PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		 AMP Incorporated Harrisburg, PA 17105-3608	
FINISH TIN PLATE 0.00254L 0.000100J MIN THK PER MIL-T-10727		MATERIAL COPPER PER ASTM B-152 ANNEALED		NAME TERMINAL, RING TONGUE, BUDGET	
SIZE CAGE CODE DRAWING NO		SCALE 10:1 SHEET 1 OF 1			
C 00779 C-33695					