








spec ref		*		dr	Peng-Bing Fu	2012/04/25	projection 	MM 	size	A3	scale	3:2
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Peng-Bing Fu	2012/11/14			ecn no		ELX-DG-013143-1	
				chr	Shao-Qi Kuang	2012/11/15			rel level		Released	
				appr	Pei-Ming Zheng	2012/11/15			product family		PwrBlade+	
surface	✓	linear	0.X	±0.5		title	4ACP	dwg no	10106262-4000001	rev	B	
			0.XX	±0.25								
			0.XXX	±0.10								
ASME Y14.5	angular	0°	±2°	www.fci.com	cat. no.		Product - Customer Drw			sheet 1 of 3		

A

B

C

D

A

B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE P/N CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025 MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07 MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.
- B

9) A

B

SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW, OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.



Copyright FCI.

dr	Peng-Bing Fu	2012/04/25	projection	MM	size	A3	scale	3:2
eng	Peng-Bing Fu	2012/11/14						
chr	Shao-Qi Kuang	2012/11/15						
appr	Pei-Ming Zheng	2012/11/15	product family		PwrBlade+	ecn no	ELX-DG-013143-1	
					rel level	Released		
www.fci.com			FCi title 4ACP RA STB HEADER		dwg no 10106262-4000001		rev B	
cat. no.			Product - Customer Drw			sheet 3 of 3		