


BCR5PM

LOW POWER USE
INSULATED TYPE, PLANAR PASSIVATION TYPE


BCR5PM



- I_T (RMS) 5A
- V_{DRM} 400V/600V
- I_{FGT} I , I_{RGT} I , I_{RGT} III 20mA (10mA) *5
- V_{iso} 1500V
- UL Recognized: File No. E80276

OUTLINE DRAWING

Dimensions
in mm



APPLICATION

Switching mode power supply, light dimmer, electric flasher unit,
control of household equipment such as TV sets · stereo · refrigerator · washing machine · infrared
kotatsu · carpet, solenoid drivers, small motor control,
copying machine, electric tool,
other general purpose control applications

MAXIMUM RATINGS

Symbol	Parameter	Voltage class		Unit
		8	12	
V_{DRM}	Repetitive peak off-state voltage *1	400	600	V
V_{DSM}	Non-repetitive peak off-state voltage *1	500	720	V

Symbol	Parameter	Conditions	Ratings	Unit
I_T (RMS)	RMS on-state current	Commercial frequency, sine full wave 360° conduction, $T_c = 95^\circ\text{C}$	5	A
I_{TSM}	Surge on-state current	60Hz sinewave 1 full cycle, peak value, non-repetitive	50	A
I^2_t	I^2_t for fusing	Value corresponding to 1 cycle of half wave 60Hz, surge on-state current	10.4	A ² s
PGM	Peak gate power dissipation		3	W
PG (AV)	Average gate power dissipation		0.3	W
VGM	Peak gate voltage		10	V
IGM	Peak gate current		2	A
T_j	Junction temperature		-40 ~ +125	°C
T_{stg}	Storage temperature		-40 ~ +125	°C
—	Weight	Typical value	2.0	g
V_{iso}	Isolation voltage	$T_a = 25^\circ\text{C}$, AC 1 minute, T1 · T2 · G terminal to case	1500	V

*1. Gate open.

BCR5PM

MEDIUM POWER USE
INSULATED TYPE, PLANAR PASSIVATION TYPE

ELECTRICAL CHARACTERISTICS

Symbol	Parameter	Test conditions	Limits			Unit
			Min.	Typ.	Max.	
I_{DRM}	Repetitive peak off-state current	$T_J=125^{\circ}\text{C}$, V_{DRM} applied	—	—	2.0	mA
V_{TM}	On-state voltage	$T_C=25^{\circ}\text{C}$, $I_{TM}=7\text{A}$, Instantaneous measurement	—	—	1.8	V
$V_{FGT\text{ I}}$	Gate trigger voltage *2	$T_J=25^{\circ}\text{C}$, $V_D=6\text{V}$, $R_L=6\Omega$, $R_G=330\Omega$	—	—	1.5	V
$V_{RGT\text{ I}}$			—	—	1.5	V
$V_{RGT\text{ III}}$			—	—	1.5	V
$I_{FGT\text{ I}}$	Gate trigger current *2	$T_J=25^{\circ}\text{C}$, $V_D=6\text{V}$, $R_L=6\Omega$, $R_G=330\Omega$	—	—	20*5	mA
$I_{RGT\text{ I}}$			—	—	20*5	mA
$I_{RGT\text{ III}}$			—	—	20*5	mA
V_{GD}	Gate non-trigger voltage	$T_J=125^{\circ}\text{C}$, $V_D=1/2V_{DRM}$	0.2	—	—	V
$R_{th(j-c)}$	Thermal resistance	Junction to case *4	—	—	4.0	$^{\circ}\text{C/W}$
$(dv/dt)_c$	Critical-rate of rise of off-state commutating voltage		*3	—	—	V/ μs

*2. Measurement using the gate trigger characteristics measurement circuit.

*3. The critical-rate of rise of the off-state commutating voltage is shown in the table below.


*4. The contact thermal resistance $R_{th(c-f)}$ in case of greasing is 0.5°C/W .

*5. High sensitivity ($I_{GT}\leq 10\text{mA}$) is also available. (IGT item ①)


Voltage class	V_{DRM} (V)	$(dv/dt)_c$			Test conditions	Commutating voltage and current waveforms (inductive load)
		Symbol	Min.	Unit		
8	400	R	—	V/ μs	1. Junction temperature $T_J=125^{\circ}\text{C}$ 2. Rate of decay of on-state commutating current $(di/dt)_c=-2.5\text{A/ms}$ 3. Peak off-state voltage $V_D=400\text{V}$	
		L	5			
12	600	R	—			
		L	5			

PERFORMANCE CURVES

MAXIMUM ON-STATE CHARACTERISTICS









RATED SURGE ON-STATE CURRENT









BCR5PM

MEDIUM POWER USE
INSULATED TYPE, PLANAR PASSIVATION TYPE







BCR5PM

MEDIUM POWER USE
INSULATED TYPE, PLANAR PASSIVATION TYPE



BCR5PM

MEDIUM POWER USE
INSULATED TYPE, PLANAR PASSIVATION TYPE



GATE TRIGGER CHARACTERISTICS TEST CIRCUITS

