




Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

228433-5 Product Details

Share Print Email



228433-5

Curing Ovens, Epoxy and Hand Polishing Products

- Product Highlights:
- Accessory
 - Region = Asia, EMEA
 - Accessory Type = Hand Polishing Film
 - Polishing Film Type = 0.3 µm
 - For Use With AMP SC

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

TE Internal Number: 228433-5



Active

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none">• LAPPING FILM, OPTIMATE (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none">• Enterprise Networks EMEA Product Catalog (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none">• None Available <p>Application Specifications:</p> <ul style="list-style-type: none">• None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none">• None Available <p>CAD Files:</p> <ul style="list-style-type: none">• None Available <p>List all Documents</p>	<p>Related Products:</p> <ul style="list-style-type: none">• Tooling

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none">• Product Type = Accessory• Accessory Type = Hand Polishing Film• Size = 215.90 x 279.40 [8.5 x 11] <p>Body Features:</p> <ul style="list-style-type: none">• Polishing Film Type = 0.3 µm• Polishing Film Grit Material = Aluminum Oxide• Polishing Film Color = White <p>Configuration Features:</p> <ul style="list-style-type: none">• Number of Connectors (Approximate) = 60-80 <p>Industry Standards:</p> <ul style="list-style-type: none">• RoHS/ELV Compliance = Not relevant for RoHS and/or ELV compliance• Lead Free Solder Processes = Not relevant for lead free process	<p>Conditions for Usage:</p> <ul style="list-style-type: none">• For Use With = AMP SC <p>Packaging Features:</p> <ul style="list-style-type: none">• Packaging Quantity = 100 Sheets <p>Product Availability:</p> <ul style="list-style-type: none">• Region = Asia, EMEA <p>Other:</p> <ul style="list-style-type: none">• Brand = AMP

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

LOC	DIST	REVISIONS					
CE	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L	ECR-05-015022	21DEC05	KG	DK

△₁ P/N 228433-6 CONTAINS 2 SHEETS OF EACH OF THE FOLLOWING TYPES:
0.3um ALUMINUM OXIDE, 8.5 x 11
1um ALUMINUM OXIDE, 8.5 x 11
5um SILICON CARBIDE, 8.5 x 11
15um SILICON CARBIDE, 8.5 x 11

OBSOLETE	10	5um SILICON CARBIDE, 5.5 x 8.5	1-228433-6
OBSOLETE	10	0.3um ALUMINUM OXIDE,5.5 x8.5	1-228433-5
OBSOLETE	2	15um SILICON CARBIDE, 8.5 x 11	1-228433-4
OBSOLETE	100	1um ALUMINUM OXIDE, 8.5 x 11	1-228433-3
OBSOLETE	10	15um SILICON CARBIDE, 4.5 x 11	1-228433-2
OBSOLETE	10	5um SILICON CARBIDE, 4.5 x 11	1-228433-1
OBSOLETE	10	1um SILICON CARBIDE, 4.5 x 11	1-228433-0
	100	15um SILICON CARBIDE, 8.5 x 11	228433-9
	100	5um SILICON CARBIDE, 8.5 x 11	228433-8
	100	1um ALUMINUM OXIDE, 8.5 x 11	228433-7
OBSOLETE	8	△ ₁	228433-6
	100	0.3um ALUMINUM OXIDE, 9 x 11	228433-5
SUPERCEDED BY 228433-7	10	1um ALUMINUM OXIDE, 9 x 11	228433-4
SUPERCEDED BY 228433-8	10	5um SILICON CARBIDE, 9 x 11	228433-3
SUPERCEDED BY 228433-9	10	15um SILICON CARBIDE, 9 x 11	228433-2

		MINIMUM ORDER QUANTITY		GRIT GRADE AND TYPE				PART NO			
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN K. GLATFELTER 14DEC2005		<div><div>tyco</div><div>Electronics</div></div> <div>Tyco Electronics Corporation Harrisburg, PA 17105-3608</div>					
				CHK D. KIRSCH 20DEC2005							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD D. KIRSCH 20DEC2005		NAME LAPPING FILM, OPTIMATE -					
				PRODUCT SPEC -							
				APPLICATION SPEC -							
				SIZE A3		CAGE CODE 00779		DRAWING NO C-228433		RESTRICTED TO -	
				MATERIAL -		FINISH -		WEIGHT -		CUSTOMER DRAWING	
						SCALE NTS		SHEET 1 OF 1		REV L	