


	1	2	3	4	5	6	7																																																																																																									
A	PLUG COMPONENT			PLUG STRIP DIMENSION			SJT 16AWGx3C 60°C Unshielded Black	END STRIP DIMENSION			CONNECTOR COMPONENT																																																																																																					
	COLOR	DESCRIPTION	Q'ty	R.I.J	R.O.J	COLOR		R.O.J	R.I.J	COLOR	COLOR	DESCRIPTION	Q'ty																																																																																																			
	40P BLACK	IH-500(320 C14)	1	6 ⁺¹ ₋₀	19 ± 1	BLACK(L)		6 ⁺¹ ₋₀	15 ± 1	BLACK(L)	40P BLACK	IH-501(320 C13)	1																																																																																																			
	Nickel-Plated	GEM 98672BS-1	3	6 ⁺¹ ₋₀	19 ± 1	WHITE(N)		6 ⁺¹ ₋₀	15 ± 1	WHITE(N)	True color	Assembly Body 111-001-005	1																																																																																																			
	BLACK Outer Body	GEM 8671P	1	6 ⁺¹ ₋₀	19 ± 1	GREEN(E)	6 ⁺¹ ₋₀	15 ± 1	GREEN(E)																																																																																																							
B													B																																																																																																			
C													C																																																																																																			
D													D																																																																																																			
E													E																																																																																																			
F	28.75±0.25 24.25±0.25 20.75±0.25 BLACK WHITE GREEN COPPER CONDUCTOR(N/mm): 26/0.254±0.003 or Substitute PVC INSULATION AVERAGE THICKNESS: 0.76mm ID: 3.05±0.1mm PVC JACKET AVERAGE THICKNESS: 0.76mm OD: 8.3±0.2mm Wire cross section 13A 125V~ E200855 LL114612 Black Marking 250±35 Hank Dimension Material: • SJT 3x16AWG(1.31mm²) VW-1, 60° 300V • Jacket color: Black • E- Green; L- Black; N- White Electrical: • 100% short & open testing • Insulation Resistance: 100Ω Min. • Voltage: 500V DC/1 minute												F																																																																																																			
G	<table><tr><td>Scale</td><td>Free</td><td></td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td colspan="3">Title</td></tr><tr><td colspan="2">TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>27.11.13</td><td>Wilson</td><td colspan="3">Power Cord Extension</td></tr><tr><td>X.</td><td>±0.3</td><td></td><td></td><td></td><td></td><td></td><td rowspan="3">Approved</td><td rowspan="3">27.02.13</td><td rowspan="3">Groll</td><td colspan="3">SJT, 16AWG, 60°C, Male/Female, 2 Meters</td></tr><tr><td>X.X</td><td>±X</td><td></td><td></td><td></td><td></td><td colspan="3">ASSMANN WSW-No.</td></tr><tr><td>X.XX</td><td>±X</td><td></td><td></td><td></td><td></td><td colspan="3">AK500/16-OE-11-2</td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td>Drawing-No.</td><td colspan="3">rev01</td></tr><tr><td>X.°</td><td>±X°</td><td rowspan="2">①</td><td rowspan="2">Change of manufacturer</td><td rowspan="2">27.11.13</td><td rowspan="2">Wilson</td><td rowspan="2">ASSMANN WSW components</td><td rowspan="2">1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us</td><td rowspan="2">Replace</td><td colspan="3">Sheet</td></tr><tr><td>X.X°</td><td>±X°</td><td colspan="3">1/1</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td colspan="7"></td></tr></table>												Scale	Free						Date	Name	Title			TOLERANCE							Drawn	27.11.13	Wilson	Power Cord Extension			X.	±0.3						Approved	27.02.13	Groll	SJT, 16AWG, 60°C, Male/Female, 2 Meters			X.X	±X					ASSMANN WSW-No.			X.XX	±X					AK500/16-OE-11-2			DIM	TOL								Drawing-No.	rev01			X.°	±X°	①	Change of manufacturer	27.11.13	Wilson	ASSMANN WSW components	1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us	Replace	Sheet			X.X°	±X°	1/1			Angle	TOL	Id.	Modification	Date	Name								G
Scale	Free						Date	Name	Title																																																																																																							
TOLERANCE							Drawn	27.11.13	Wilson	Power Cord Extension																																																																																																						
X.	±0.3						Approved	27.02.13	Groll	SJT, 16AWG, 60°C, Male/Female, 2 Meters																																																																																																						
X.X	±X					ASSMANN WSW-No.																																																																																																										
X.XX	±X					AK500/16-OE-11-2																																																																																																										
DIM	TOL								Drawing-No.	rev01																																																																																																						
X.°	±X°	①	Change of manufacturer	27.11.13	Wilson	ASSMANN WSW components	1840 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us	Replace	Sheet																																																																																																							
X.X°	±X°								1/1																																																																																																							
Angle	TOL	Id.	Modification	Date	Name																																																																																																											
H	RoHS Compliant												H																																																																																																			
	1	2	3	4	5	6	7																																																																																																									