



P	LTR	DESCRIPTION	DATE	DWN	APVD
	H1	REVISED PER ECO-15-001396	30JAN2015	NK	DR



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED	2/0 AWG SOLID OR STRANDED



- 1 STAMP AMP 2/0W* APPROX AS SHOWN.
- 2 TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545.
- 3 BRIGHT TIN LEAD PLATE 0.00254[.000100] MIN EXT THK PER B-545.
- 4 COPPER PER ASTM B-152, ANNEALED.
- 5 MEETS MS20659-136, CLASS 2.
- 6 NICKEL PLATE 0.00762[.00030] MIN EXT. THK. PER SAE AMS QQ-N-290.
- 7 NOT UL OR CSA APPROVED FOR STRANDED WIRE ONLY.

170°C[338°F]	50	LOOSE PIECE	3	2-321873-2
343°C[650°F]	50	LOOSE PIECE	6	321873-2
170°C[338°F]	50	LOOSE PIECE	2	321873
MAX RECOMMENDED OPERATING TEMP.	QTY	PACKAGE TYPE	FINISH	PART NO.

MAX. RECOMMENDED OPERATING TEMPERATURE:	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 1/14/94	 TE Connectivity						
SEE TABLE	DIMENSIONS:		CHK AJ KAUFMAN 1/19/94	NAME TERMINAL, RING TONGUE, SOLISTRAND						
VOLTAGE RATING: N/A	MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD JL MECKLEY 1/19/94							
CIRCULAR MIL AREA: 60.6–76.3mm ² [119,500–150,500] SOLID OR STRANDED		0 PLC ± – 1 PLC ± – 2 PLC ± 0.20[.008] 3 PLC ± – 4 PLC ± – ANGLES ± –	PRODUCT SPEC —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
	MATERIAL 	FINISH SEE TABLE	WEIGHT —					A2 00779  321873		
			CUSTOMER DRAWING		SCALE	2:1	SHEET	1 of 1	REV	H1