







Rating		21A 14VDC		Mounting Hole		Circuit Diagram	
Contact Resistance		50m ohm Max.					
Insulation Resistance		DC 500V 100M ohm Min.					
Dielectric Strength		AC 1500V 1 minute					
Operation Temperature		-25°~85°					
Switch Function		5P SPST OFF - ON Lamp		Thickness(mm)	X(mm)	Y(mm)	
				0.75~1.25	21.0 ^{+0.3} ₀	36.6+0.1	
				1.25~2.0		36.8+0.1	
				2.0~3.0		37.0+0.1	
Lamp Type		LED 1 - 12VDC 14V Independent w/resistor LED 2 - 12VDC 14V Dependent w/resistor					

Material:

1. Frame: Nylon-66(94V-2) - Black
Actuator: Nylon-66+33%GF - Black
Lens 1: PC, Amber
Lens 2: PC, Green
Terminal: Silver plated copper
(excepted lamp terminal)
Printed: None
2. Waterproof: "IP-67".



TOLERANCE: ±0.3mm UNLESS OTHERWISE SPECIFIED.

RoHS Compliant

3	Added Lamp Type. 12/19/2011.
2	Changed IP-66 to IP-67. 12/13/10
1	Switch Function OFF-ON was ON-OFF. 8/24/10.

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 5/20/10

Rev. 3

Unit: mm

Checked By: *G. Guld*

Title: **ROCKER SWITCH**

CW P/N: **GRB292A301BBAG1**