

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A12	REVISED PER ECO-17-001761	10MAY2017	RK	AS

TE LOGO

3

1

2

3

2A 250VAC

5A 120VAC

RATING

EPOXY SEAL

DATE CODE

04-YEAR

01-WEEK

AND

COUNTRY

OF ORIGIN

5

FUNCTION

ON ON

ALCO

8.89

[.350]

4.70±0.41

[.185±.016]

12.70

[.500]

6.86

[.270]

FUNCTION CHART

FUNCTION			
	1 2 3	1 2 3	1 2 3
01	ON	NONE	ON
03	ON	OFF	ON
05	(ON)	OFF	(ON)
07	ON	OFF	(ON)
08	ON	NONE	(ON)
TERMINALS CONNECTED	2-3	---	1-2

NONE: NO MECHANICAL POSITION

OFF: MECHANICAL POSITION WITH NO ELECTRICAL CONNECTION

(ON): MOMENTARY ACTION

SPECIFICATIONS

RATING, B CONTACTS	.4VA MAX @20V MAX. AC OR DC
RATING, G CONTACTS-SEE NOTE 2	.4VA MAX @20V MAX. AC OR DC OR
	5A @120 VAC OR 28 VDC (RESISTIVE)
	2A @250 VAC (RESISTIVE)
RATING, Q CONTACTS	5A @120 VAC OR 28 VDC (RESISTIVE)
	2A @250 VAC (RESISTIVE)
ELECTRICAL LIFE	6,000 CYCLES AT RATED LOAD
CONTACT RESISTANCE	10 MILLIOHMS MAX INITIAL @ 2-4VDC, 100MA
INSULATION RESISTANCE	1,000 MEGOHMS MIN
DIELECTRIC WITHSTANDING VOLTAGE	1,000 V RMS AT SEA LEVEL
OPERATING TEMPRATURE	-30C TO 85C

1 ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS).

2 G CONTACT OPTION CAN BE USED FOR SIGNAL OR POWER LEVEL SWITCHING. IF SWITCH IS USED AT LEVELS EXCEEDING .4VA @ 20V AC/DC, SWITCH IS RENDERED FOR POWER SWITCHING ONLY DUE TO ARC REMOVAL OF GOLD PLATING. RATING MARKED ON SWITCH IS 2A 250VAC, 5A 120VAC.

3 TE CONNECTIVITY LOGO PER PER TEC-202-36.

5 DATE CODE AND COUNTRY OF ORIGIN MAY APPEAR ON EITHER SIDE OF SWITCH.

6 PANEL MOUNT BRACKET SUPPLIED WITH TERMINALS W, Z AND Z3 ONLY.

7 ACTUATOR MARKED 0 -

8 ACTUATOR MARKED - 0

9 ACTUATOR MARKED -

10 ALL LOGO, RATING, DATE CODE, AND FUNCTION MARKINGS TO BE LASER MARKED.

11 OBSOLETE

12 GRAY ACTUATOR WITH MODIFIED BRACKET (SUPPORT BRACKET TRIMMED PARALLEL TO THE PCB)

PART NUMBER SEQUENCE CHART

MODEL	FUNCTION	ACTUATOR	TERMINAL	CONTACT	ACTUATOR COLOR	BEZEL COLOR	ROHS
A1							04
	01	J1	A	B	0 BLACK (STD)	0 BLACK (STD)	
	03	J3	AV2	G	1 BROWN	1 BROWN	
	05	J50	C	Q	2 RED	2 RED	
	07	J51	V3		3 ORANGE	3 ORANGE	
	08	J52	V4		4 YELLOW	4 YELLOW	
		J2	V6		5 GREEN	5 GREEN	
		J4	V7		6 BLUE	6 BLUE	
		J60	W		8 GRAY	8 GRAY	
		J61	W4		9 WHITE	9 WHITE	
		J62	Z				
			Z3				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.25[0.01]

4 PLC ± -

ANGLES ± 4°

FINISH -

MATERIAL -

DWN M.BINNER 06JAN05

CHK M.ZITTO 06JAN05

APVD M.ZITTO 06JAN05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

GEMINI A SERIES ROCKER SWITCH

SINGLE POLE

SIZE A2

CAGE CODE 00779

DRAWING NO C-1571986

RESTRICTED TO -







SCALE 2:1


SHEET 1 OF 5

REV A12


1471-9 (1/15)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN M.BINNER	06JAN05	 TE Connectivity		
			CHK M.ZITTO	06JAN05			
			APVD M.ZITTO	06JAN05			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		GEMINI A SERIES ROCKER SWITCH SINGLE POLE	
		0 PLC ± -		PRODUCT SPEC			
		1 PLC ± -		—			
		2 PLC ± -		APPLICATION SPEC			
		3 PLC ± 0.25[0.01]		—			
4 PLC ± -		—		SIZE		RESTRICTED TO	
MATERIAL		FINISH		WEIGHT		CAGE CODE	
-		-		-		DRAWING NO	
				A2 00779		1571986	
				CUSTOMER DRAWING		SCALE	
						2:1	
						SHEET	
						2 of 5	
						REV	
						A12	



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—




J2 SMALL




J4 LARGE



J60 SNAP-IN




J61 SNAP-IN WITH BEZEL




J62 SNAP-IN WITH BEZEL/L.E.D.

NOTE: L.E.D. NOT SUPPLIED




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	M.BINNER	06JAN05
DIMENSIONS:		CHK	M.ZITTO	06JAN05
mm [INCHES]		APVD	M.ZITTO	06JAN05
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
0 PLC		—		
1 PLC		—		
2 PLC		—		
3 PLC		—		
4 PLC		—		
ANGLES		—		
FINISH		—		
MATERIAL		—		
CUSTOMER DRAWING		—		
SCALE		2:1		
SHEET		3 OF 5		
REV		A12		



VERTICAL SUPPORT
BRACKET

OPTION CODE	DIM "A"
V3	11.68[.460]
V4	16.00[.630]



VERTICAL SUPPORT BRACKET

OPTION CODE	DIM "A"
V6	11.68[.460]
V7	16.00[.630]

