


## C14 IEC Inlet - Mini Bezel

### MINIMUM COMBINED BEZEL SIZE



- Inlet with 2.8, 4.8 or 6.3mm tags
- Horizontal Module Arrangement
- Single and Double Pole Switch Variations
- Filtered Inlet Option



### How to Order

**BZM xx / xxxxx / xx x**

| Type of Inlet / Outlet                                                                                                                  | Filtered or Non Filtered Inlet                                                                                                                                                                                                                                                    | Switch Variation                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | Panel Thickness                                                              |
|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------|
| C14 Power Inlet (cold condition), 6.3, 4.8 & 2.8mm tabs:<br><br><b>27</b> = PX0575/63<br><b>42</b> = PX0575/48<br><b>28</b> = PX0575/28 | Z0000 = Non Filtered<br>Axxxx = Standard<br>Bxxxx = Medical<br><br><div>                         For Filtered inlet use 6th to 9th characters from filter ordering code see pages 95-96.<br/><br/>                         E.g. BZM27/<b>A0120</b>/57B                     </div> | Single Pole Switch, 4.8mm or solder tab, marked I/O:<br><b>53</b> = S.P. Switch, 4.8mm tab (I/O)<br><b>54</b> = S.P. Switch, solder tab (I/O)<br><br>Single Pole Illuminated Switch, 4.8mm or solder tab:<br><b>55</b> = S.P. Switch Illum. Red, 4.8mm tab<br><b>61</b> = S.P. Switch Illum. Green, 4.8mm tab<br><b>56</b> = S.P. Switch Illum. Red, solder tab<br><b>62</b> = S.P. Switch Illum. Green, solder tab<br><br>Double Pole Switch, 4.8mm or solder tab, marked I/O:<br><b>57</b> = D.P. Switch, 4.8mm tab (I/O)<br><b>58</b> = D.P. Switch, solder tab (I/O)<br><br>Double Pole Illuminated Switch, 4.8mm or solder tab:<br><b>59</b> = D.P. Switch Illum. Red, 4.8mm tab<br><b>63</b> = D.P. Switch Illum. Green, 4.8mm tab<br><b>60</b> = D.P. Switch Illum. Red, solder tab<br><b>64</b> = D.P. Switch Illum. Green, solder tab<br><br>Double Pole High Inrush, 4.8mm tabs:<br><b>65</b> = D.P. High Inrush Switch, 4.8mm tabs (S.P. format)<br><br>Double Pole High Inrush, 4.8mm tabs, marked I/O:<br><b>68</b> = D.P. High Inrush Switch, 4.8mm tabs, I/O (S.P. format)<br><br>Single Pole Illuminated Switch, 4.8mm or solder tab, Marked I/O:<br><b>A1</b> = S.P. Switch Illum. Red, 4.8mm tab (I/O)<br><b>A5</b> = S.P. Switch Illum. Green, 4.8mm tab (I/O)<br><b>A2</b> = S.P. Switch Illum. Red, solder tab (I/O)<br><b>A6</b> = S.P. Switch Illum. Green, solder tab (I/O)<br><br>Double Pole Illuminated Switch, 4.8mm or solder tab, Marked I/O:<br><b>A3</b> = D.P. Switch Illum. Red, 4.8mm tab<br><b>A7</b> = D.P. Switch Illum. Green, 4.8mm tab<br><b>A4</b> = D.P. Switch Illum. Red, solder tab<br><b>A8</b> = D.P. Switch Illum. Green, solder tab | <b>1.0mm</b> = A<br><b>1.5mm</b> = B<br><b>2.0mm</b> = C<br><b>3.0mm</b> = D |

Note: For technical details of individual components please see page 74

Inlet Approvals:

