



LEDTECH ELECTRONICS CORP.

USA Sales Office  
19209 Parthenia Street - Suite D  
Northridge, CA 91324  
Phone: (818) 701-7240  
Fax: (818) 701-7217

# SPECIFICATION

*PART NO. : UA(C) 5641-11 EWRN*  
*0.56"(14.22mm)SINGLE DIGIT DISPLAY*



Approved by

Checked by


Prepared by

*Tung*

*Andy*

*Feng*


## Dimensions



### Notes:

1. The slope angle of any PIN may be  $\pm 5.0^\circ$  Max.
2. All dimensions are in mm, tolerance is  $\pm 0.25$ mm unless otherwise noted.

## Internal Circuit Diagram



**UA(C)5641-11****0.56" SINGLE DIGIT  
DISPLAY****Description**

Part No.	LED Chip		Face Color	
	Material	Emitting Color	Surface	Segments
UA5641-11 EWRN	GaAsP/GaP	Orange	Grey	White
UC5641-11 EWRN	GaAsP/GaP	Orange	Grey	White

**Absolute Maximum Ratings at Ta=25 °C**

Parameter	Symbol	Rating	Unit
Power Dissipation Per Segment	P <sub>D</sub>	78	mW
Pulse Current(1/10Duty Cycle,0.1ms Pulse Width.) Per Chip	I <sub>FP</sub>	100	mA
Forward Current Per Chip	I <sub>F</sub>	30	mA
Reverse (Leakage)Current Per Chip	I <sub>r</sub>	100	uA
Reverse Voltage Per Chip	V <sub>R</sub>	5	V
Operating Temperature Range	Topr.	-25 to +85	°C
Storage Temperature Range	Tstg.	-40 to +100	°C
Soldering Temperature.	Tsol.	Dip Soldering: 260°C for 5 sec. Hand Soldering: 350°C for 3 sec.	

**UA(C)5641-11****0.56" SINGLE DIGIT  
DISPLAY****Electrical and Optical Characteristics:**

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Luminous Intensity Per Segment	I <sub>v</sub>	If=10mA/seg.	1.15	3.3		mcd
Forward Voltage	V <sub>f</sub>	If=20mA/seg.		2.1	2.6	V
Peak Wavelength	λ <sub>p</sub>	If=20mA/seg.		635		nm
Dominant Wavelength	λ <sub>d</sub>	If=20mA/seg.		626		nm
Reverse Current Per Chip (Leakage Current Per Chip)	I <sub>r</sub>	V <sub>r</sub> =5V			100	μA
Spectrum Line Halfwidth	Δλ	If=20mA/seg.		35		nm
Response Time	T	-----		250		ns

Note: Customer's special requirements are also welcome.

## Typical Electrical/Optical Characteristic Curves

(25°C Ambient Temperature Unless Otherwise Noted)




Fig.1 RELATIVE INTENSITY VS.  
WAVELENGTH




Fig.2 MAXIMUM TOLERABLE PEAK  
CURRENT VS. PULSE DURATION




Fig.3 FORWARD CURRENT VS.  
FORWARD VOLTAGE PER CHIP




Fig.4 FORWARD CURRENT VS.  
DERATING CURVE




Fig.5 RELATIVE LUMINOUS INTENSITY  
VS. FORWARD CURRENT




Fig.6 LUMINOUS INTENSITY VS.  
AMBIENT TEMPERATURE

## **Precautions in Use:**

**PLEASE PAY SPECIAL ATTENTION TO THE NEXT POINT TO INCORPORATE OPTO  
DEVICE TO HIGH RELIABILITY**

1. Do not bend the lead. Bending leads could cause breakage of leads or the degradation of the chip.

When bending is unavoidable, strictly follow the cautionary instruction below.

- (1) Bend the leads before soldering.
- (2) Bending a lead must be done by fixing a lead tightly and applying no stress on the resin part.
- (3) The lead bending point must be more than 1.6mm away from the edge or the resin part.
- (4) When a pin is tested for its endurance, bending degree should be 45° and repeated no more than two times.

2. Setting a product by using tool such as a holder should be avoided.

When necessary, no stress should be applied to the resin part and lead to consider dimension tolerance, thermal expansion, thermal contraction of holder, product and circuit board etc.

3. The hole pitch of a circuit board must fit into the lead pitch of products.

4. When soldering, care the followings:

- (1) Do not heat a product under any stress (i.e.: twist) to leads.
- (2) Do not heat ( for example, by soldering ) a product while out side force is applied the resin part.
- (3) The lead bending point must be more than 1.6mm away from the edge or the resin part.
- (4) Soldering with PC Board should be conducted with following conditions.
  - (a) For dip soldering
    - Pre-heating : 90°C Max. for within 60 Sec.
    - Soldering Max. : 260±5°C (Solder Temp.) for within 5 Sec.
  - (b) Soldering iron : 350°C (Soldering iron tip) for within 3 Sec.

5. Flux could corrode the leads. Use flux that contains as little chlorine as possible (RA, RMA, less than 0.2 wt%) and need not be washed way. When, however, washing is necessary, partially wash around the leads, instead of the entire LED, by the following conditions.

Cleaning agent : Methyl Alcohol

Cleaning temp : 45°C Max.

Cleaning time : 30Sec. Max.

6. Minimum amount of soldering flux should be used. Soldering flux should be applied only to the pin portion.

7. The following may damage products or LED chips: Attachment or contact of residual flux solvent onto the product surface or to LED chips, or invasion of the same into the product.