


Encoder 11mm Size Metal Shaft Type

EC11 Series



Compact and highly reliable type available in many varieties.



Typical Specifications

Items	Specifications
Rating	10mA 5V DC
Operating life	15,000cycles EC11EH:30,000cycles EC11K:100,000cycles 500,000cycles 1,000,000cycles
Operating temperature range	−40°C to +85°C

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

Metal
Shaft

Insulated
Shaft

Hollow
Shaft

Ring
Type



Automotive
Use

Product Line

Structure	Actuator configuration	Actuator length (mm)	Torque (mN·m)	Number of detent	Number of pulse	Push-on switch	Travel of push-on switch (mm)	Operating life (cycles)	Minimum order unit (pcs.)	Product No.	Drawing No.					
Horizontal	Flat	20	12±7	30	15	Without	——		1,400	EC11B15202AA	1					
						With	0.5			EC11B15242AE	2					
							1.5			EC11B15242AF	3					
Vertical			10±7	18	9	Without	——	15,000	2,400	EC11E09204A4	4					
										30		15	EC11E15204A3			
				7 ⁺³ ₋₄	Without					18		EC11E1530401				
				10±7	36					18		EC11E1820402				
				7 ⁺³ ₋₄	Without					18		EC11E1830401				
				10±7	18					9	With	0.5	EC11E09244BS	5		
			30			15	EC11E15244G1									
			7 ⁺³ ₋₄		Without	18	EC11E153440D									
			10±7		36	18	EC11E18244AU									
			7 ⁺³ ₋₄		Without	18	EC11E183440C									
			10±7		18	9	1.5			EC11E09244AQ						
				30						15		EC11E15244B2				
				7 ⁺³ ₋₄	Without	18				EC11E1534408						
				10±7	36	18				EC11E18244A5						
				7 ⁺³ ₋₄	Without	18				EC11E1834403						
				12±5	18	9				Without		——	100,000	2,000	EC11K0920401	6
			30				15								EC11K1520401	
			18			9	With	0.5		EC11K0924401	7					
										1.5					EC11K1524402	
								30							15	EC11K0925401
										EC11K1525401						
			18		9	Without	——	EC11K0920601		6						
								30			15	EC11K1520601				
			18		9	With	0.5	500,000		EC11K0924601	7					
										30		15	EC11K1524601			
					18								9		1.5	EC11K0925601
										30		15				EC11K1525601
					18					9	Without	——	1,000,000		EC11K0920801	6
															30	
			18			9	With	0.5		EC11K0924801					7	
	30	15								EC11K1524801						
										18						9
	30	15														

Product Line

	Structure	Actuator configuration	Actuator length (mm)	Torque (mN·m)	Number of detent	Number of pulse	Push-on switch	Travel of push-on switch (mm)	Operating life (cycles)	Minimum order unit (pcs.)	Product No.	Drawing No.					
Detector	Push lock	20-tooth serration	25	10±7	30	15	Without	—		1,600	EC11E152T409	8					
			26.4				With	8			EC11E152U402	9					
Push	Self-return switch		15	3 to 30	Without	Self-return switch	Without	—	15,000		EC1110120005	10					
Slide							20	10±7			ABC switch	With	0.5	30,000	2,400	EC111012010H	11
																1.5	
Rotary			ABC switch				Flat	20			10±7	30	15	With	0.5	30,000	2,400
Encoders	30	EC11EH224403															
	18	EC11EH124404															
Power		EC11EH224404															
Dual-in-line Package Type	Dual-shaft		Inner-shaft=25	30	30	15		0.5	15,000	1,400	EC11EBB24C03	13					
TACT Switch™		Slotted	Outer-shaft=15					—			EC11E0B2LB01	14					
		Flat	Inner-shaft=25					1.5									
Custom-Products		Slotted	Outer-shaft=15					3 to 30					Without	Self-return switch	Without	—	

Packing Specifications

Tray

	Product No.	Number of packages (pcs.)		Export package measurements (mm)
		1 case /Japan	1 case /export packing	
Metal Shaft	EC11B	700	1,400	370×520×201
	EC11E09/15/18/EC11EH	1,200	2,400	540×360×250
	EC11K	1,000	2,000	
Insulated Shaft	EC11E152T/U	800	1,600	374×529×213
Hollow Shaft	EC111	1,200	2,400	363×507×216
Ring Type	EC11E0B/BB	700	1,400	374×529×213

Notes

- Products other than those listed in the above chart are also available. Please contact us for details.
- Please place purchase orders per minimum order unit N (integer).



Refer to **P.209** for product varieties.
Refer to **P.217** for product specifications.
Refer to **P.217** for attached parts.

Dimensions

Unit:mm

No.	Photo	Style	PC board mounting hole dimensions (Viewed from mounting side)
1			
2			
3			
4			
5			

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-Products

Metal Shaft

Insulated Shaft

Hollow Shaft











Ring Type



Automotive Use










Dimensions

Unit:mm

No.	Photo	Style	PC board mounting hole dimensions (Viewed from mounting side)
6	Vertical 		 EC11K09 Type only EC11K15 Type only PC board mounting detail A slant line part shows the solder land black part: Do not solder and wiring for electrical contact
7	Vertical with push-on switch (travel 0.5mm/1.5mm) 		 EC11K09 Type only EC11K15 Type only PC board mounting detail A slant line part shows the solder land black part: Do not solder and wiring for electrical contact
8	Push-lock mechanism 		
9	Push-lock mechanism with push-lock switch 		
10	Self-return switch 		

Dimensions

Unit:mm

No.	Photo	Style	PC board mounting hole dimensions (Viewed from mounting side)
11	Self-return switch with push-on switch (travel 0.5mm/1.5mm) 		
12	ABC switch with push-on switch (travel 0.5mm/1.5mm) 		
13	Dual-shaft type with push-on switch (travel 0.5mm) Inner shaft: encoder Outer shaft: encoder 		
14	Dual-shaft type with push-on switch (travel 1.5mm) Inner shaft: encoder Outer shaft: self-return switch 		

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

Metal
Shaft

Insulated
Shaft

Hollow
Shaft

Ring
Type



Automotive
Use

Product Varieties


Shaft Dimensions

1. Single-shaft Type (EC11K is excluded. Refer to P.212 for EC11K)

1) Knurled Type Unit:mm

Configuration(Shaft diameter: $\phi 6$)

Not applicable for EC11E with push-lock mechanism




Detailed dimensions

L ₁	L _B	ℓ ₁	ℓ ₂	S ₁
20	7	6	1	7
25	10	10	2	11

2) Flat Type Unit:mm

Configuration(Shaft diameter: $\phi 6$)



Detailed dimensions


L ₁	L _B	ℓ
15	5	7
15	7	5 (6)
20	7	10 (12)
25	10	12

※Does not comply with EC111

Dimensions marked with () apply to products without push-on switches.

3) Slotted Type Unit:mm

Configuration(Shaft diameter: $\phi 6$)




Detailed dimensions

L ₁	L _B
15	7
20	7
25	10

2. Standard Dimensions and configuration of Dual-shaft Type

1) Flat Type Unit:mm

Configuration(Inner-shaft : $\phi 3.5$ Outer-shaft : $\phi 6$)



Detailed dimensions

L ₁	L ₂	L _B	ℓ ₁	ℓ ₂
20	10	5	7	4
25	15	7	7	5
30	20	10	7	5

Notes

- The highlighted figures in shaft types refer to Product Specifications in P.204 and P.205.
- Products other than those listed in the above chart are also available. Please contact us for details

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Custom-
Products

Metal
Shaft

Insulated
Shaft

Hollow
Shaft

Ring
Type



Automotive
Use

List of Varieties

	Type		Metal shaft							
			9mm size		11mm size					
	Series		EC09E	EC11B	EC11E		EC111	EC11EH		
Detector	Photo									
Push	Output		Incremental				Self-return switch	ABC switch		
Slide	Outline specifications	Shaft types	Single-shaft			Dual-shaft	Single-shaft			
Rotary		Operating direction	Vertical	Horizontal		Vertical				
Encoders		Number of pulse/ Number of detent	15/30			9/18 15/30 18/36		_____	6×ABC/18 10×ABC/30	
		Push switch (Travel mm)	Without/With (0.5, 1.5)							
		Optional functions	_____			Push-lock mechanism Without detent		_____		
Power		Changeover angle	_____				17 to 40°		_____	
Dual-in-line Package Type	Dimensions (mm)	W	9.5	11.7						
		D		13.8		12		13		12
		H	4.5	5.5		4.5	8.5	5		4.5
Custom-Products	Soldering	Manual soldering	350℃ max. 3s max.							
		Dip soldering	260±5℃, 3±1s		260±5℃, 5±1s					
	Operating temperature range		-40℃ to +85℃							
	Automotive use		○	○	○		○	○		
	Maximum operating current (Resistive load)		10mA							
Metal Shaft	Electrical performance	Output signal	Output of A and B signals, proportionate to phase difference				Self-return switch		Three phase A, B and C	
		Output wave	Please see P.217							
		Sliding noise	Please see P.217							
		Insulation resistance	100MΩ min. 250V DC							
		Voltage proof	300V AC for 1minute							
Hollow Shaft	Mechanical performance	Rotational torque	_____			7 ⁺³ / ₋₄ mN·m	—	3~30mN·m		_____
Detent torque		8±5mN·m		12±7mN·m		10±7mN·m		_____	10±7mN·m	
Ring Type		Push-pull strength	100N							
	Environmental performance	Cold	-40±3℃ for 240h							
		Dry heat	+85±3℃ for 240h							
		Damp heat	60±2℃, 90 to 95%RH for 240h							
	Page		203		204					

Push-on Switch Specifications

Items	EC09E		EC11B		EC11E		EC111		EC11EH	
Contact arrangement	Single pole and single throw (Push-on)									
Travel (mm)	0.5±0.3	1.5±0.5	0.5 ^{+ 0.4} _{- 0.3}	1.5±0.5	0.5±0.3	1.5±0.5 8±0.8※	0.5±0.3	1.5±0.5	0.5±0.3	1.5±0.5
Operating force (N)	6 ^{+ 2.5} _{- 2}	4±2	6±3	5±2	6 ^{+ 2.5} _{- 2}	4±2 8 max. ※	6 ^{+ 2.5} _{- 2}	4±2	6 ^{+ 2.5} _{- 2}	4±2
Rating	10mA 5V DC		0.1A 5V DC (500μA 5V DC min. ratings)		0.1A 5V DC (500μA 5V DC min. ratings) 0.5A 12V DC ※		0.1A 5V DC (500μA 5V DC min. ratings)			
Contact resistance	100mΩ max. for initial period; 200mΩ max. after operating life.									
Operating life	10,000times min.		25,000 times min.	20,000 times min.	20,000times min. 10,000times min.※		20,000times min.			

Notes

- ※marked specification is only applicable to EC11E152U402.
- marks in "Available for automotive use" indicate that some of the series products can work at the operating temperature range from -40°C to +85°C.

List of Varieties

Type		Metal shaft			
		11mm size		20mm size	
Series		EC11K	EC11J	EC20A/RK203	EM20B
Photo					
Output		Incremental			
Outline specifications	Shaft types	Single-shaft			
	Operating direction	Vertical			
	Number of pulse/ Number of detent	9/18 15/30		18/18	40/40
	Push switch (Travel mm)	Without With (0.5, 1.5)		Without With (1.5)	Without With (0.5)
	Optional function				Display function
Dimensions (mm)	W	11.7		20.2	20
	D	12	14.2	19.2	22.25
	H	4.5		10	13
Soldering	Manual soldering	350°C max. 3s max.			
	Dip soldering	260±5°C, 3±1s		260±5°C, 5±1s	260°C max. 3s max.
	Reflow soldering		Please see P.212		
Operating temperature range		-40°C to +85°C			-10°C to +70°C
Automotive use		○	○	○	—
Maximum operating current (Resistive load)		10mA			—
Electrical performance	Output signal	Output of A and B signals, proportionate to phase difference			V _H : +4.0V min. V _{LO} : 0.5V max. (Isink=5mA)
	Output wave	Please see P.217			—
	Output phase				A, B (Squarewave)
	Sliding noise	Please see P.217			—
	Insulation resistance	100MΩ min. 250V DC		10MΩ min. 50V DC	100MΩ min. 250V DC
	Voltage proof	300V AC for 1minute		50V AC for 1minute	300V AC for 1minute
Mechanical performance	Rotational torque				7mN·m max.
	Detent torque	12±5mN·m		40±20mN·m	8±5mN·m
	Push-pull strength	100N			
Environmental performance	Cold	-40±2°C for 240h		-40±3°C for 240h	-30±3°C for 240h
	Dry heat	85±2°C for 240h		85±3°C for 240h	80±3°C for 240h
	Damp heat	60±2°C, 90 to 95% RH for 240h		60±3°C, 90 to 95% RH for 240h	40±2°C, 90 to 95% RH for 240h
Page		204	210	213	215

Push-on Switch Specifications

Items	EC11K/EC11J		EC20A	EM20B
Contact arrangement	Single pole and single throw (Push-on)			
Travel (mm)	0.5±0.3	1.5±0.5		0.5 ^{+0.4} _{-0.3}
Operating force (N)	5±2	4±2		6±3
Rating	0.1A 5V DC		0.5A 16V DC (1mA 16V DC min. ratings)	0.1A 5V DC
Contact resistance	100mΩ for initial period; 200mΩ after operating life			
Operating life	1,000,000 times min.	100,000 times min.	20,000times min.	25,000times min.

Note

○marks in "Available for automotive use" indicate that some of the series products can work at the operating temperature range from -40°C to +85°C.

Detector

Push

Slide

Rotary

Encoders

Power


Dual-in-line
Package Type

TACT Switch™



Custom-
ProductsMetal
ShaftInsulated
ShaftHollow
ShaftRing
Type

Product Specifications



Output Wave



Circuit Diagram



Sliding Noise



Attached Parts

EC11B Series

Unit:mm

