




Dimensions mm[inch]

 tolerances acc. to DIN ISO 2768-m
Toleranzen gem. DIN ISO 2768-m




Isometric

Scale 2:1
Maßstab 2:1



Layout

Top view
Draufsicht



Marking

according to EN60062/factory code
gem. EN60062/Fertigungsstätte

MEDER electronic **SIL05-1A31-71Q** **YWP**

Coil Data at 20 °C	Conditions	Min	Typ	Max	Unit
Coil resistance		72	80	88	Ohm
Coil voltage			5		VDC
Rated power			312		mW
Thermal resistance	max. Relay temperature = operating temperature + self heating		109		K/W
Pull-In voltage				3,5	VDC
Drop-Out voltage		0,75			VDC

Contact data 31	Conditions	Min	Typ	Max	Unit
Contact-material	independent on position		Hg		
Switching suitability			bounce free		
Contact rating	Any DC combination of V & A up to 500V max. 50W, with 1000V max. 5W			50	W
Switching voltage	DC or Peak AC			500	V
Switching current	DC or Peak AC			2	A
Carry current	DC or Peak AC			2	A
Contact resistance static	Measured with 40% overdrive Start Value			80	mOhm
Insulation resistance	RH <45 %, 100 V test voltage	100			GOhm
Breakdown voltage	according to EN 60255-5	1.500			VDC
Operate time incl. bounce	measured with 40% overdrive			1,2	ms
Release Time	measured with no coil excitation			1	ms
Capacity	@ 10 kHz across open switch		0,3		pF

Special Product Data	Conditions	Min	Typ	Max	Unit
Dielectric Strength Coil/Contact	according to EN 60255-5	2			kV DC
Insulation resistance Coil/Contact	RH <45%, 200 VDC measuring voltage	1			TOhm
Housing material			epoxy resin		
Connection pins			CuFe2P, tin plated		
Magnetic Shield			yes		
Reach / RoHS conformity			no		
Remark			Check conditions at high packing density! (Rth)		



Products for
tomorrow...

Europe: +49 / 7731 8399 0 | Email: info@meder.com
USA: +1 / 508 295 0771 | Email: salesusa@meder.com
Asia: +852 / 2955 1682 | Email: salesasia@meder.com

Item No.:

3305131371

Item:

SIL05-1A31-71Q

Environmental data	Conditions	Min	Typ	Max	Unit
Shock	1/2 sine, duration 11ms, in 3 axis			50	g
Vibration	from 10 - 2000 Hz			20	g
Operating temperature		-20		55	°C
Storage temperature		-35		95	°C
Soldering temperature	wave soldering max. 5 sec.			260	°C
Washability				fully sealed	

General data	Conditions	Min	Typ	Max	Unit
Total weight			2,4		g
Packaging				tube per 25 pcs.	

Modifications in the sense of technical progress are reserved

Designed at: 11.09.07 Designed by: THAUKE
Last Change at: 14.09.12 Last Change by: NMHAI

Approval at: 11.09.07 Approval by: RRIPPL
Approval at: 18.09.12 Approval by: CRUF

Version: 4