

International
IR Rectifier

SAFEIR Series 20ETS16, 20ETS16S

INPUT RECTIFIER DIODE


Description/Features

The 20ETS.. rectifier **SAFEIR** series has been optimized for very low forward voltage drop, with moderate leakage. The glass passivation technology used has reliable operation up to 150°C junction temperature.

Typical applications are in input rectification and these products are designed to be used with International Rectifier Switches and Output Rectifiers which are available in identical package outlines.

	$V_F < 1V @ 10A$
	$I_{FSM} = 300A$
	$V_{RRM} 1600V$

Package Outline




Major Ratings and Characteristics

Characteristics	20ETS..	Units
$I_{F(AV)}$ Sinusoidal waveform	20	A
V_{RRM} Range(*)	1600	V
I_{FSM}	300	A
$V_F @ 10A, T_J = 25^\circ C$	1.0	V
T_J	-40 to 150	°C

(*)Contact Factory

Package Outline



Output Current in Typical Applications

	Single-phase Bridge	Three-phase Bridge	Units
Capacitive input filter $T_A = 55^\circ C$, $T_J = 125^\circ C$, common heatsink of $1^\circ C/W$	16.3	21	A

20ETS16, 20ETS16S *SAFEIR* Series

Bulletin I2161 10/01

International
IR Rectifier

Voltage Ratings

Part Number	V_{RRM} , maximum peak reverse voltage V	V_{RSM} , maximum non repetitive peak reverse voltage V	I_{RRM} 150°C mA
20ETS16, 20ETS16S	1600	1700	1

Absolute Maximum Ratings

Parameters	20ETS..	Units	Conditions
$I_{F(AV)}$ Max. Average Forward Current	20	A	@ $T_C = 105^\circ\text{C}$, 180° conduction half sine wave
I_{FSM} Max. Peak One Cycle Non-Repetitive Surge Current	250	A	10ms Sine pulse, rated V_{RRM} applied
	300		10ms Sine pulse, no voltage reapplied
I^2t Max. I^2t for fusing	316	A^2s	10ms Sine pulse, rated V_{RRM} applied
	442		10ms Sine pulse, no voltage reapplied
$I^2\sqrt{t}$ Max. $I^2\sqrt{t}$ for fusing	4420	$A^2\sqrt{s}$	$t = 0.1$ to 10ms, no voltage reapplied

Electrical Specifications

Parameters	20ETS..	Units	Conditions
V_{FM} Max. Forward Voltage Drop	1.1	V	@ 20A, $T_J = 25^\circ\text{C}$
r_t Forward slope resistance	10.4	mΩ	$T_J = 150^\circ\text{C}$
$V_{F(TO)}$ Threshold voltage	0.85	V	
I_{RM} Max. Reverse Leakage Current	0.1	mA	$T_J = 25^\circ\text{C}$
	1.0		$T_J = 150^\circ\text{C}$

$V_R = \text{rated } V_{RRM}$

Thermal-Mechanical Specifications

Parameters			20ETS..	Units	Conditions
T _J	Max. Junction Temperature Range		-40 to 150	°C	
T _{stg}	Max. Storage Temperature Range		-40 to 150	°C	
R _{thJC}	Max. Thermal Resistance Junction to Case		1.3	°C/W	DC operation
R _{thJA}	Max. Thermal Resistance Junction to Ambient		62	°C/W	(*) For D ² Pak version
R _{thCS}	Typ. Thermal Resistance Case to Heatsink		0.5	°C/W	Mounting surface, smooth and greased
wt	Approximate Weight		2 (0.07)	g (oz.)	
T	Mounting Torque	Min.	6 (5)	Kg-cm (lbf-in)	
		Max.	12 (10)		
Case Style			TO-220AC, D ² Pak (SMD-220)		

* When mounted on 1" square (650mm²) PCB of FR-4 or G-10 material 4 oz (140μm) copper 40°C/W
For recommended footprint and soldering techniques refer to application note #AN-994




Fig. 1 - Current Rating Characteristics




Fig. 2 - Current Rating Characteristics




Fig. 3 - Forward Power Loss Characteristics




Fig. 4 - Forward Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current








Fig. 6 - Maximum Non-Repetitive Surge Current



Outline Table




20ETS16, 20ETS16S *SAFEIR* Series


Bulletin I2161 10/01

International
IR Rectifier

Marking Information




Tape & Reel Information



Ordering Information Table

Device Code						
20	E	T	S	16	S	TRL
1	2	3	4	5	6	7
1	-	Current Rating				
2	-	Circuit Configuration				
		E = Single Diode				
3	-	Package				
		T = TO-220AC				
4	-	Type of Silicon				
		S = Standard Recovery Rectifier				
5	-	Voltage code: Code x 100 = V_{RRM}				
6	-	S = TO-220 D ² Pak (SMD-220) Version				
7	-	Tape and Reel Option				
		TRL = Left Reel				
		TRR = Right Orientation Reel				



16 = 1600V (*)

(*) Contact Factory

Data and specifications subject to change without notice.
This product has been designed and qualified for Industrial Level.
Qualification Standards can be found on IR's Web site.

International
IR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105

TAC Fax: (310) 252-7309

Visit us at www.irf.com for sales contact information. 10/01