

OCT 06 2009

COMPANY CONFIDENTIAL: The information contained herein is the property of MICA Microwave. Its use or reproduction is prohibited except as provided for by prior written authorization from MICA Microwave.

NOTE: THIS IS A COMPUTER GENERATED DRAWING. ALL CHANGES HEREIN MUST BE REFLECTED IN THE COMPUTER DATABASE.

REV. DESCRIPTION

A PRODUCTION RELEASE PER ECO# 1756

B REV "B" PER ECO# 3501

DWG. NO. 210961

SH 1


REV. B

APPROVED

DATE

01/23/91

01/06/99



COUNTER - CLOCKWISE
CIRCULATION

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES, TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± .03 .XXX ± .010 .XXXX ±

APPROVALS

DRAWN P.T

CHECKED

ISSUED

DATE

06/21/01

MICA®

CIRCULATOR 5 PORT
C-310S01

SIZE FSCM NO.

A 7Y213

DWG. NO. 210961

SCALE NONE

SHEET 1 OF 1

NEXT ASSY USED ON

APPLICATIONS

DO NOT SCALE DRAWING

MATERIAL

FINISH

FLAME SPRAY

REVISIONS

REV. B

OCT 06 2009

DWG. NO. 220763 SH 1 REV. A

REVISIONS

REV.	DESCRIPTION	DATE	APPROVED
A	REV. A' PER ECO NO. 1756	1/23/91	N. Klayak

UNCONTROLLED

FREQUENCY RANGE : 10.74 TO 14.76 GHz
ISOLATION : 20 dB PER JUNCTION
INSERTION LOSS : 0.6 dB PER JUNCTION
1.8 dB MAX. J2 TO J1
0.6 dB MAX. J1 TO J3
VSWR : 1.25 : 1 MAX.
TEMPERATURE : OPERATING 0°C TO +70°C
STORAGE -55°C TO +85°C

QTY REQD	FSCM NO.	PART OR IDENTIFYING NO.	NOMENCLATURE OR DESCRIPTION	MATERIAL SPECIFICATION
PARTS LIST				
CONTRACT NO.				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES = .XX ± .XXX ± =				
MATERIAL				
FINISH				
DO NOT SCALE DRAWING				
APPROVALS				
DRAWN D.N.				
CHECKED T. Klayak				
ISSUED				
DATE 10/11/89				
DATE 10/13/89				
QA A. CHAN				
01/28/91				
SCALE 1 OF 1				
DWG. NO. 220763				
REV. A				
FSCM NO. 7Y213				
SIZE A				
SPECS C-310S01				
mika				
NEXT ASSY				
USED ON				
APPLICATION				