




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AI	00		D	ECR-14-012060	11AUG14	LS	GS




1. HEXAGON SOCKET SCREW KEY 2.5 IS FIXED AT HAND TOOL

2. INSTRUCTION SHEET IS IN SCOPE OF DELIVERY
TE P/N 5-744001-2

3. PACKED IN ONE BOX

OPTION
4. REPAIR KIT, TE P/N 539635-2
CONSISTING OF:
10 DIE RETAINING SCREW, M4x11
11 DIE RETAINING SCREW, M4x10
12 ADJUSTMENT WHEEL
13 RETAINING PLATE 4
14 SCREWED STOP PIN, M3x5
15 TENSION SPRING



SPARE PARTS				
POS	QTY	REV	TE- P/N	DESCRIPTION
2	1	A	519151-9	Linsenkopfschraube, M4x10
3	1	A	8-539634-5	Linsenkopfschraube, M4x11

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. Reissig	28JAN99	 TE Connectivity		
		CHK U. Reuter	03FEB99			
DIMENSIONS: mm		APVD U. Reuter	03FEB99	NAME ERGOCRIMP HAND TOOL ERGOCRIMP Handzange		
		PRODUCT SPEC				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC		SIZE A3		
MATERIAL		Gewicht / Weight in Kg	0.626	DRAWING NO 539635-1		
		FINISH				
CUSTOMER DRAWING				SCALE 1:1.5	SHEET 1 OF 1	REV D