



CONNECTOR ASSEMBLY EXEMPLARY LOADED



CONNECTOR APPEARANCES POSSIBLE VERSIONS




CONTACT LAYOUT

	z	a	b	c	d	e	f
1	T	P	P	P	P	P	T
2	T	P	P	P	P	P	T
3	T	P	P	P	P	P	T
4	T	P	P	P	P	P	T
5	T	P	P	P	P	P	T
6	T	P	P	P	P	P	T
7	T	P	P	P	P	P	T
8	T	P	P	P	P	P	T
9	T	P	P	P	P	P	T
10	T	P	P	P	P	P	T
11	T	P	P	P	P	P	T
MULTI PURPOSE CENTRE							
15	T	P	P	P	P	P	T
16	T	P	P	P	P	P	T
17	T	P	P	P	P	P	T
18	T	P	P	P	P	P	T
19	T	P	P	P	P	P	T
20	T	P	P	P	P	P	T
21	T	P	P	P	P	P	T
22	T	P	P	P	P	P	T
23	T	P	P	P	P	P	T
24	T	P	P	P	P	K	T
25	T	P	P	P	P	K	T

REVISIONS				
REV	DATE	DESCRIPTION	BY	APPD
1	24-JUN-94	EH-0394-94	LvdH	-
2	31-JUL-01	SR10-0332-01	FB	-


CONTACT DIMENSIONS



NOTES:

- FOR FINISH TYPES SEE PLATING TABLE.
- MATERIAL CONTACT: PHOSPHORBRONZE.
- MATERIAL POST ALIGNMENT STRIP: UNFILLED POLYESTER
- MATERIAL HOUSING: GREY GLASSFILLED POLYESTER
- UL-RATING 94V0.
- CONNECTOR MARKED WITH PART NUMBER AND DATE CODE. (OTHER MARKING OPTIONAL)
- PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.
- AREA FOR KEYING PART (BASIC PART NUMBER 100525).
- FOR ACTUAL PIN LOADING SEE "CONTACT LAYOUT".
- LOCATION PEG.

- CONNECTOR LUBRICATED WITH BELCORE.
- APPROVED LUBRICANT TECHNICAL REFERENCE
- TR-NWT-001217 ISSUE 1 SEPT 1992



RECOMMENDED PCB-HOLE LAY-OUT COMPONENT SIDE SHOWN

P.C.B. HOLE DIM. ACTION PIN

DRILLED HOLE: 0.7 ± 0.025mm
FIN. HOLE : 0.55 TO 0.65mm
Cu-thks : 0.025 TO 0.050mm
SnPb-thks : 0.004 TO 0.010mm

PART NUMBER	UNDER-COATING μm Ni MIN.	CONTACT AREA μm Au MIN.	ACTION-PIN AREA μm Sn/Pb	CONSERVATION TREATMENT	MATERIAL
0-188257-9	1,27	0,76	0,5-2,5	Yes	Δ
0-188257-1	1,27	0,76	0,5-2,5	No	Δ

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE	31-JUL-01	BY	Frederik Beun
DIMENSIONS:		APPROVED		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	108-19082	APPLICATION SPEC	
MATERIAL		SIZE	114-19029	WEIGHT	
FINISH		SCALE	A2 00779	RESTRICTED TO	
		CUSTOMER DRAWING	188257	SHEET	1 OF 1