

1,550nm DFB DWDM Direct Modulation Laser

FLD5F6CX-J

FEATURES


- Direct Modulated DFB Laser
- Built-in TEC, Thermistor and Monitor PD
- 14-Pin Butterfly Type Module
- 10mW Output Power
- Low Residual Chirp
- Optimized for 2.5 Gb/s Modulation Rates
- Selected wavelengths according to ITU-T grid available

APPLICATIONS

This laser is intended for the application of 2.5 Gb/s long haul Dense Wavelength Division Multiplexing (DWDM). Transmission spans of 100 km (1800ps/nm) are possible.

DESCRIPTION

The FLD5F6CX-J is a high power laser capable of 2.5 Gb/s transmission. It is packaged in a “butterfly” type module. The module employs a high efficiency optical coupling system, coupling the laser output through a built-in optical isolator into a single mode fiber pigtail. The module also includes a monitor photodiode, a thermoelectric cooler (TEC) and thermistor. This device is optimally designed for use in DWDM direct modulation transmission systems. Selected wavelengths are available to the specified ITU-T grid.



ABSOLUTE MAXIMUM RATINGS (T_c=25°C, unless otherwise specified)

Parameter	Symbol	Condition	Rating		Unit
			Min.	Max.	
Storage Temperature	T _{stg}	-	-40	+70	°C
Operating Case Temperature	T _{op}	-	-20	+65	°C
Optical Output Power	P _f	CW	-	12	mW
Laser Forward Current	I _F	CW	-	150	mA
Laser Reverse Voltage	V _R	CW	-	2	V
Photodiode Forward Current	-	-	-	10	mA
Photodiode Reverse Voltage	V _{DR}	-	-	20	V
TEC Voltage	V _c	Cooling	-	+2.5	V
		Heating	-2.5	-	
TEC Current	I _c	Cooling	-	+1.4	A
		Heating	-0.9	-	
Thermistor Temperature	T _{th}	ATC Operation	-20	+65	°C
Lead Soldering Time	T _{sold}	260°C	-	10	sec
Environmental Operating Humidity	X _{op}	T _{op} <30°C	-	95	%
Environmental Storage Humidity	X _{st}	T _{stg} <30°C	-	95	%

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_L=T_{set}$, $T_C=25^{\circ}\text{C}$, BOL, unless otherwise specified)

Parameter	Symbol	Test Conditions	Limits			Unit
			Min.	Typ.	Max.	
Laser Set Temperature	T_{set}	-	20	-	35	$^{\circ}\text{C}$
Threshold Current	I_{th}	CW	3	-	40	mA
Forward Voltage	V_{FDC}	CW, $I_F=30\text{ mA}$, pin 12,-13	-	1.6	1.75	V
Series Resistance	R_s	CW, pin 12,-13	22	25	28	Ω
Optical Output Power	P_f	CW	10.0	-	-	mW
Slope Efficiency	η	CW, $P_f=10\text{mW}$	0.14	-	-	mW/mA
Threshold Power	P_{th}	$I_F=I_{th}$, CW	-	-	150	μW
Tracking Error (Note 1)	TE	$P_f=10\text{mW}$, $T_C=-20\text{ to }65^{\circ}\text{C}$, APC	-0.5	-	+0.5	dB
Monitor Current	I_m	CW, $P_f=10\text{mW}$, $V_{DR}=5\text{V}$	0.25	-	2.5	mA
Photodiode Dark Current	I_D	$V_{DR}=5\text{V}$	-	2	100	nA
Photodiode Capacitance	C_t	$V_{DR}=5\text{V}$, $f=1\text{ MHz}$	-	-	10	pF
Photodiode Cutoff Frequency	f_{cm}	$V_{DR}=5\text{V}$, 50Ω load	100	-	-	MHz
Peak Wavelength	λ_p	Note (2)	Note (4)			nm
Wavelength Drift	$\Delta\lambda$	after 20 years	-200	-	+200	pm
Wavelength Stability with Case Temperature	$d\lambda/dT_c$	$T_C=-20\text{ to }65^{\circ}\text{C}$	-1	-	+1	pm/ $^{\circ}\text{C}$
Side Mode Suppression	S_r	Note (2)	33	35	-	dB
Spectral Width (-20dB)	$\delta\lambda$	Note (2)	-	-	0.5	nm
Rise Time (10%-90%)	t_r	Note (2)	-	0.1	0.125	nsec
Fall Time (10%-90%)	t_f	Note (2)	-	0.1	0.125	nsec
Cutoff Frequency	f_c	$P_f=10\text{mW}$, -3 dB	4.0	-	-	GHz
In-Band Ripple (Window)	S_{21}	$f=50\text{ MHz to }3\text{ GHz}$	-1.5	-	+1.5	dB
RF Return Loss	S_{11}	$f=50\text{ MHz to }2\text{ GHz}$	8	-	-	dB
		$f=2\text{ GHz to }3\text{ GHz}$	6	-	-	dB
		$f=3\text{ GHz to }5\text{ GHz}$	3	-	-	dB
Optical Isolation	I_s	$T_C=-20\text{ to }65^{\circ}\text{C}$	25	35	-	dB
Relative Intensity Noise	RIN	$f=2.5\text{ GHz}$ $P_f=10\text{ mW}$, ORL=24 dB	-	-	-140	dB/Hz
Kinks	Kns	up to 12 mW	None			
Pulsation	-	-	None			
BER Performance	ER	Note (3)	No Floor			
Dispersion Penalty	dP	Note (3)	-	-	2.0	dB

TEC AND THERMISTOR CHARACTERISTICS ($T_L = T_{set}$, $T_C = 25^\circ\text{C}$, BOL, unless otherwise specified)

Parameter	Symbol	Test Conditions	Limit			Unit
			Min.	Typ.	Max.	
TEC Current	I_C	$T_L = T_{set}$, $P_f = 10\text{mW}$, $T_C = 65^\circ\text{C}$	-	-	1.0	A
TEC Voltage	V_C	$T_L = T_{set}$, $P_f = 10\text{mW}$, $T_C = 65^\circ\text{C}$	-	-	2.4	V
Cooler Power	P_C	$T_L = T_{set}$, $P_f = 10\text{mW}$, $T_C = 65^\circ\text{C}$	-	-	2.4	W
TEC Resistance	R_C	$T_L = T_{set}$, $P_f = 10\text{mW}$, $T_C = 65^\circ\text{C}$	2.0	2.4	3.2	Ω
Thermistor Resistance	R_{tr}	$T_L = 25^\circ\text{C}$	9.5	10.0	10.5	k Ω
Thermistor B Constant	B	-	3,270	3,450	3,630	K

Note 1. $TE = 10 \cdot \log\{P_f(T_{case})/P_f(T_C = 25^\circ\text{C})\}$ dB

Note 2. 2.5 Gb/s NRZ, $P_{peak} = 2.0\text{mW}$, $R_{ext} = 8.2\text{dB}$, PRBS=2²³-1,

Note 3. Bit rate=2.48832 Gb/s, PRBS=2²³-1, Dispersion=1,800 ps/nm, $P_{peak} = 10\text{mW}$,
 $R_{ext} = 10\text{dB}$

Decision point: Center of Back-to-Back at 10⁻⁹, No Floor,

Receiver: Eudyna Standard Receiver

Note 4. The selected wavelengths available are listed in Fig. 8

Fig. 1 Forward Current vs Output Power




Fig. 2 Frequency Response




Fig. 3 RF Return Loss




Fig. 4 Cooler Voltage -Current




Fig. 5 Spectrum




Fig. 6 Temperature Dependence of
Wavelength(ACC Operation)




Fig. 7 Transmission Characteristics





Fig. 8 Wavelength Table

Part Number	Wavelength (nm) (TL=Tset) (in vacuum)	Tolerance (nm)
FLD5F6CX-J62	1527.99	±0.1
-J61	1528.77	±0.1
-J60	1529.55	±0.1
-J59	1530.33	±0.1
-J58	1531.12	±0.1
-J57	1531.90	±0.1
-J56	1532.68	±0.1
-J55	1533.47	±0.1
-J54	1534.25	±0.1
-J53	1535.04	±0.1
-J52	1535.82	±0.1
-J51	1536.61	±0.1
-J50	1537.40	±0.1
-J49	1538.19	±0.1
-J48	1538.98	±0.1
-J47	1539.77	±0.1
-J46	1540.56	±0.1
-J45	1541.35	±0.1
-J44	1542.14	±0.1
-J43	1542.94	±0.1
-J42	1543.73	±0.1

-J41	1544.53	±0.1
-J40	1545.32	±0.1
-J39	1546.12	±0.1
-J38	1546.92	±0.1
-J37	1547.72	±0.1
-J36	1548.51	±0.1
-J35	1549.32	±0.1
-J34	1550.12	±0.1
-J33	1550.92	±0.1
-J32	1551.72	±0.1
-J31	1552.52	±0.1
-J30	1553.33	±0.1
-J29	1554.13	±0.1
-J28	1554.94	±0.1
-J27	1555.75	±0.1
-J26	1556.55	±0.1
-J25	1557.36	±0.1
-J24	1558.17	±0.1
-J23	1558.98	±0.1
-J22	1559.79	±0.1
-J21	1560.61	±0.1
-J20	1561.42	±0.1
-J19	1562.23	±0.1
-J18	1563.05	±0.1


"CX" PACKAGE

UNIT: mm



Grounded Type

PIN #	FUNCTION
1.	Thermistor
2.	Thermistor
3.	Laser DC Bias (-)
4.	Monitor (Anode)
5.	Monitor (Cathode)
6.	Thermoelectric Cooler (+)
7.	Thermoelectric Cooler (-)
8.	Case Ground
9.	Case Ground
10.	N.C.
11.	Case Ground
12.	Laser Modulation (-)
13.	Case Ground
14.	N.C.



For further information please contact:

Eudyna Devices USA Inc.

2355 Zanker Rd.
San Jose, CA 95131-1138, U.S.A.
TEL: (408) 232-9500
FAX: (408) 428-9111
www.us.eudyna.com

Eudyna Devices Europe Ltd.

Network House
Norreys Drive
Maidenhead, Berkshire SL6 4FJ
United Kingdom
TEL: +44 (0) 1628 504800
FAX: +44 (0) 1628 504888

Eudyna Devices Asia Pte Ltd.

Hong Kong Branch
Rm. 1101, Ocean Centre, 5 Canton Rd.
Tsim Sha Tsui, Kowloon, Hong Kong
TEL: +852-2377-0227
FAX: +852-2377-3921

Eudyna Devices Inc.

Sales Division
1, Kanai-cho, Sakae-ku
Yokohama, 244-0845, Japan
TEL: +81-45-853-8156
FAX: +81-45-853-8170

CAUTION

Eudyna Devices Inc. products contain **gallium arsenide (GaAs)** which can be hazardous to the human body and the environment. For safety, observe the following procedures:

- Do not put this product into the mouth.
- Do not alter the form of this product into a gas, powder, or liquid through burning, crushing, or chemical processing as these by-products are dangerous to the human body if inhaled, ingested, or swallowed.
- Observe government laws and company regulations when discarding this product. This product must be discarded in accordance with methods specified by applicable hazardous waste procedures.

Eudyna Devices Inc. reserves the right to change products and specifications without notice. The information does not convey any license under rights of Eudyna Devices Inc. or others.

© 2004 Eudyna Devices USA Inc.
Printed in U.S.A.