

M62381FP

8-BIT 8CH MULTIPLYING D-A CONVERTER WITH BUFFER AMPLIFIERS


EXPLANATION OF TERMINALS

Pin No.	Symbol	Function
②①	DI	Serial data input terminal
①⑧	Do	Serial data output terminal
①⑦	CLK	Serial clock input terminal
①⑥	LD	When LD terminal level is "H",latch circuit data is load
③	Vo1	8-bit resolution D-A converter output terminal
②	Vo2	
①	Vo3	
②④	Vo4	
①⑩	Vo5	
①①	Vo6	
①②	Vo7	
①③	Vo8	
②①	V _{DD}	Analog and digital common power supply terminal
①⑨	V _{SS}	Analog negative power supply terminal
⑥	GND	GND terminal
⑤	V _{IN1}	D-A converter reference input terminal
④	V _{IN2}	
②③	V _{IN3}	
②②	V _{IN4}	
⑧	V _{IN5}	
⑨	V _{IN6}	
①④	V _{IN7}	
①⑤	V _{IN8}	
⑦	RESET	When RESET terminal level is "H",all D-A output terminal became "0V"

M62381FP

8-BIT 8CH MULTIPLYING D-A CONVERTER WITH BUFFER AMPLIFIERS

DIGITAL DATA FORMAT




(1)DAC set up data

MSB				LSB				D-A output
D7	D6	D5	D4	D3	D2	D1	D0	
0	0	0	0	0	0	0	0	-V _{IN}
0	0	0	0	0	0	0	1	(1/128-1) X V _{IN}
⋮	⋮	⋮	⋮	⋮	⋮	⋮	⋮	⋮
0	1	1	1	1	1	1	1	(127/128-1) X V _{IN}
1	0	0	0	0	0	0	0	(128/128-1) X V _{IN}
1	0	0	0	0	0	0	1	(129/128-1) X V _{IN}
⋮	⋮	⋮	⋮	⋮	⋮	⋮	⋮	⋮
1	1	1	1	1	1	1	0	(254/128-1) X V _{IN}
1	1	1	1	1	1	1	1	(255/128-1) X V _{IN}

(2)DAC select data

MSB			LSB	
D11	D10	D9	D8	DAC selection
0	0	0	0	Don't care
0	0	0	1	ch1 selection
0	0	1	0	ch2 selection
⋮	⋮	⋮	⋮	⋮
0	1	1	1	ch7 selection
1	0	0	0	ch8 selection
1	0	0	1	Don't care
⋮	⋮	⋮	⋮	⋮
1	1	1	1	Don't care

TIMING CHART (MODEL)



M62381FP**8-BIT 8CH MULTIPLYING D-A CONVERTER WITH BUFFER AMPLIFIERS****ABSOLUTE MAXIMUM RATINGS**

Symbol	Parameter	Conditions	Ratings	Unit
V _{DD}	Supply voltage		-0.3 to +6.0	V
V _{IN}	Digital input voltage		-0.3 to +6.0	V
V _{SS}	Analog negative supply voltage		-6.0 to +3.0	V
V _{IN}	Input voltage		V _{SS} +0.3 to V _{DD} -0.3	V
V _O	Output voltage		V _{SS} +0.3 to V _{DD} -0.3	V
T _{opr}	Operating temperature		-20 to +85	°C
T _{stg}	Storage temperature		-40 to +125	°C

ELECTRICAL CHARACTERISTICS**Digital part**(V_{DD}=+5V, V_{SS}=-5V, V_{DD}≥V_{IN}≥V_{SS}, GND=0V, Ta=-20 to +85°C, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min.	Typ.	Max.	
V _{DD}	Supply voltage		4.5	5.0	5.5	V
I _{ILK}	Input leak current	V _{IN} =0 to V _{CC}	-10		10	μA
V _{IL}	Input low voltage				0.2V _{DD}	V
V _{IH}	Input high voltage		0.8V _{DD}			V
V _{OL}	Output low voltage	I _{OL} =2.5mA			0.4	V
V _{OH}	Output high voltage	I _{OH} =-400μA	V _{DD} -0.4			V

Analog part(V_{DD}=+5V, V_{SS}=-5V, V_{DD}≥V_{IN}≥V_{SS}, GND=0V, Ta=-20 to +85°C, unless otherwise noted)

Symbol	Parameter	Test conditions	Limits			Unit
			Min.	Typ.	Max.	
I _{IN}	D-A converter reference input current			0.2	0.4	mA
V _{AO}	Buffer amplifier output voltage range	I _{AO} =±500μA	V _{AOZERO} +0.15		V _{AOFULL} -0.15	V
		I _{AO} =±1mA	V _{AOZERO} +0.3		V _{AOFULL} -0.3	
I _{AO}	Buffer amplifier output current range	V _{AO} =V _{AOZERO} +0.3 to V _{AOFULL} -0.3	-1.0		1.0	mA
RES	Resolution		8			bit
DNL	Differential nonlinearity		-1.0		1.0	LSB
NL	Nonlinearity	V _{DD} -0.5≥V _{IN} ≥V _{SS} +0.5	-1.5		1.5	LSB
EG	Gain error		-3		3	%FS


AC CHARACTERISTICS

Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
t _{CXL}	Clock "L" pulse width		200			ns
t _{CXH}	Clock "H" pulse width		200			ns
t _{CR}	Clock rise time				200	ns
t _{CF}	Clock fall time				200	ns
t _{DCH}	Data set up time		30			ns
t _{CHD}	Data hold time		60			ns
t _{CHL}	LD set up time		200			ns
t _{LDH}	LD hold time		100			ns
t _{LDC}	LD "H" pulse width		100			ns
t _{DO}	Data output delay time	C _L =100pF	70		350	ns
t _{LDD}	D-A output setting time	Without load				ns

M62381FP

8-BIT 8CH MULTIPLYING D-A CONVERTER WITH BUFFER AMPLIFIERS

TIMING CHART



APPLICATION EXAMPLE

