



Damper Diodes (For TV)

Parameter Type No.		Absolute Maximum Ratings					Electrical Characteristics (Ta=25°C)							Others		
		V _{RM} (V)	I _F (A _V) (A) 50Hz Half-cycle Sinewave Single Shot	I _{FSM} (A)	T _J (°C)	T _{stg} (°C)	V _F (V)		I _R (μA)	I _R (H) (μA)	t _{rr} ① (μs)		t _{rr} ② (μs)		R _{th} (j-ℓ)	Mass
max	I _F (A)						V _R =V _{RM} max	V _R =V _{RM} Ta=100°C max	I _F /I _{RP} (mA)		I _F /I _{RP} (mA)	(°C/W)	(g)			
FMV-G5FS		1500	10.0	50	-40 to +150	1.5	10.0	50	700	2.0	500/500	0.8	500/1000	2.0	6.5	Ⓐ
FMR-G5HS		1800				1.6		20	200	1.8		0.7				

FMV-G5FS



FMR-G5HS



External Dimensions

(Unit: mm) (Full-mold)

Flammability:
UL94V-0 or Equivalent

