

# IM series

## Sealed snap-action pushbutton switches - bushing Ø 12 mm - momentary

Distinctive features and specifications

UG1410-A-R2



- ☐ Snap-action : tactile feedback with audible click
- ☐ High current/voltage rating
- ☐ Sealed to IP67
- ☐ Flat round actuator for optional marking

### ENVIRONMENTAL SPECIFICATIONS

- Front panel sealing : IP67 according to IEC 60529
- Shock resistance : 50 g - 11 ms according to IEC 68-2-27
- Salt spray : IEC 512-6, test 11f
- Operating temperature : -40°C to +85°C
- Storage temperature : -40°C to +85°C

### ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load : 3A 28VDC
- Initial contact resistance : 100 mΩ max.
- Insulation resistance : 1 GΩ min. at 500VDC
- Dielectric strength : 500 Vrms between terminals
- Electrical life at full load : 25.000 cycles

### GENERAL SPECIFICATIONS

- Panel thickness : 1,5 mm (.059) to 10 mm (.394)
- Total travel : 1,7 mm (.067) +/- 0,3 mm
- Low level or mechanical life : 1.000.000 cycles
- Torque (applied to nut) : 1 Nm max. with metal nut U166  
1,5 Nm max. with plastic nut U4248

### MATERIALS

- Case : polyamide 4/6
- Actuator : polyamide 6/6
- Bushing/bezel : polyamide 6/6
- Contacts : silver, gold plated
- Terminal seal : epoxy

### AGENCY APPROVAL




1A 125VAC/250VAC  
File E83438

**Availability** : consult factory for details of approved models.

**Marking** : to order switches marked UL, complete appropriate box of ordering format.


### MOUNTING - STANDARD BEZEL

#### Panel cut-out




① Flat seal

#### Matrix mounting




#### Back of panel space requirement




### MOUNTING - REDUCED BEZEL

#### Panel cut-out




② O-ring

#### Matrix mounting




#### Back of panel space requirement



# IM series

Sealed snap-action pushbutton switches - bushing Ø 12 mm - momentary

Overview



### ABOUT THIS SERIES

On the following pages, you will find successively :  
model structure of switches and options in the same order as in above chart

**Dimensions** : first dimensions are in mm while inches are shown as bracketed numbers.



**NOTICE** : please note that not all combinations of above numbers are available.  
Refer to the following pages for further information.



**A sealing boot** is available to protect the switches against frost and sand (P/N U5125).  
It is presented after the IA series and in section H.



**Mounting accessories** : Standard hardware supplied : 1 flat seal (standard bezel) or 1 O-ring (reduced bezel) and 1 metal hex nut 14 mm (.551) across flats. Hex nut part number U166.  
Plastic nut 17 mm (.669) across flats, thickness 4 mm (.157) available on request. Part number U4248.





**Packaging unit** : 50 pieces

The company reserves the right to change specifications without notice.


# IM series

Sealed snap-action pushbutton switches - bushing Ø 12 mm - momentary

Round - non-illuminated



## MODEL STRUCTURE



Actuator marking available on IMP models (symbol 10 mm max.). On request.

Common terminal identified by a horizontal dash

B1

## Standard bezel - straight PC terminals



Curved actuator  
**IMR7P4**




NC+NO

Flat actuator  
**IMP7P4**



NC+NO



## Standard bezel - quick-connect terminals



Curved actuator  
**IMR7Z4**




NC+NO


Flat actuator  
**IMP7Z4**



NC+NO




## ACTUATOR COLOURS



1 : blue - B : dark blue - 2 : black - 3 : green - 4 : grey - 5 : yellow - 6 : red - 7 : white - 9 : orange

## BUSHING AND BEZEL COLOURS



2 : black (standard)  
Other : on request

# IM series


Sealed snap-action pushbutton switches - bushing Ø 12 mm - momentary

Options


## BEZEL OPTIONS




- Blank** Standard bezel
- 075** Dia. 15 (.590) reduced bezel, mounting of the switch from the front into a threaded panel cut-out
- 234** Dia. 15 (.590) reduced bezel, standard mounting




## ACTUATOR OPTION



- Blank** Standard actuator
- 104** High actuator



## AGENCY APPROVAL



**UL**

**Availability** : consult factory for details of approved models.  
**Marking** : to order switches marked UL, complete above box with "UL".

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Apem:

[IMP7P462](#) [IMR7Z452075](#) [IMR7P422075](#) [IMP7P422104](#) [IMR7P412104](#) [IMP7Z452104](#) [IMR7P492075](#)  
[IMP7Z462075](#) [IMR7Z412234](#) [IMP7Z492](#) [IMP7Z422](#) [IMP7P462234](#) [IMR7P462104](#) [IMR7P452234](#) [IMR7Z462](#)  
[IMP7P432075](#) [IMR7Z492104](#) [IMP7P4B2075](#) [IMR7P432](#) [IMR7P4B2](#) [IMR7Z4B2075](#) [IMP7Z412](#) [IMR7P4B2075](#)  
[IMR7Z422104](#) [IMR7P492104](#) [IMR7Z462234](#) [IMR7P422104](#) [IMP7Z472](#) [IMP7Z462104](#) [IMP7P472](#) [IMR7Z462075](#)  
[IMP7Z4B2](#) [IMR7P462](#) [IMP7P422234](#) [IMP7P412234](#) [IMR7Z432104](#) [IMP7Z432](#) [IMP7P412](#) [IMR7P472104](#)  
[IMR7P432075](#) [IMP7P472234](#) [IMP7Z4B2075](#) [IMR7Z412](#) [IMR7P412](#) [IMR7P452](#) [IMP7Z412075](#) [IMP7Z472075](#)  
[IMP7Z4B2234](#) [IMR7Z4B2104](#) [IMR7P462234](#) [IMP7Z462234](#) [IMP7P4B2234](#) [IMR7Z4B2234](#) [IMP7Z432075](#)  
[IMP7Z472104](#) [IMR7Z4B2](#) [IMR7Z462104](#) [IMP7P432234](#) [IMR7P452075](#) [IMP7P472075](#) [IMP7Z452234](#) [IMP7P492](#)  
[IMR7P4B2104](#) [IMR7Z412075](#) [IMP7Z492075](#) [IMR7Z472075](#) [IMP7P492104](#) [IMP7Z412104](#) [IMR7Z452104](#)  
[IMP7Z422075](#) [IMP7Z452](#) [IMR7Z432075](#) [IMR7Z472234](#) [IMR7Z452](#) [IMP7P422](#) [IMP7P452234](#) [IMP7Z452075](#)  
[IMP7Z422234](#) [IMP7Z432104](#) [IMP7P412104](#) [IMR7Z422](#) [IMP7P432104](#) [IMR7P412075](#) [IMR7P4B2234](#) [IMR7P472075](#)  
[IMP7P422075](#) [IMR7Z422234](#) [IMR7Z412104](#) [IMR7Z472](#) [IMR7P452104](#) [IMR7P462075](#) [IMR7Z422075](#)  
[IMP7P452075](#) [IMP7P462104](#) [IMR7Z452234](#) [IMP7Z462](#) [IMR7P422](#) [IMR7Z472104](#) [IMR7P432104](#) [IMP7P432](#)